

Reassembly (continued)

6. Dome/Combination Spring and Dome Loaded Regulators are more easily reassembled by holding regulator firmly in vise and reinstalling dome.
7. Self-Venting Regulator - If your regulator has an adjustable relief valve mechanism, it is set on final assembly at the factory and usually will not require further adjustment. If adjustment becomes necessary, use the following procedure after regulator has been installed:
 - Step 1. Remove hole plug in control knob.
 - Step 2. Using control knob, apply 10 to 15 psi on downstream side.
 - Step 3. Turn CW vent adjusting screw (located under hole plug) until media can be heard escaping through relief valve.

Reassembly (continued)

- Step 4. Turn screw CCW until media flow stops, plus 1/2 turn. Replace hole plug.
8. Reinstalling wire mesh inlet filter: Insert filter into primary inlet port. It then must be expanded to fit correctly. This can be accomplished by inserting a metal tool the same size as the port and then lightly tapping it with a hammer.



AFTER REGULATOR HAS BEEN REASSEMBLED, IT SHOULD BE CONNECTED TO A PRESSURE SOURCE WITH MEDIA COMPATIBLE WITH THE USE OF THE REGULATOR AND PRESSURIZED TO CHECK FOR INTERNAL AND EXTERNAL LEAKAGE AND OPERATING CHARACTERISTICS.

LIMITED WARRANTY

Tescom Corporation ("Seller") warrants that the licensed firmware embodied in the goods will execute the programming instructions provided by Seller, and that the goods manufactured or services provided by Seller will be free from defects in materials or workmanship under normal use and care until the expiration of the applicable warranty period. Goods are warranted for twelve (12) months from the date of initial installation or eighteen (18) months from the date of shipment by Seller, whichever period expires first. Consumables and services are warranted for a period of 90 days from the date of shipment or completion of the services. Products purchased by Seller from a third party for resale to Buyer ("Resale Products") shall carry only the warranty extended by the original manufacturer. Buyer agrees that Seller has no liability for Resale Products beyond making a reasonable commercial effort to arrange for procurement and shipping of the Resale Products. If buyer discovers any warranty defects and notifies Seller thereof in writing during the applicable warranty period, Seller shall, at its option, correct any errors that are found by Seller in the firmware of services or repair or replace F.O.B. point of manufacture that portion of the goods or firmware found by Seller to be defective, or refund the purchase price of the defective portion of the goods/services. All replacements or repairs necessitated by inadequate maintenance, normal wear and usage, unsuitable power sources or environmental conditions, accident, misuse, improper installation, modification, repair, storage or handling, or any other cause not the fault of Seller are not covered by this limited warranty, and shall be at buyer's expense. Seller shall not be obligated to pay any costs or charges incurred by buyer or any other party except as may be agreed upon in writing in advance by Seller. All costs of dismantling, reinstallation and freight and the time and expenses of Seller's personnel and representatives for site travel and diagnosis under this warranty clause shall be borne by buyer unless accepted in writing by Seller. Goods repaired and parts replaced by Seller during the warranty period shall be in warranty for the remainder of the original warranty period or ninety (90) days, whichever is longer. This limited warranty is the only warranty made by Seller and can be amended only in a writing signed by Seller. THE WARRANTIES AND REMEDIES SET FORTH ABOVE ARE EXCLUSIVE. THERE ARE NO REPRESENTATIONS OR WARRANTIES OF ANY KIND, EXPRESSED OR IMPLIED, AS TO MERCHANTABILITY, FITNESS FOR PARTICULAR PURPOSE OR ANY OTHER MATTER WITH RESPECT TO ANY OF THE GOOD OR SERVICES.

12616 Industrial Boulevard
Elk River, MN 55330 USA
T +1 800 447 1250
+1 763 241 3238
F +1 763 241 3224
E na.tescom@emerson.com
W www.tescom.com

TESCOM


EMERSON
Process Management

OPERATION AND SERVICE MANUAL

for

TESCOM

Diaphragm Sensed Pressure Reducing Regulators

General

TESCOM's diaphragm sensed pressure reducing regulators are specifically engineered for applications requiring dependable pressure regulation. These regulators are especially appropriate for installations where high system pressures (up to 6000 psi) must be reduced to levels suitable for actuating low pressure (28 vac to 500 psi) instruments and related equipment.

Pressure Activation Methods

TESCOM uses three basic types of activation methods. The activation method provides the means by which the operator can set the force that determines the outlet pressure of a regulator.

Control Knob: Delivery pressure is increased by turning the control knob. The control knob applies a load through a spring to the diaphragm.

Dome Load: Delivery pressure is increased by applying pressurized gas or liquid to the dome of a regulator at a pressure equal to the outlet pressure desired. This dome pressure is normally provided by a second regulator called the pilot regulator.

Combination Spring and Dome: Delivery pressure is increased by applying a spring force as well as the introduction of pressurized gas or liquid.

Operation (Control Knob Adjustment)

Controlled outlet pressure settings are obtained using TESCO pressure reducing regulators by adjusting the control knob. Rotating the knob clockwise raises the outlet pressure while a counterclockwise rotation coupled with venting of the downstream side of the regulator plumbing lowers the outlet pressure. Final adjustments should be made in the direction of increasing pressure to obtain the most accurate set point.

TESCOM regulators will operate with any liquid or gaseous media compatible with the wetted materials. Some series/modifications come with an internal filter designed to stop random contamination resulting from the installation of the regulator. An auxiliary upstream filter is recommended for use in all but the cleanest media. Gaseous media should be free of excessive moisture to prevent icing of the regulator at high flow rates.



A REGULATOR IS NOT INTENDED TO BE USED AS A SHUTOFF DEVICE. WHEN THE REGULATOR IS NOT IN USE, THE INLET SUPPLY SHOULD BE TURNED OFF. AS A SAFETY PRECAUTION, A PRESSURE RELIEF DEVICE SHOULD BE INSTALLED DOWNSTREAM OF THE REGULATOR.

Maintenance

The following procedures are provided to enable the customer to perform all normal maintenance and repair operations. These operations are more easily performed with the regulator removed from the line. However, in some cases repair may be accomplished without removal of the regulator body as long as the supply has been shut off and the inlet and outlet pressures have been vented.

The following steps outline the disassembly of pressure reducing regulators for maintenance and repair (up-to-date assembly drawings and bills of material are available from TESCO):

1. Clamp the regulator in a vise by the flats on the bottom and/or side of the regulator body.
2. Turn control knob and/or spring adjustment mechanism counterclockwise to insure removal of all spring force on the diaphragm.

Maintenance (continued)

NOTE: (Dome loaded regulators) All pressurized gas or liquid must be vented from dome before disassembly.

3. Remove upper portion of regulator (bonnet and/or dome). Some models require the mounting bracket to be removed first.

NOTE: Upper portion of regulator may also include spring button, load spring back-up plate, and diaphragm, etc. Review correct drawing to ensure that all parts have been disassembled.

NOTE: (Two-Stage Regulator) TESCO Model Series 44-3400 is a two-stage regulator that has portions on both ends of the regulator body that must be removed. It is TESCO's recommendation that two-stage regulators be returned to the factory for repair.

4. The valve parts can now be removed from the regulator body by turning the seat retainer and/or back cap counterclockwise until it is free of the regulator body.

NOTE: If necessary, valve seat may be removed from the seat retainer using a sharp instrument.

CAUTION: When removing valve parts from a regulator that has a back cap, care must be taken to insure the main valve stem remains vertical. If the main valve stem is not removed correctly, parts may remain in the regulator.

5. To disassemble main valve assembly and/or valve, clamp valve in smoothed jaw vice or hold with pliers. Clamping should be done on flats.

CAUTION: Care must be used to not damage valve.



SEVERAL TESCO REGULATORS ARE SUPPLIED WITH INTERNAL FILTERS. THEY WILL BE LOCATED EITHER IN THE INLET PORT OR IN THE MAIN VALVE AREA OF THE REGULATOR. IN EACH CASE, THEY SHOULD BE REMOVED AND REPLACED BEFORE REASSEMBLY.

Reassembly

The regulator is reassembled in the reverse order of disassembly, observing the following precautions. Please reference the Bill of Material and assembly drawing for the correct location of replacement parts and correct torque specifications.

1. Inspect all parts and replace those worn or damaged with TESCO replacement parts.
2. All parts should be cleaned to the cleanliness level required for safe operation with the media and system they will be used in. All parts in the flow stream must be free of particles which could prevent proper seating of the main valve.
3. Apply a thin uniform coating of fluorocarbon grease to any or all of the following parts: Indentation of spring button, threaded portion of adjusting screw, entire threaded area of the bonnet, all O-rings, all threaded parts internal to regulator.



DO NOT APPLY ANY TYPE OF GREASE TO THREADED INTERNAL PARTS OF REGULATORS THAT COME STANDARD WITH METAL TO METAL DIAPHRAGM SEALS. THESE MODELS INCLUDE THE FOLLOWING REGULATOR SERIES: 44-2200, 44-2300, 44-2600, 44-2800, 44-3200, 44-3400, 44-4600 AND 44-4800 SERIES.

NOTE: Do NOT apply any type of grease to the inlet or outlet connections.

4. Valve seat must be installed with the chamfered side towards the main valve.
5. Standard Regulator with Control Knob - The body and bonnet are best joined by holding the bonnet assembly open end up and dropping all required items into place one at a time. The last item to be placed in the bonnet will be the diaphragm. It can be centered on the seating surface of the bonnet before the body assembly is inverted and screwed into the bonnet firmly – hand tight. Regulator should then be placed in vise and bonnet retorqued to correct specifications. See print.