ATEX Hazardous Area Approvals Fisher™ FIELDVUE™ DVC6200 Series Digital Valve Controllers

Hazardous Area Approvals and Special Instructions for "Safe Use" and Installations in Hazardous Locations

Certain nameplates may carry more than one approval, and each approval may have unique installation/wiring requirements and/or conditions of "safe use". These special instructions for "safe use" are in addition to, and may override, the standard installation procedures. Special instructions are listed by approval type.

NOTE

This information supplements the nameplate markings affixed to the product and the DVC6200 Series Quick Start Guide (D103556X012), available from your Emerson sales office or at Fisher.com.

Always refer to the nameplate itself to identify the appropriate certification.

Approval information is for both aluminum and stainless steel constructions.

WARNING

Failure to follow these conditions of "safe use" could result in personal injury or property damage from fire or explosion and area re-classification.

WARNING

To avoid static discharge from the plastic cover when flammable gases or dust are present, do not rub or clean the cover with solvents. To do so could result in a spark that may cause the flammable gases or dust to explode, resulting in personal injury or property damage. Clean with a mild detergent and water only.



March 2024 D104205X012

WARNING

Special Conditions of Use:

The apparatus enclosure contains aluminium and is considered to constitute a potential risk of ignition by impact or friction. This shall be taken into account when installed in Zone 0 locations and care shall be taken to prevent impact or friction during the installation and use (applicable only to aluminium constructions).

Flameproof II 2 GD

WARNING

Potential electrostatic charging hazard. See WARNING on page 1.

Covered by Standards: EN IEC 60079-0: 2018 EN 60079-1:2014 EN 60079-31:2014

DVC6200 and DVC6205 Series HART, FOUNDATION Fieldbus, PROFIBUS Ex db IIC T5/T6 Gb, IP66
Ex tb IIIC T88 °C Db, IP66 (not applicable to DVC6205 Series)
Ta = -52 or -40 to +85 °C

DVC6215 and DVC6215NA Ex db IIC T4/T5/T6 Gb, IP66 Ta = -52 to +125 °C

Type n, Increased Safety 🖾 II 3 G

WARNING

Potential electrostatic charging hazard. See WARNING on page 1.

Covered by Standards: EN IEC 60079-0: 2018 EN IEC 60079-15: 2019

DVC6200 and DVC6205 Series HART, FOUNDATION Fieldbus, PROFIBUS Ex nC IIC T5/T6 Gc, IP66

Ta = -52 or -40 to +80 °C

DVC6215 Ex ec IIC T4/T5/T6 Gc, IP66 Ta = -52 to +125 °C

Intrinsically Safe 🖘 II 1 GD

WARNING

Potential electrostatic charging hazard. See WARNING on page 1.

Covered by Standards: EN IEC 60079-0: 2018 EN 60079-11:2012

DVC6200 and DVC6205 Series

Ex ia IIC or IIB T4/T5/T6 Ga, IP66 Ex ia IIC, T4/T5/T6 Ga, IP66 Ex ia IIIC Txx °C Da, IP66 Ta = -52 / -40 to +80 °C Ex ia IIC/IIB valid to: Ta = -55 to +80 °C HART FOUNDATION Fieldbus, PROFIBUS DVC6200 Series DVC6200 and DVC6205 Series DVC6200 and DVC6205 Series

DVC6215

Ex ia IIC T4/T5/T6 Ga, IP66 Ta = -52 to +125 °C

Intrinsically safe when connected per control drawing GE42990, as shown in the following figures:

DVC6200 HW2 and DVC6200 SIS	Figures 1 and 5
DVC6205, DVC6205 SIS and DVC6215 Remote Mount	
DVC6200f and DVC6200p	
DVC6205f, DVC6205p and DVC6215 Remote Mount	Figures 4 and 5

D104205X012

Figure 1. Loop Schematics – FIELDVUE DVC6200 HW2 and DVC6200 SIS

**ZONE 0, Ex ia IIC OR IIB T5 TO T6 **ZONE 20, Ex ia IIIC Txx °C

	DVC6200, DVC6200S HW2 - WITH OR WITHOUT I/O PACKAGE			
I/O PACKAGE?	NO	YES	YES	
RATING	Ex ia IIC	Ex ia IIC	Ex ia IIC	
LOOP TERMINALS	Ui: 30 V DC Ii: 130 mA Pi: 1.0 W Ci: 15 nF Li: 0.15 mH	Ui: 30 V DC Ii: 130 mA Pi: 1.0 W Ci: 15 nF Li: 0.15 mH	Ui: 30 V DC Ii: 101 mA Pi: 757 mW Ci: 15 nF Li: 0.30 mH	
AUX TERMINALS	NOT PROVIDED	NOT USED	U: 30 V DC Io: 101 mA Po: 757 mW Co: 52.4 nF Lo: 3.18 mH	
RATING	N/A	Ex ia IIC	Ex ia IIC	
OUTPUT TERMINALS	NOT PROVIDED	Ui: 28 V DC Ii: 100 mA Pi: 1.0 W Ci: 15 nF Li: 0.23 mH	Ui: 28 V DC Ii: 100 mA Pi: 1.0 W Ci: 15 nF Li: 0.23 mH	

NOTES:

^{***} NOTE - EQUIPMENT MARKED Ex ia IIIC Txx °C MAY USE ANY OF THE ENTITY PARAMETERS STATED ABOVE.

	Without I/O Package	With I/O Package	
CAC	T5 (Ta ≤ 80 °C)	T5 (Ta ≤ 80 °C)	
GAS	T6 (Ta ≤ 74 °C)	T6 (Ta ≤ 61 °C)	
DUCT	T91 °C (Ta ≤ 80 °C)	T104 °C (Ta ≤ 80 °C)	
DUST	T85 °C (Ta ≤ 74 °C)	T85 °C (Ta ≤ 61 °C)	

GE42990 Sheet 11 Rev. E


^{1.} SEE NOTES IN FIGURE 5.

^{**} NOTE - POWER MAY BE APPLIED TO EITHER THE LOOP TERMINALS OR OUTPUT TERMINALS OR TO BOTH SETS OF TERMINALS AT THE SAME TIME.

^{**} NOTE - THE AUX TERMINAL PARAMETERS ARE NOT FULLY INDEPENDENT FROM THE LOOP TERMINAL PARAMETERS AND IS THEREFORE DEEMED AS A SOURCE WITH OUTPUTS.

^{**} NOTE - WHEN THE AUX TERMINALS ARE USED, THE MAXIMUM OUTPUT (U, I AND P) WILL BE IDENTICAL TO THE ASSOCIATED APPARATUS FEEDING THE LOOP TERMINALS.

^{**} NOTE - ONLY IF THE NAMEPLATE BEARS THIS MARKING.



March 2024

D104205X012

Figure 2. Loop Schematics – FIELDVUE DVC6205, DVC6205 SIS and DVC6215

ZONE 0, Ex ia IIC OR IIB T5 TO T6

	DVC6205 HW2 - WITH OR WITHOUT I/O PACKAGE			
	REMOTE FIELD WIRING TERMINAL BOX	FIELD WIRING TERMINAL B		TERMINAL BOX
	REMOTE TERMINALS	I/O PACKAGE?	NO	YES
	Ex ia IIC	RATING	Ex ia IIC	Ex ia IIC
ZONE 0, Ex ia IIC T4 to T6		LOOP TERMINALS	Ui: 30 V DC Ii: 130 mA Pi: 1.0 W Ci: 15 nF Li: 0.15 mH	Ui: 30 V DC Ii: 130 mA Pi: 1.0 W Ci: 15 nF Li: 0.15 mH
DVC6215 Ui: 30 V DC Ii: 226 mA Pi: 1.4 W Ci: 50 nF	- Uo: 30 V DC - Io: 21.2 mA - Po: 160 mW - Co: 55 nF	AUX TERMINALS	NOT PROVIDED	NOT USED
Li: 0.55 mH	Lo: 78 mH	RATING	N/A	Ex ia IIC
Ex ia IIC T4 to T6 TYPE		OUTPUT TERMINALS	NOT PROVIDED	Ui: 28 V DC Ii: 100 mA Pi: 1.0 W Ci: 15 nF Li: 0.23 mH
NOTES				<u> </u>

NOTES

^{**} NOTE - WHEN THE AUX TERMINALS ARE USED, THE MAXIMUM OUTPUT (U, I AND P) WILL BE IDENTICAL TO THE ASSOCIATED APPARATUS FEEDING THE LOOP TERMINALS.

	Ex ia IIC or IIB T5 to T6		
	Without I/O Package	With I/O Package	
TYPE	T CODE =	T CODE =	
DVC6205	T5 (Ta ≤ 80 °C)	T5 (Ta ≤ 80 °C)	
	T6 (Ta ≤ 74 °C)	T6 (Ta ≤ 61 °C)	


GE42990 Sheet 12 Rev. E

^{1.} SEE NOTES IN FIGURE 5.

^{**} NOTE - POWER MAY BE APPLIED TO EITHER THE LOOP TERMINALS OR OUTPUT TERMINALS OR TO BOTH SETS OF TERMINALS AT THE SAME TIME.


^{**} NOTE - THE AUX TERMINAL PARAMETERS ARE NOT FULLY INDEPENDENT FROM THE LOOP TERMINAL PARAMETERS AND IS THEREFORE DEEMED AS A SOURCE WITH OUTPUTS.

D104205X012 March 2024



March 2024 D104205X012

Figure 3. Loop Schematics – FIELDVUE DVC6200f and DVC6200p



	Ex ia IIC T4 to T6	***Ex ia IIIC Txx °C
TYPE	T CODE =	Txx °C =
DVC6200F	T4 (Ta ≤ 80 °C)	T103 °C (Ta ≤ 80 °C)
DVC6200FS DVC6200P	T5 (Ta ≤ 77 °C)	T100 °C (Ta ≤ 77 °C)
DVC6200PS	T6 (Ta ≤ 62 °C)	T85 °C (Ta ≤ 62 °C)


NOTES:

- 1. SEE NOTES IN FIGURE 5.
- ** NOTE: THE AUX TERMINALS ALLOW FOR ADDITIONAL CONFIGURATIONS BY SHORTING THEM TOGETHER LOCALLY OR REMOTELY BY USE OF A SWITCH.
- ** NOTE: IF FISCO IS IMPLEMENTED,
 - UI: 17.5 V DC AND PI: 5.32 W
- *** ONLY IF THE NAMEPLATE BEARS THIS MARKING.

GE42990 Sheet 3, Rev. G

D104205X012 March 2024

Figure 4. Loop Schematics – FIELDVUE DVC6205f, DVC6205p and DVC6215



NOTES:

- 1. SEE NOTES IN FIGURE 5.
- ** NOTE: THE AUX TERMINALS ALLOW FOR ADDITIONAL CONFIGURATIONS BY SHORTING THEM TOGETHER LOCALLY OR REMOTELY BY USE OF A SWITCH.
- ** NOTE: IF FISCO IS IMPLEMENTED, UI: 17.5 V DC AND PI: 5.32 W

UO: 17.5 V DC

GE42990 Sheet 9, Rev. E

March 2024 D104205X012

Figure 5. Notes for Loop Schematics

SPECIAL CONDITIONS OF USE:

THE APPARATUS ENCLOSURE CONTAINS ALUMINUM AND IS CONSIDERED TO CONSTITUTE A POTENTIAL RISK OF IGNITION BY IMPACT AND FRICTION. CARE MUST BE TAKEN INTO ACCOUNT DURING INSTALLATION AND USE TO PREVENT IMPACT OR FRICTION.

1. THE ENTITY CONCEPT ALLOWS INTERCONNECTION OF INTRINSICALLY SAFE APPARATUS TO ASSOCIATED APPARATUS NOT SPECIFICALLY EXAMINED IN SUCH COMBINATION. THE CRITERIA FOR INTERCONNECTION IS THAT THE VOLTAGE (VMAX OR UI), THE CURRENT (IMAX OR II), AND THE POWER (PMAX OR PI) OF THE INTRINSICALLY SAFE APPARATUS MUST BE EQUAL TO OR GREATER THAN THE VOLTAGE (VOC OR UO), AND THE CURRENT (ISC OR IO), AND THE POWER (PO) DEFINED BY THE ASSOCIATED APPARATUS. IN ADDITION, THE SUM OF THE MAX UNPROTECTED CAPACITANCE (CI) AND MAX UNPROTECTED INDUCTANCE (LI), INCLUDING THE INTERCONNECTING CABLING CAPACITANCE (CCABLE) AND CABLING INDUCTANCE (LCABLE) MUST BE LESS THAN THE ALLOWABLE CAPACITANCE (CA) AND INDUCTANCE (LA) DEFINED BY THE ASSOCIATED APPARATUS. IF THE ABOVE CRITERIA IS MET, THEN THE COMBINATION MAY BE CONNECTED.

Vmax or Ui ≥ Voc or Uo Imax or Ii ≥ Isc or Io Pmax or Pi ≥ Po Ci + Ccable ≤ Ca Li + Lcable ≤ La

2. THE FISCO CONCEPT ALLOWS INTERCONNECTION OF INTRINSICALLY SAFE APPARATUS TO ASSOCIATED APPARATUS NOT SPECIFICALLY EXAMINED IN SUCH COMBINATION. THE CRITERIA FOR THE INTERCONNECTION IS THAT THE VOLTAGE (VMAX OR UI), CURRENT (IMAX OR II), AND POWER (PMAX OR PI), WHICH AN INTRINSICALLY SAFE APPARATUS CAN RECEIVE AND REMAIN INTRINSICALLY SAFE, CONSIDERING FAULTS, MUST BE EQUAL TO OR GREATER THAN THE VOLTAGE (VOC OR UO), CURRENT (ISC OR IO), AND POWER (PO) LEVELS WHICH CAN BE DELIVERED BY THE ASSOCIATED APPARATUS, CONSIDERING FAULTS AND APPLICABLE FACTORS. IN ADDITION, THE MAXIMUM UNPROTECTED CAPACITANCE (CI) AND INDUCTANCE (LI) OF EACH APPARATUS (OTHER THAN THE TERMINATION) CONNECTED TO THE FIELDBUS MUST BE LESS THAN OR EQUAL TO 5 NF AND 10 UH, RESPECTIVELY.

IN EACH SEGMENT, ONLY ONE ACTIVE DEVICE, NORMALLY THE ASSOCIATED APPARATUS, IS ALLOWED TO PROVIDE THE NECESSARY ENERGY FOR THE FIELDBUS SYSTEM. THE VOLTAGE (UO OR VOC OR VT) OF THE ASSOCIATED APPARATUS HAS TO BE LIMITED TO THE RANGE OF 9 TO 17.5 V DC. ALL OTHER EQUIPMENT CONNECTED TO THE BUS CABLE HAS TO BE PASSIVE, MEANING THAT THEY ARE NOT ALLOWED TO PROVIDE ENERGY TO THE SYSTEM, EXCEPT FOR A LEAKAGE CURRENT OF 50 UA FOR EACH CONNECTED DEVICE. SEPARATELY POWERED EQUIPMENT NEEDS A GALVANIC ISOLATION TO ASSURE THAT THE INTRINSICALLY SAFE FIELDBUS CIRCUIT REMAINS PASSIVE.

- continued -

D104205X012 March 2024

Figure 5. Notes for Loop Schematics (continued)

THE CABLE USED TO INTERCONNECT THE DEVICES NEEDS TO HAVE THE PARAMETERS IN THE FOLLOWING RANGE:

LOOP RESISTANCE R': 15 TO 150 OHMS/KM INDUCTANCE PER UNIT LENGTH L: 0.4 TO 1 MH/KM CAPACITANCE PER UNIT LENGTH C': 80 TO 200 NF/KM

C' = C' LINE/LINE + 0.5' LINE/SCREEN, IF BOTH LINES ARE FLOATING OR

C' = C' LINE/LINE + C' LINE/SCREEN, IF THE SCREEN IS CONNECTED TO ONE LINE. LENGTH OF SPLICE: < 1 M (T-BOX MUST ONLY CONTAIN TERMINAL

CONNECTIONS WITH NO ENERGY STORAGE

CAPABILITY)

LENGTH OF SPUR CABLE: < 30 M LENGTH OF TRUNK CABLE: < 1 KM

AT EACH END OF THE TRUNK CABLE, AN APPROVED INFALLIBLE TERMINATION WITH THE FOLLOWING PARAMETERS IS SUITABLE:

R = 90 TO 100 OHMS AND C = 0 TO 2.2 UF

NOTE: A BUILT-IN TERMINATOR IS INCLUDED ON THE FIELD SIDE AND A SELECTABLE TERMINATOR IS AVAILABLE ON THE HOST SIDE.

THE NUMBER OF PASSIVE DEVICES CONNECTED TO THE BUS SEGMENT IS NOT LIMITED IN THE FISCO CONCEPT FOR INTRINSICALLY SAFE REASONS. IF THE ABOVE RULES ARE RESPECTED, UP TO A TOTAL LENGTH OF 1000 M (SUM OF THE LENGTH OF THE TRUNK CABLE AND ALL SPUR CABLES), THE INDUCTANCE AND CAPACITANCE OF THE CABLE WILL NOT IMPAIR THE INTRINSIC SAFETY OF THE INSTALLATION.

- 3. INSTALLATION MUST BE IN ACCORDANCE WITH THE NATIONAL WIRING PRACTICES OF THE COUNTRY IN USE.
- 4. LOOPS MUST BE CONNECTED ACCORDING TO THE BARRIER MANUFACTURER'S INSTRUCTIONS.
- 5. IF HAND-HELD COMMUNICATOR OR MULTIPLEXER IS USED, IT MUST BE IECEX APPROVED WITH ENTITY PARAMETERS AND INSTALLED PER THE MANUFACTURER'S CONTROL DRAWINGS.

GE42990 Sheet 8, Rev. E





D104205X012 © 2017, 2024 Fisher Controls International LLC. All rights reserved.

Neither Emerson, nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher and FIELDVUE are marks owned by one of the companies in the Emerson business unit of Emerson Electric Co. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Marshalltown, Iowa 50158 USA Sorocaba, 18087 Brazil Cernay, 68700 France Dubai, United Arab Emirates Singapore 128461 Singapore

www.Fisher.com



