


CGA103450A: Prismatic Model



To ensure safety, the referenced Li-ion cell is not sold as a bare cell. Li-ion cells must be integrated with the appropriate safety circuitry via an authorized Panasonic Li-ion pack assembler.



Specifications

Nominal Voltage		3.7 V
Standard Capacity^{*1}		1950mAh
Dimensions^{*2}	Width	34.0 + 0/-0.6mm
	Height	50.0 + 0/-1.0mm
	Thickness	10.6 + 0/-0.6mm
	Weight	Approx. 39g


*1 After a fresh battery has been charged at constant voltage/constant current (4.2 V, 1200 mA (max), 2 hours, 20°C), the average of the capacity (ending voltage of 3 V at 20°C) that is discharged at a standard current (370 mA).

*2 Dimensions of a fresh battery

Discharge Characteristics



Charge Characteristics



Cycle Life Characteristics

