

C5015 2 Pin, Sensor Cable

Emerson has a variety of C5015 2 Pin Sensor Cables to fit your needs including armored versions.

| Overview | |
|--|---|
| Cable Style | Multi-Conductor Shielded |
| Conductors | 2 |
| Sensor Connector | Push-on Environmental Boot for C-5015, 2 Pin |
| Cable Termination | Blunt Cut or BNC – see order matrix |
| Environmental | |
| Temperature Range | -50 to 121°C (-58 to 250°F) |
| Electrical | |
| Capacitance | 118 pF/m (36 pF/ft) |
| Physical | |
| Material | Black Polyurethane |
| Cable Diameter/ Minimum Bend Radius | 6.35 mm (0.25") / 63.5 mm (2.5") |
| Cable Weight | 62 g/m (0.67 oz/ft) |
| Conductor Details | 2; 1.02 mm (0.04") diameter, 19 Strand, 32AWG, Tin Plated Copper |
| Shield Details | Braid: 90% minimum coverage |



Available Versions:

- A612-NA-09-0; C5015 push on boot, no armor, 9 m (30') cable, blunt cut termination
- A612-NA-18-0; C5015 push on boot, no armor, 18 m (60') cable, blunt cut termination
- A612-NA-30-0; C5015 push on boot, no armor, 30 m (100') cable, blunt cut termination
- A612-AR-09-0; C5015 push on boot, with armor, 9 m (30') cable, blunt cut termination
- A612-AR-18-0; C5015 push on boot, with 9 m (30') armor, 18 m (60') blunt cut cable
- A612-AR-30-0; C5015 push on boot, with 9 m (30') armor, 30 m (100') blunt cut cable
- A612-NA-09-B; C5015 push on boot, no armor, 9 m (30') cable, BNC termination
- A612-NA-18-B; C5015 push on boot, no armor, 18 m (60') cable, BNC termination
- A612-NA-30-B; C5015 push on boot, no armor, 30 m (100') cable, BNC termination

**Emerson Process Management
Reliability Solutions**
835 Innovation Drive
Knoxville, TN 37932
T (865) 675-2400

©2015, Emerson Process Management. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Machinery Health is a mark of one of the Emerson Process Management family of companies. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.