

5700 Transmitter Specifications

Standard interface/display	Graphical backlit display with 4-button optical controls and flowmeter-status LED Supports English, German, French, Spanish, Portuguese, Russian, Chinese and Japanese
Power	Self switching AC/DC input, automatically recognizes supply voltage
Configurable I/O version	<ul style="list-style-type: none"> • Up to 3 mA outputs • Up to 3 Pulse outputs • Up to 3 Discrete outputs • Up to 2 Discrete inputs • mA and Pulse inputs • Modbus/RS-485
Ethernet version	<ul style="list-style-type: none"> • Dual Ethernet ports supporting EtherNet/IP, Modbus TCP, and Profinet • Additional channel configurable to mA output, Pulse output, Discrete Output, or Discrete Input
Fieldbus version	<ul style="list-style-type: none"> • FOUNDATION™ Fieldbus channel • mA output • Pulse output
Operating temperature limit	-40 to +149 °F (-40 to +65 °C)
Mounting	Integral or remote-mount options (4-wire and 9-wire)
Communication protocols	Modbus/USB, HART/RS-485, Modbus/RS-485, HART/Bell 202
Advanced features	Smart Meter Verification, Concentration Measurement, API Referral, Batching



5700 Transmitter



CONFIDENCE & INSIGHT



For over 35 years, Emerson's Micro Motion has been a technology leader delivering the most precise flow, density and concentration measurement devices for fiscal applications, process control and process monitoring. Our passion for solving flow and density measurement challenges is proven through the highly accurate and unbeatable performance of our devices.



For more information, please visit: www.MicroMotion.com/5700

©2016 Micro Motion, Inc. All rights reserved. The Emerson logo is a trademark and service mark of Emerson Electric Co. Micro Motion, ELITE, ProLink, MVD and MVD Direct Connect marks are marks of one of the Emerson Process Management family of companies. All other marks are property of their respective owners.

Emerson Process Management Americas

7070 Winchester Circle
Boulder, Colorado USA 80301
www.MicroMotion.com
www.Rosemount.com
T: +1 800 522 6277
T: +1 (303) 527 5200
F: +1 (303) 530 8459

Mexico T: 52 55 5809 5300
Argentina T: 54 11 4837 7000
Brazil T: 55 15 3413 8000
Venezuela T: 58 26 1300 8100

Emerson Process Management Europe/Middle East

Central & Eastern Europe T: +41 41 7686 111
Dubai T: +971 4 811 8100
Abu Dhabi T: +971 2 697 2000
France T: 0800 917 901
Germany T: 0800 182 5347
Italy T: 8008 77334
The Netherlands T: +31 318 495 555
Belgium T: +32 2 716 77 11
Spain T: +34 913 586 000
U.K. T: 0870 240 1978
Russia/CIS T: +7 495 981 9811

Emerson Process Management Asia Pacific

Australia T: (61) 3 9721 0200
China T: (86) 21 2892 9000
India T: (91) 22 6662 0566
Japan T: (81) 3 5769 6803
South Korea T: (82) 2 3438 4600
Singapore T: (65) 6 777 8211

THE NEXT GENERATION OF
PROCESS INSIGHT IS HERE



MICRO MOTION® MODEL 5700

THE CORIOLIS FLOW AND DENSITY TRANSMITTER
FOR SUPERIOR PROCESS MEASUREMENT

INTRODUCING EMERSON'S MICRO MOTION® 5700 TRANSMITTER

Superior Process Insight for Optimizing Your Performance: Today and in the Future

The Micro Motion 5700 transmitter delivers the best in measurement technology and offers unparalleled support — ensuring total measurement confidence, valuable process insight and greater operational efficiency.

The 5700 provides the scalability, compatibility and performance that your application demands.



You face more than your share of obstacles when it comes to managing uptime, throughput, and optimizing your operations - and challenges like a retiring workforce and tighter regulations add to the complexity. To meet your goals, you need measurements you can count on, simple and easy products to work with and expert support for help when you need it.

The Micro Motion 5700 Transmitter Delivers:

Repeatable, Reliable, Accurate Measurements

- Faster processing speed delivers the best response even in the most challenging applications such as meter proving, filling & dosing and batching
- Smart Meter Verification provides you with the confidence you need in your meter performance
- Zero verification confirms the calibration and indicates when it's time to re-zero the meter

A Window into Your Process


- Easy access to detailed measurement history gives you valuable insight into your process for better troubleshooting and optimization
- Real-time indication of multi-phase flow events allow for greater process control
- High-accuracy density measurement reduces or eliminates waste in your process, while the embedded historian records upsets and process deviations

Productivity Through Simplified Solutions

- Designed to minimize the time and expertise needed to install and operate the flowmeter
- Configurable I/O version offers up to five fully configurable channels that can be easily upgraded with changing needs
- Ethernet version offers dual Ethernet ports plus configurable channel for expansive connectivity
- Fieldbus version offers fieldbus connection, plus additional I/O
- Offline configuration and auditing through new file shuttling capability


Simplified Installation and Commissioning

An intuitive user interface, spacious side-access wiring compartment and convenient mounting brackets



Measurement History for Easier Troubleshooting and Optimization

Detailed history files deliver key time-stamped information about your process from configuration changes and alerts to process events and statistics




Smart Meter Verification

Our online tool verifies your meter performs as well as the day it was installed, giving you assurance in less than 90 seconds



Unmatched System Connectivity and Services Interfaces

Multiple versions of the 5700 platform offer the broadest range of input and output options, and several powerful service interfaces



The Micro Motion 5700 Transmitter
 NOW IT'S ALL JUST A PART OF THE PROCESS...