

MATERIAL SAFETY DATA SHEET

MANUFACTURER: Manufactured for
ROSEMOUNT ANALYTICAL INC.
ADDRESS: 851 McKinley Avenue
Colombus, OH 43222

DATE REVISED: 1-27-11
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Nitroprusside Reagent, Reagent #3 (Green)

Synonyms:

Part Number: 180-1010-74

SECTION 2-Composition/Information on Ingredients

| Ingredient(s) | CAS # | Percent | Hazardous |
|--------------------------------|------------|---------|-----------|
| Water | 7732-18-5 | 99.968 | no |
| Sodium Nitroprusside Dihydrate | 13755-38-9 | 0.032 | no |

SECTION 3-Hazards Identification

Health Rating: 2
Flammability Rating: 0
Reactivity Rating: 1

Lab Protective Equip: gloves, safety goggles with shields

SECTION 4-First Aid Measures

INHALATION: Remove to fresh air. Seek attention if necessary.
INGESTION: Do not induce vomiting. Give large volumes of milk or water. Call a physician.
SKIN CONTACT: Flush well with soap and water.
EYE CONTACT: Flush well with water for at least 15 minutes. Seek medical attention if irritation persists.

SECTION 5-Fire Fighting Measures

Fire: Not Combustible
Explosion: N/A
Fire Extinguishing Media: Fight Surrounding Fire
Special Information: N/A

SECTION 6-Accidental Release Measures

May cause surfaces to become slippery; ventilate; absorb on inert material. Store in an enclosed container and dispose of according to local, state & federal regulations, or neutralize with dilute acid and dispose of as non-hazardous waste.

SECTION 7-Handling and Storage

N/A

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/A
Ventilation System: Normal room ventilation
Personal Respirators (NIOSH Approved): Not required
Skin Protection: impervious gloves
Eye Protection: safety glasses with shields

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid
Odor: Odorless
Solubility: soluble
Specific Gravity: N/E
pH: 3.72
Boiling Point: 213 degrees Fahrenheit
Melting Point: N/E
Vapor Density (Air=1): N/E
Vapor Pressure (mm Hg): N/E
Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable
Hazardous Decomposition Products: None
Hazardous Polymerization: N/E
Incompatibilities: None
Conditions to Avoid: Ferric salts, mineral acids, lime water

SECTION 11-Toxicological Information:

Routes of absorption: Inhalation, ingestion.
Threshold limit value: N/E
Signs, symptoms and effects of exposure:
 Acute: May cause irritation to eyes skin respiratory tract
 Chronic: N/E

SECTION 12-Ecological Information

Environmental Fate: N/A
Environmental Toxicity: N/A

SECTION 13-Disposal Considerations

SPECIFIC WASTE DISPOSAL METHOD(S): Treat a dilute basic solution (pH 10-11 of the material with a 50% excess of commercial laundry bleach. Control the temperature by the addition rate of bleach and adjust pH if necessary. Let stand overnight. Cautiously adjust solution to pH 7. Vigorous evolution of gas may occur. Filter any solids for disposal in accordance with local, state & federal guidelines.

SECTION 14-Transport Information

None found

Reportable Quantity: N/A

SECTION 15-Regulatory Information

Concentrated sodium nitropursside is classified as a highly toxic (USA definition) and very toxic (European definition). This material is subject to SARA section 313 reporting requirements. This solution contains less than one half of a percent.

SECTION 16-Other Information

N/A

NFPA Ratings: Health:2 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....
Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500