

MATERIAL SAFETY DATA SHEET

MANUFACTURER: Manufactured for
ROSEMOUNT ANALYTICAL INC.
ADDRESS: 851 McKinley Avenue
Colombus, OH 43222

DATE REVISED: 1-27-11
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Dye (DMAB), Reagent #2 (Orange)

Synonyms:

Part Number: 180-1018-32

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	85.7	no
Methanol	67-56-1	6.0	yes
Sulfuric Acid	7664-93-9	7.4	yes
4-(Dimethylamino)Benzaldehyde	100-10-7	0.9	yes

SECTION 3-Hazards Identification

Health Rating: 3
Flammability Rating: 0
Reactivity Rating: 1

Lab Protective Equip: gloves, safety goggles, Lab Coat

SECTION 4-First Aid Measures

INHALATION: Fresh air and normal ventilation. Call a physician if difficulty in breathing persists.

INGESTION: Do not induce vomiting. Give large volumes of milk and water. Call a physician.

SKIN CONTACT: Wash thoroughly with water and soap, call a physician.

EYE CONTACT: Immediately flush with water for at least 15 minutes, call a physician.

SECTION 5-Fire Fighting Measures

Fire: Not Combustible

Explosion: None.

Fire Extinguishing Media: Use media appropriate for surrounding fire.

Special Information: Move from fire area if possible.

SECTION 6-Accidental Release Measures

Wear protective gloves, goggles and dike area, do not walk in or stand in solution. Dilute spill with more water. Neutralize by covering surface with slaked lime, add water to form a slurry. Scoop up and flush with excess water. Observe all laws.

SECTION 7-Handling and Storage

Warning! May be harmful if swallowed. May cause severe irritation to skin, eyes, respiratory tract and gastrointestinal tract. Do not get in eyes, on skin, or on clothing. Wash thoroughly after handling. Avoid breathing mist.

Material must be stored and disposed of in accordance with all local, state and federal laws.

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/E

Ventilation System: Local or mechanical ventilation. Use adequate ventilation as required.

Personal Respirators (NIOSH Approved): Not Required

Skin Protection: Rubber Gloves, lab coat (optional)

Eye Protection: Safety Goggles. Contact lenses should not be worn when working with this material. Maintain eye wash fountain and quick drench facilities in work area.

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid

Odor: Odorless

Solubility: Soluble

Specific Gravity: 1.0

pH: 1.25

Boiling Point: Approximately 215°F

Melting Point: N/A

Vapor Density (Air=1): N/A

Vapor Pressure (mm Hg): N/E

Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable

Hazardous Decomposition Products: Oxides of sulfur at very high temperatures

Hazardous Polymerization: N/E

Incompatibilities: Alkalis

Conditions to Avoid: Excessive heat

SECTION 11-Toxicological Information:

Routes of absorption: Inhalation, skin, eyes, ingestion

Threshold limit value: 1 mg. (H₂SO₄)/m³ (TWA)

Signs, symptoms and effects of exposure:

Acute: Irritation of eyes, nose, throat, and skin

Chronic: May cause burns, erode teeth, cause mouth to become sore; eye, nose & throat inflammation.

SECTION 12-Ecological Information

Environmental Fate: When released into the soil, this material may leach into groundwater. When released into the air, this material may be removed from the atmosphere to a moderate extent by wet deposition. When released into the air, this material may be removed from the atmosphere to a moderate extent by dry deposition.

Environmental Toxicity: LC50 Flounder 100 to 330mg/l/48hr aerated water/Conditions of bioassay not specified; LC50 Shrimp 80 to 90 mg/l/48 hr aerated water. This material may be toxic to aquatic life.

SECTION 13-Disposal Considerations

Material must be stored and disposed of in accordance with all local, state and federal laws. Whatever can not be saved for recovery or neutralized should be sent to a RCRA approved incinerator or disposed in a RCRA approved waste facility.

SECTION 14-Transport Information

UN2796, Sulfuric Acid solution, 8, Corrosive, PGII

SECTION 15-Regulatory Information

-----\Chemical Inventory Status - Part 1\-----

Ingredient	TSCA	EC	Japan	Australia
Sulfuric Acid (7664-93-9)	Yes	Yes	Yes	Yes
Water (7732-18-5)	Yes	Yes	Yes	Yes

-----\Chemical Inventory Status - Part 2\-----

Ingredient	Korea	--Canada--		Phil.
		DSL	NDSL	
Sulfuric Acid (7664-93-9)	Yes	Yes	No	Yes
Water (7732-18-5)	Yes	Yes	No	Yes

-----\Federal, State & International Regulations - Part 1\-----

Ingredient	-SARA 302-		-----SARA 313-----	
	RQ	TPQ	List	Chemical Catg.
Sulfuric Acid (7664-93-9)	1000	1000	Yes	No
Water (7732-18-5)	No	No	No	No

-----\Federal, State & International Regulations - Part 2\-----

Ingredient	CERCLA	-RCRA-	-TSCA-
		261.33	8 (d)
Sulfuric Acid (7664-93-9)	1000	No	No
Water (7732-18-5)	No	No	No

Chemical Weapons Convention: No TSCA 12(b): No CDTA: Yes
SARA 311/312: Acute: Yes Chronic: Yes Fire: No Pressure: No
Reactivity: No (Pure / Liquid)

Australian Hazchem Code: 2R

Poison Schedule: None allocated.

WHMIS:

This MSDS has been prepared according to the hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all of the information required by the CPR.

SECTION 16-Other Information

Label Hazard Warning:

DANGER! CORROSIVE. LIQUID AND MIST CAUSE SEVERE BURNS TO ALL BODY TISSUE. MAY BE FATAL IF SWALLOWED OR CONTACTED WITH SKIN. HARMFUL IF INHALED. AFFECTS TEETH. CANCER HAZARD. STRONG INORGANIC ACID MISTS CONTAINING SULFURIC ACID CAN CAUSE CANCER. Risk of cancer depends on duration and level of exposure.

NFPA Ratings: Health:3 Flammability:0 Reactivity:1

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....

Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500