

MATERIAL SAFETY DATA SHEET

MANUFACTURER: Manufactured for
ROSEMOUNT ANALYTICAL INC.
ADDRESS: 851 McKinley Avenue
Colombus, OH 43222

DATE REVISED: 1-27-11
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345
(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Reagent #3, Buffer (green)
Synonyms: Ammonium acetate (2.4%), Acetic acid (2.8%) in aqueous solution.
Part Number: 180-1026-32

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	94.8	no
Ammonium Acetate	631-61-8	2.4	no
Acetic Acid	64-19-7	2.8	no

SECTION 3-Hazards Identification

Health Rating: 1
Flammability Rating: 0
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles, lab coat

SECTION 4-First Aid Measures

INHALATION: Mildly irritating to mucous membranes if inhaled- remove to fresh air. Give oxygen if necessary, seek medical attention immediately.
INGESTION: Harmful if swallowed- Induce vomiting. Give plenty of water, seek medical attention.
SKIN CONTACT: Mildly irritating- Wash with soap and water. Remove contaminated clothing. Call a physician if irritation persists.
EYE CONTACT: An eye irritant- flush with water for at least 15 minutes. Seek medical attention if irritation persists.

SECTION 5-Fire Fighting Measures

Fire: Not flammable
Explosion: N/A
Fire Extinguishing Media: Fight Surrounding Fire
Special Information: N/A

SECTION 6-Accidental Release Measures

Stop the leak if possible. Flush area well with water to dilute. Absorb onto an inert material and store it in a closed container. Vent any confined spaces to outside atmosphere.

SECTION 7-Handling and Storage

Wash thoroughly after handling. Don't breath vapors. Do not get in eyes, on skin or on clothing. Keep containers closed. Store in closed containers.

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/A
Ventilation System: Normal room ventilation is adequate.
Personal Respirators (NIOSH Approved): N/A
Skin Protection: Gloves, lab coat.
Eye Protection: Use safety glasses or goggles.

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid
Odor: Mild ammonium odor
Solubility: soluable
Specific Gravity: N/E
pH: 6.8
Boiling Point: Approximately 212-214°F
Melting Point: No data
Vapor Density (Air=1): N/E
Vapor Pressure (mm Hg): N/E
Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable
Hazardous Decomposition Products: Could include CO, Carbon Dioxide, Nitrogen
Hazardous Polymerization: Will not occur
Incompatibilities: Strong oxidizers, strong acids.
Conditions to Avoid: Extreme heat/ flames

SECTION 11-Toxicological Information:

Routes of absorption: Inhalation, skin, eyes, ingestion
Threshold limit value: N/E
Signs, symptoms and effects of exposure:
 Acute: Irritation of mucous membranes
 Chronic: N/A

Acute oral toxicity (LD 50, rat): 632 mg/kg (con. Ammonium acetate)
Dermal toxicity: irritating to skin
Mildly irritating to respiratory tract

SECTION 12-Ecological Information

Environmental Fate: N/A
Environmental Toxicity: N/A

Additional information: Waste from this product could have a long-term environmental effect thus incineration may be more desirable than landfill disposal.

SECTION 13-Disposal Considerations

Comply with all Federal, State and local regulations. Almost all disposal methods are subject to regulation under RCRA. In particular, review RCRA land disposal restrictions. Under some conditions, material contaminated with this product may be landfilled at appropriately permitted facilities.

SECTION 14-Transport Information

Non-hazardous; maximum container: 5 liters

SECTION 15-Regulatory Information

US Federal Regulations:

Toxic Substances Control Act (TSCA): N/V
(29CFR1910.1200) Hazard
class - none

OSHA Hazard Communication Standard

EPA SARA Title III Section 312 (40CFR370) Hazard Class: none
EPA SARA Title III Section 313 (40CFR372) toxic chemicals above
"de minimis" level are
None

State Regulations:

Proposition 65 Substances (components) known to the State of
California to cause cancer and/or reproductive toxicity and subject
to warning and discharge requirements under the "Safe Drinking
Water and Toxic Enforcement Act of 1986":
None

SECTION 16-Other Information

N/A

NFPA Ratings: Health:1 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....
Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500