

MATERIAL SAFETY DATA SHEET

MANUFACTURER: Manufactured for
ROSEMOUNT ANALYTICAL INC.
ADDRESS: 851 McKinley Avenue
Colombus, OH 43222

DATE REVISED: 1-27-11
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Iron Color Reagent, Reagent #4 (Blue)

Synonyms:

Part Number: 180-1026-41

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	99.9952	no
3-(2-Pyridyl)-5, 6-Bis (4 Phenyl Sulfonic Acid- 1,2,4-Triazine, monosodium monohydrate	69898-45-9	0.048	no

SECTION 3-Hazards Identification

Health Rating: 1
Flammability Rating: 0
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles

SECTION 4-First Aid Measures

INHALATION: Remove to fresh air treat symptoms as appropriate.
INGESTION: Dilute with water (drink large quantities of water), do not induce vomiting.
SKIN CONTACT: Wash with soap and water and flush well with water.
EYE CONTACT: Flush well with water for at least 15 minutes. Seek medical attention if irritation persists.

SECTION 5-Fire Fighting Measures

Fire: Not flammable
Explosion: N/A
Fire Extinguishing Media: Fight Surrounding Fire
Special Information: None

SECTION 6-Accidental Release Measures

Absorb residue with inert material (ie paper towel); rinse area with water.

SECTION 7-Handling and Storage

N/A

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/A

Ventilation System: N/A
Personal Respirators (NIOSH Approved): N/A
Skin Protection: disposable gloves, safety glasses
Eye Protection: N/A

SECTION 9-Physical and Chemical Properties

Appearance: Clear, pale yellow solution
Odor: Odorless
Solubility: N/A
Specific Gravity: N/E
pH: N/E
Boiling Point: N/E
Melting Point: N/A
Vapor Density (Air=1): N/A
Vapor Pressure (mm Hg): N/E
Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable
Hazardous Decomposition Products: None
Hazardous Polymerization: N/E
Incompatibilities: None
Conditions to Avoid: None

SECTION 11-Toxicological Information:

Routes of absorption: Inhalation, ingestion
Threshold limit value: Rat, 5000 mg/kg "slightly toxic" (for pure triazine)
Signs, symptoms and effects of exposure: N/E

SECTION 12-Ecological Information

Environmental Fate: N/A
Environmental Toxicity: N/A

SECTION 13-Disposal Considerations

Material must be stored and disposed of in accordance with all local, state and federal laws.

SECTION 14-Transport Information

Reportable Quantity: N/A

SECTION 15-Regulatory Information

None Reported

SECTION 16-Other Information

Wash after handling

NFPA Ratings: Health:1 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....

Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500