

MATERIAL SAFETY DATA SHEET

MANUFACTURER: Manufactured for
ROSEMOUNT ANALYTICAL INC.
ADDRESS: 851 McKinley Avenue
Colombus, OH 43222

DATE REVISED: 1-27-11
PREPARED BY: T. Phillips

TELEPHONE: (614) 224-5345

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

SECTION 1-Product Identification

Product Name: Sodium Monitor Reagent #1
Synonyms: Reagent #1, Diisopropylamine, buffer, DIPA
Part Number: 180-1011-31

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	99.4	no
Diisopropylamine	108-18-9	0.6	yes

SECTION 3-Hazards Identification

Health Rating: 2
Flammability Rating: 0
Reactivity Rating: 2

Lab Protective Equip: Safety Goggles, Gloves, Lab apron.

SECTION 4-First Aid Measures

INHALATION: Irritating to mucous membranes. Remove to fresh air, give oxygen if necessary.

INGESTION: Harmful if swallowed. Induce vomiting. Give plenty of water. Seek Medical attention. Do not give anything orally if unconscious.

SKIN CONTACT: Mildly Corrosive to skin; can be absorbed through the skin. Wash with soap and water. Remove and wash contaminated clothing.

EYE CONTACT: An eye irritant. Flush with water for at least 15 minutes. Seek medical attention if irritation persists.

SECTION 5-Fire Fighting Measures

Fire: Not Combustible
Explosion: N/A
Fire Extinguishing Media: Fight Surrounding Fire
Special Information: Stay upwind, slight amounts of ammonia gas, oxides of nitrogen and carbon monoxide may be produced.

SECTION 6-Accidental Release Measures

Stop the leak if possible. Flush area well with water to dilute. Absorb onto an inert material and store it in a closed container. Vent any confined spaces outside atmosphere.

SECTION 7-Handling and Storage

Wash thoroughly after handling. Do not breathe vapors. Do not get in eyes, on skin or on clothing. Keep containers closed. Store in tightly closed containers.

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/A

Ventilation System: Normal room ventilation is fine

Personal Respirators (NIOSH Approved): Under normal use of product, respirator is not required.

Skin Protection: gloves

Eye Protection: Use safety glasses or goggles.

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid

Odor: very slight ammonia

Solubility: Soluble

Specific Gravity: 0.996-0.998

pH: 4-7

Boiling Point: Approximately 100-101°C

Melting Point: N/A

Vapor Density (Air=1): N/A

Vapor Pressure (mm Hg): N/E

Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable

Hazardous Decomposition Products: Could include Carbon monoxide, carbon dioxide, nitrogen oxides.

Hazardous Polymerization: Will not occur.

Incompatibilities: Strong Acids, Strong oxidizers.

Conditions to Avoid: Extreme heat/flames.

SECTION 11-Toxicological Information:

Acute Oral Toxicity (LD 50, Rat): 700 mg/kg (for concentrated DIPA)

Acute Dermal Toxicity (LD 50, Rabbit): >1000 mg/kg (for con. DIPA)

Acute Inhalation Toxicity ((LC 50, Rat): 4.8 mg/l/2 hr. (for con. DIPA)

Irritation Effects Data: Corrosive to the skin of a rabbit (for con. DIPA)

Routes of absorption: Inhalation, skin, eyes, ingestion

Threshold limit value: N/E

Signs, symptoms and effects of exposure:

Acute: N/A

Chronic: N/A

SECTION 12-Ecological Information

Environmental Fate: N/A

Environmental Toxicity: Waste from this product could have a long-term environmental effect, thus incineration may be more desirable than landfill disposal.

SECTION 13-Disposal Considerations

Material must be stored and disposed of in accordance with all local, state and federal laws.

SECTION 14-Transport Information

DOT Non-bulk Shipping Name: Diisopropylamine// 2 // UN3267 // PG III

Mildly Corrosive Liquid, Basic, Organic,
NOS [1.0-2.0] UN3267

SECTION 15-Regulatory Information

US Federal Regulations:

Toxic Substances Control Act (TSCA):

OSHA Hazard Communication Standard (29CFR1910.1200) Hazard class - mildly corrosive, mildly toxic by continued inhalation

EPA SARA Title III Section 312 (40CFR370) Hazard Class: Possible health hazard through long term, continual contact.

EPA SARA Title III Section 313 (40CFR372) toxic chemicals above "de minimis" level are

None

State Regulations:

Proposition 65 Substances (components) known to the State of California to cause cancer and/or reproductive toxicity and subject to warning and discharge requirements under the "Safe Drinking Water and Toxic Enforcement Act of 1986":

None

New Jersey Trade Secret Registry Number(s):

None

SECTION 16-Other Information

Canada:

DSL: Included on inventory

WHMIS Hazard Classification: Class Division Class Division
Class

WHMIS Trade Secret Registry Number(s): None

WHMIS Hazardous Ingredients: None

WHMIS Symbols: Test tube/hand, Skull & Crossbones

European Economic Community (EEC):

EINECS Master Inventory: Included on inventory as concentrated material. Maximum concentration is 0.6 %.

EEC SYMBOL: Irritant

EEC Risk (R) Phrases: Irritating to eyes, respiratory system and skin.

EEC Safety Phrases: Keep container in a ventilated area.

Legend:

N/A - Not Applicable

N/D - Not Determined

N/V - Not Available

w/w - weight/weight

w/v - weight/volume

v/v - volume/volume

NFPA Ratings: Health:2 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....

Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500