

**MATERIAL SAFETY DATA SHEET**

MANUFACTURER: ROSEMOUNT ANALYTICAL INC.  
ADDRESS: 2400 Barranca Parkway  
Irvine, CA 92606

DATE REVISED: 3-28-11  
PREPARED BY: T. Phillips

TELEPHONE: (949) 757-8500

(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

**SECTION 1-Product Identification**

**Product Name: Oil Resistant Soaking Solution**

**Synonyms:**

**Part Number: 9210433**

**SECTION 2-Composition/Information on Ingredients**

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	72.1	no
Potassium Chloride	7447-40-7	26.0	no
Silver Chloride	7783-90-6	0.2	no
Non-hazardous proprietary ingredient		1.7	no

**SECTION 3-Hazards Identification**

Health Rating: 0  
Flammability Rating: 0  
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles

**SECTION 4-First Aid Measures**

INHALATION: No known effects, remove to fresh air if necessary.  
INGESTION: Dilute with water. Seek medical attention. Do NOT induce vomiting unless directed to do so by medical personnel.  
SKIN CONTACT: Wash with soap and water for 15 minutes.  
EYE CONTACT: Flush with water for at least 15 minutes.

**SECTION 5-Fire Fighting Measures**

**Fire: Non-flammable**  
**Explosion: N/A**  
**Fire Extinguishing Media: Fight Surrounding Fire**  
**Special Information: N/A**

**SECTION 6-Accidental Release Measures**

Rinse area with water; mop. Dispose in accordance with federal, state and local regulations.

**SECTION 7-Handling and Storage**

Keep in a tightly closed container, stored in a cool, dry, ventilated area.

**SECTION 8-Exposure Controls/Personal Protection**

**Airborne Exposure Limits:** N/E

**Ventilation System:** Normal room ventilation is generally adequate.

**Personal Respirators (NIOSH Approved):** None required.

**Skin Protection:** Gloves, lab coat.

**Eye Protection:** Use safety glasses or goggles.

**SECTION 9-Physical and Chemical Properties**

**Appearance:** Clear, colorless liquid sloution

**Odor:** Odorless

**Solubility:** Miscible in water

**Specific Gravity:** 1.00

**pH:** approximately 7

**Boiling Point:** Approximately 102°C

**Melting Point:** -7.5°C

**Vapor Density (Air=1):** N/A

**Vapor Pressure (mm Hg):** N/E

**Evaporation Rate (BuAc=1):** N/E

**SECTION 10-Stability and Reactivity**

**Stability:** Stable

**Hazardous Decomposition Products:** Emits toxic fumes of chlorine and potassium oxide when heated to decomposition.

**Hazardous Polymerization:** Will not occur

**Incompatibilities:** Iron, cement, BrF3, sulfuric acid and potassium permanganate.

**Conditions to Avoid:** Heat, incompatibles.

**SECTION 11-Toxicological Information:**

**Potassium chloride:** Oral rat LD50: 2600 mg/kg. Irritation eye rabbit (std Draize): 500 mg/24H mild. Oral human

LDlo: 20 mg/kg. Investigated as a mutagen.

-----\Cancer Lists\-----

Ingredient	---NTP Carcinogen---		IARC Category
	Known	Anticipated	
<b>Potassium Chloride</b> (7447-40-7)	No	No	None

**SECTION 12-Ecological Information**

**Environmental Fate:** N/A

**Environmental Toxicity:** N/A

**SECTION 13-Disposal Considerations**

Material must be stored and disposed of in accordance with all local, state and federal laws.

**SECTION 14-Transport Information**

Not regulated

**SECTION 15-Regulatory Information**

```

-----\Chemical Inventory Status - Part 1\-----
Ingredient                                     TSCA  EC   Japan  Australia
-----
Potassium Chloride (7447-40-7)                Yes  Yes   Yes    Yes

```

```

-----\Chemical Inventory Status - Part 2\-----
Ingredient                                     Korea  DSL   NDSL   Phil.
-----
Potassium Chloride (7447-40-7)                Yes   Yes   No     Yes

```

```

-----\Federal, State & International Regulations - Part 1\-----
Ingredient                                     -SARA 302-  -SARA 313-
RQ      TPQ      List  Chemical Catg.
-----
Potassium Chloride (7447-40-7)                No     No     No     No

```

```

-----\Federal, State & International Regulations - Part 2\-----
Ingredient                                     CERCLA  -RCRA-  -TSCA-
261.33  8(d)
-----
Potassium Chloride (7447-40-7)                No     No     No

```

Chemical Weapons Convention: No      TSCA 12(b): No      CDTA: No  
SARA 311/312: Acute: Yes      Chronic: No      Fire: No      Pressure: No  
Reactivity: No      (Pure / Liquid)

**Australian Hazchem Code:** None allocated.

**Poison Schedule:** None allocated.

**WHMIS:**

This **MSDS** has been prepared according to the hazard criteria of the Controlled Products Regulations (CPR) and the **MSDS** contains all of the information required by the CPR.

**SECTION 16-Other Information**

N/A

**NFPA Ratings:**      Health:0      Flammability:0      Reactivity:0

\*\*\*\*\*

**Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.**

Prepared by: Rosemount Analytical Inc.

Phone Number: (949) 757-8500