

MATERIAL SAFETY DATA SHEET

PART NUMBER: 905-3008
IDENTITY: pH 7.42 BUFFER POWDER
MANUFACTURER: ROSEMOUNT ANALYTICAL INC.
ADDRESS: 2400 BARRANCA PARKWAY
IRVINE, CA 92606
TELEPHONE: 949/757-8500
(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

DATE REVISED: 01/26/11
PREPARED BY: R. MORRISON
REVISED BY: T. PHILLIPS

SECTION 1--MATERIAL IDENTIFICATION AND INFORMATION

COMPONENTS	%	OSHA PEL	ACGIH TLV	OTHER LIMIT RECOMMENDED
SODIUM PHOSPHATE, DIBASIC, ANYDROUS (CAS # 7558-79-4)	78%			
POTASSIUM PHOSPHATE MONOBASIC (CAS # 7778-77-0)	22%			
NON-HAZARDOUS INGREDIENTS TOTAL	100			

No health hazard or other information is available for the solution of the mixture. The following sections are based on information obtained from <http://www.jtbaker.com/msds/englishhtml/S4760.htm> <http://www.jtbaker.com/msds/englishhtml/P6038.htm> and our best scientific understanding of the solution.

SECTION 2--PHYSICAL/CHEMICAL CHARACTERISTICS

BOILING POINT	100°C
SPECIFIC GRAVITY (H ₂ O = 1)	1.0
VAPOR PRESSURE (mm Hg/TEMPERATURE)	24 mmHg @ 25°C
MELTING POINT	N/A
VAPOR DENSITY (AIR = 1)	N/A
EVAPORATION RATE (= 1)	N/A
SOLUBILITY IN WATER	COMPLETE
WATER REACTIVE	N/A
APPEARANCE AND ODOR	ODORLESS SOLUTION

SECTION 3--FIRE AND EXPLOSION HAZARD DATA

FLASH POINT AND METHOD USE	N/A
AUTO IGNITION TEMPERATURE	N/A
FLAMMABILITY LIMITS IN AIR BY VOLUME	N/A
LEL	N/A
UEL	N/A
EXTINGUISHER MEDIA	N/A
SPECIAL FIRE FIGHTING PROCEDURE	N/A

UNUSUAL FIRE AND EXPLOSION HAZARD: NOT FLAMMABLE OR EXPLOSIVE

SECTION 4--REACTIVITY HAZARD DATA

STABILITY	STABLE <u>X</u>	UNSTABLE <u> </u>
CONDITIONS TO AVOID:	NONE	
IN COMPATIBILITY MATERIALS TO AVOID:	NONE	
HAZARDOUS DECOMPOSITION PRODUCTS:	NONE	

HAZARDOUS POLYMERIZATION: MAY OCCUR__ WILL NOT OCCUR_X

HAZARDOUS POLYMERIZATION CONDITIONS TO AVOID: N/A

SECTION 5--HEALTH HAZARD DATA 905-3008

PRIMARY ROUTES OF ENTRY: INHALATION__ SKIN ABSORPTION__
INGESTION__ NOT HAZARDOUS_X

CARCINOGEN LISTED: NPT__ IRAC__ OSHA__ NOT LISTED_X

HEALTH HAZARDS

ACUTE: UNKNOWN

CHRONIC: UNKNOWN

SIGNS AND SYMPTOMS OF EXPOSURE: UNKNOWN

MEDICAL CONDITIONS GENERALLY AGGRAVATED BY EXPOSURE: UNKNOWN

EMERGENCY FIRST AID PROCEDURES:

EYE CONTACT: FLUSH WITH WATER 15 MINUTES

SKIN CONTACT: WASH WITH SOAP AND WATER

INHALATION: REMOVE TO FRESH AIR IF NECESSARY

INGESTION: DILUTE WITH WATER. SEEK MEDICAL ASSISTANCE IF NECESSARY.

SECTION 6--CONTROL AND PROTECTIVE MEASURES

RESPIRATORY PROTECTION (SPECIFY TYPE): NIOSHA/MSHA APPROVED RESPIRATOR

PROTECTIVE GLOVES: YES

EYE PROTECTION: YES

VENTILATION TO BE USED

LOCAL EXHAUST:

MECHANICAL (GENERAL): YES

SPECIAL OTHER (SPECIFY): N/A

PROTECTIVE CLOTHING AND EQUIPMENT: LAB COAT/APRON

HYGIENIC WORK PRACTICES: WASH HANDS AFTER HANDLING

SECTION 7--PRECAUTIONS FOR SAFE HANDLING AND USE/LEAK PROCEDURES

STEPS TO BE TAKEN IF MATERIAL IS SPILLED OR RELEASED: RINSE AREA WITH WATER AND MOP

WASTE DISPOSAL METHODS: DISPOSE OF IN ACCORDANCE WITH LOCAL REGULATIONS

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE: STORE IN A PLASTIC CONTAINER, ROOM TEMP.

OTHER PRECAUTIONS AND/OR SPECIAL HAZARDS:

RATING:

HEALTH_1

FLAMMABILITY_0

REACTIVITY_1

SPECIFIC NONE