

MATERIAL SAFETY DATA SHEET

PART NUMBER: 9210371
IDENTITY: 499Acl-03 Fill Solution
MANUFACTURER: ROSEMOUNT ANALYTICAL INC.
ADDRESS: 2400 BARRANCA PARKWAY
IRVINE, CA 92606
TELEPHONE: 949/757-8500
(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

DATE REVISED: 01/26/11
PREPARED BY: J. Garretson
REVISED BY: T. PHILLIPS

SECTION 1--MATERIAL IDENTIFICATION AND INFORMATION

COMPONENTS	CAS#	%	OSHA PEL	ACGIH TLV	OTHER LIMIT RECOMMENDED
POTASSIUM BROMIDE	7758-02-3	11.9			
SODIUM ACETATE	6131-90-4	10.0			
ACETIC ACID	64-19-7	21.2			
NON-HAZARDOUS INGREDIENTS		56.9			
TOTAL		100			

No health hazard or other information is available for the solution of the mixture. The following sections are based on information obtained from <http://www.jtbaker.com/msds/englishhtml/P5587.htm> <http://www.jtbaker.com/msds/englishhtml/S2666.htm> <http://www.jtbaker.com/msds/englishhtml/A0323.htm> and our best scientific understanding of the solution.

SECTION 2--PHYSICAL/CHEMICAL CHARACTERISTICS

BOILING POINT	100°C
SPECIFIC GRAVITY (H ₂ O = 1)	1.0
VAPOR PRESSURE (mm Hg/TEMPERATURE)	24 mmHG @ 25°C
MELTING POINT	N/A
VAPOR DENSITY (AIR = 1)	N/A
EVAPORATION RATE (= 1)	N/A
SOLUBILITY IN WATER	COMPLETE
WATER REACTIVE	N/A
APPEARANCE AND ODOR	COLORLESS, VINEGAR ODOR

SECTION 3--FIRE AND EXPLOSION HAZARD DATA

FLASH POINT AND METHOD USE	N/A
AUTO IGNITION TEMPERATURE	N/A
FLAMMABILITY LIMITS IN AIR BY VOLUME	N/A
LEL	N/A
UEL	N/A
EXTINGUISHER MEDIA	N/A
SPECIAL FIRE FIGHTING PROCEDURE	N/A

UNUSUAL FIRE AND EXPLOSION HAZARD: THIS IS AN AQUEOUS SOLUTION WHICH IS NOT FLAMMABLE NOR EXPLOSIVE.

SECTION 4--REACTIVITY HAZARD DATA

STABILITY	STABLE <u>X</u>	UNSTABLE <u> </u>
CONDITIONS TO AVOID:	NONE	
INCOMPATIBILITY MATERIALS TO AVOID:	NONE	
HAZARDOUS DECOMPOSITION PRODUCTS:	NONE	
HAZARDOUS POLYMERIZATION:	MAY OCCUR <u> </u>	WILL NOT OCCUR <u>X</u>
HAZARDOUS POLYMERIZATION CONDITIONS TO AVOID:	DOES NOT POLYMERIZE	

SECTION 5--HEALTH HAZARD DATA 9210371

PRIMARY ROUTES OF ENTRY: INHALATION__ SKIN ABSORPTION__
 INGESTION X NOT HAZARDOUS__

CARCINOGEN LISTED: NTP__ IRAC__ OSHA__ NOT LISTED X

HEALTH HAZARDS

ACUTE: MAY CAUSE IRRITATION. LARGE DOSES MAY PRODUCE GASTROINTESTINAL DISTURBANCE/IRRITATION.
CHRONIC: UNKNOWN

SIGNS AND SYMPTOMS OF EXPOSURE:

MEDICAL CONDITIONS GENERALLY AGGRAVATED BY EXPOSURE: IMPAIRED KIDNEY FUNCTION

EMERGENCY FIRST AID PROCEDURES:

EYE CONTACT: FLUSH WITH WATER 15 MINUTES.

SKIN CONTACT: WASH WITH SOAP AND WATER.

INHALATION: REMOVE TO FRESH AIR IF NECESSARY.

INGESTION: DILUTE WITH SEVERAL GLASSES OF WATER. SEEK MEDICAL ASSISTANCE IF NECESSARY.

SECTION 6--CONTROL AND PROTECTIVE MEASURES

RESPIRATORY PROTECTION (SPECIFY TYPE): NIOSHA/MSHA APPROVED RESPIRATOR

PROTECTIVE GLOVES: YES

EYE PROTECTION: YES

VENTILATION TO BE USED

LOCAL EXHAUST:

MECHANICAL (GENERAL): X

SPECIAL OTHER (SPECIFY): N/A

PROTECTIVE CLOTHING AND EQUIPMENT: LAB APRON/COAT

HYGIENIC WORK PRACTICES: WASH HANDS AFTER HANDLING.

SECTION 7--PRECAUTIONS FOR SAFE HANDLING AND USE/LEAK PROCEDURES

STEPS TO BE TAKEN IF MATERIAL IS SPILLED OR RELEASED: RINSE AREA WITH WATER. MOP.

WASTE DISPOSAL METHODS: DISPOSE IN ACCORDANCE WITH FEDERAL, STATE AND LOCAL REGULATIONS.

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE: STORE IN DRY, ROOM TEMPERATURE AREA.

OTHER PRECAUTIONS AND/OR SPECIAL HAZARDS:

RATING:

HEALTH 3 FLAMMABILITY 2 REACTIVITY 2 SPECIFIC___Contact=4