

MATERIAL SAFETY DATA SHEET

PART NUMBER: 05010781899, 05010797875
REFERENCE: SS-6, SS-6A
IDENTITY: CONDUCTIVITY SOLUTION
MANUFACTURER: ROSEMOUNT ANALYTICAL INC.
ADDRESS: 2400 BARRANCA PARKWAY
IRVINE, CA 92606
TELEPHONE: 949/757-8500
(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

DATE REVISED: 02/07/13
PREPARED BY: R. MORRISON
REVISED BY: T. PHILLIPS

SECTION 1--MATERIAL IDENTIFICATION AND INFORMATION

COMPONENTS	CAS#	%	OSHA PEL	ACGIH TLV	OTHER LIMIT RECOMMENDED
POTASSIUM CHLORIDE (7447-40-7)		<.1			
NON-HAZARDOUS INGREDIENTS		100			
TOTAL		100			

No health hazard or other information is available for the solution of the mixture. The following sections are based on information obtained from <http://www.jtbaker.com/msds/englishhtml/P5631.htm> and our best scientific understanding of the solution.

SECTION 2--PHYSICAL/CHEMICAL CHARACTERISTICS

BOILING POINT	100°C
SPECIFIC GRAVITY (H ₂ O = 1)	1.0
VAPOR PRESSURE (mm Hg/TEMPERATURE)	24 mmHg @ 25°C
MELTING POINT	N/A
VAPOR DENSITY (AIR = 1)	N/A
EVAPORATION RATE (= 1)	N/A
SOLUBILITY IN WATER	COMPLETE
WATER REACTIVE	N/A
APPEARANCE AND ODOR	COLORLESS, ODORLESS SOLUTION

SECTION 3--FIRE AND EXPLOSION HAZARD DATA

FLASH POINT AND METHOD USE	N/A
AUTO IGNITION TEMPERATURE	N/A
FLAMMABILITY LIMITS IN AIR BY VOLUME	N/A
LEL	N/A
UEL	N/A
EXTINGUISHER MEDIA	N/A
SPECIAL FIRE FIGHTING PROCEDURE	N/A

UNUSUAL FIRE AND EXPLOSION HAZARD: THIS IS AN AQUEOUS SOLUTION WHICH IS NOT FLAMMABLE NOR EXPLOSIVE.

SECTION 4--REACTIVITY HAZARD DATA

STABILITY STABLE X UNSTABLE __
CONDITIONS TO AVOID:

INCOMPATIBILITY MATERIALS TO AVOID: NONE

HAZARDOUS DECOMPOSITION PRODUCTS: NONE
HAZARDOUS POLYMERIZATION: MAY OCCUR__ WILL NOT OCCUR X
HAZARDOUS POLYMERIZATION CONDITIONS TO AVOID: DOES NOT POLYMERIZE

SECTION 5--HEALTH HAZARD DATA

SS-6, SS-6A

PRIMARY ROUTES OF ENTRY: INHALATION__ SKIN ABSORPTION__
 INGESTION__ NOT HAZARDOUS XCARCINOGEN LISTED: NPT__ IRAC__ OSHA__ NOT LISTED X**HEALTH HAZARDS**ACUTE: N/A
CHRONIC: N/A

SIGNS AND SYMPTOMS OF EXPOSURE: UNKNOWN

MEDICAL CONDITIONS GENERALLY AGGRAVATED BY EXPOSURE: UNKNOWN

EMERGENCY FIRST AID PROCEDURES:

EYE CONTACT: FLUSH WITH WATER A MINIMUM 15 MINUTES.

SKIN CONTACT: WASH WITH SOAP AND WATER.

INHALATION: REMOVE TO FRESH AIR IF NECESSARY.

INGESTION: SILUTE WITH SEVERAL GLASSES OF WATER. SEEK MEDICAL ATTENTION.

SECTION 6--CONTROL AND PROTECTIVE MEASURES

RESPIRATORY PROTECTION (SPECIFY TYPE): NIOSHA/MSHA APPROVED RESPIRATOR

PROTECTIVE GLOVES: YES

EYE PROTECTION: YES

VENTILATION TO BE USED**LOCAL EXHAUST:**

MECHANICAL (GENERAL): X

SPECIAL OTHER (SPECIFY): N/A

PROTECTIVE CLOTHING AND EQUIPMENT: LAB COAT/APRON

HYGIENIC WORK PRACTICES: WASH HANDS AFTER HANDLING.

SECTION 7--PRECAUTIONS FOR SAFE HANDLING AND USE/LEAK PROCEDURES

STEPS TO BE TAKEN IF MATERIAL IS SPILLED OR RELEASED: RINSE AREA WITH WATER. MOP.

WASTE DISPOSAL METHODS: DISPOSE IN ACCORDANCE WITH FEDERAL, STATE AND LOCAL REGULATIONS.

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE: STORE IN PLASTIC CONTAINER AT ROOM TEMPERATURE.

OTHER PRECAUTIONS AND/OR SPECIAL HAZARDS:**RATING:**HEALTH 0 FLAMMABILITY 0 REACTIVITY 0 SPECIFIC__