

MATERIAL SAFETY DATA SHEET

MANUFACTURER: ROSEMOUNT ANALYTICAL INC.
ADDRESS: 2400 BARRANCA PARKWAY
IRVINE, CA 92606
TELEPHONE: 949/757-8500
(1-800-424-9300 24 Hr. CHEMTREC/ CODE: RANA)

DATE REVISED: 7-29-13
PREPARED BY: T. Phillips

SECTION 1-Product Identification

Product Name: 2.5M Saturated KCl- Solution (Sensor Booting Solution)

Synonyms:

Part Number: 9210098

SECTION 2-Composition/Information on Ingredients

Ingredient(s)	CAS #	Percent	Hazardous
Water	7732-18-5	81.5	no
Potassium Chloride	7747-40-7	18.5	no

SECTION 3-Hazards Identification

Health Rating: 1
Flammability Rating: 0
Reactivity Rating: 0

Lab Protective Equip: gloves, safety goggles

SECTION 4-First Aid Measures

INHALATION: No known effects, remove to fresh air if necessary.

INGESTION: Dilute with water. Seek medical attention. Do NOT induce vomiting unless directed to do so by medical personnel.

SKIN CONTACT: Wash with soap and water for 15 minutes.

EYE CONTACT: Flush with water for at least 15 minutes.

SECTION 5-Fire Fighting Measures

Fire: Non-flammable

Explosion: N/A

Fire Extinguishing Media: Fight Surrounding Fire

Special Information: N/A

SECTION 6-Accidental Release Measures Rinse area with water; mop. Dispose in accordance with federal, state and local regulations.

SECTION 7-Handling and Storage Keep in a tightly closed container, stored in a cool, dry, ventilated area.

SECTION 8-Exposure Controls/Personal Protection

Airborne Exposure Limits: N/E

Ventilation System: Normal room ventilation is generally adequate.

Personal Respirators (NIOSH Approved): None required.

Skin Protection: Gloves, lab coat.

Eye Protection: Use safety glasses or goggles.

SECTION 9-Physical and Chemical Properties

Appearance: Clear, colorless liquid slolution

Odor: Odorless

Solubility: Miscible in water

Specific Gravity: 1.00

pH: approximately 7

Boiling Point: Approximately 102°C

Melting Point: -7.5°C

Vapor Density (Air=1): N/A

Vapor Pressure (mm Hg): N/E

Evaporation Rate (BuAc=1): N/E

SECTION 10-Stability and Reactivity

Stability: Stable

Hazardous Decomposition Products: Emits toxic fumes of chlorine and potassium oxide when heated to decomposition.

Hazardous Polymerization: Will not occur

Incompatibilities: Iron, cement, BrF3, sulfuric acid and potassium permanganate.

Conditions to Avoid: Heat, incompatibles.

SECTION 11-Toxicological Information

Potassium chloride: Oral rat LD50: 2600 mg/kg. Irritation eye rabbit (std Draize): 500 mg/24H mild. Oral human LDlo: 20 mg/kg. Investigated as a mutagen.

-----\Cancer Lists\-----

Ingredient ---NTP Carcinogen---
Known Anticipated IARC Category

Potassium Chloride (7447-40-7) No No None

SECTION 12-Ecological Information

Environmental Fate: N/A

Environmental Toxicity: N/A

SECTION 13-Disposal Considerations

Material must be stored and disposed of in accordance with all local, state and federal laws.

SECTION 14-Transport Information

Not regulated

SECTION 15-Regulatory Information

-----\Chemical Inventory Status - Part 1\-----				
Ingredient	TSCA	EC	Japan	Australia
Potassium Chloride (7447-40-7)	Yes	Yes	Yes	Yes

-----\Chemical Inventory Status - Part 2\-----				
Ingredient	Korea	DSL	NDSL	Phil. --Canada--
Potassium Chloride (7447-40-7)	Yes	Yes	No	Yes

-----\Federal, State & International Regulations - Part 1\-----				
Ingredient	-SARA 302- RQ	TPQ	-----SARA 313----- List Chemical Catg.	
Potassium Chloride (7447-40-7)	No	No	No	No

-----\Federal, State & International Regulations - Part 2\-----			
Ingredient	CERCLA	-RCRA- 261.33	-TSCA 8(d)
Potassium Chloride (7447-40-7)	No	No	No

Chemical Weapons Convention: No TSCA 12(b): No CDTA: No
SARA 311/312: Acute: Yes Chronic: No Fire: No Pressure: No
Reactivity: No (Pure / Liquid)

Australian Hazchem Code: None allocated.

Poison Schedule: None allocated.

WHMIS:

This **MSDS** has been prepared according to the hazard criteria of the Controlled Products Regulations (CPR) and the **MSDS** contains all of the information required by the CPR.

SECTION 16-Other Information

NFPA Ratings: Health:1 Flammability:0 Reactivity:0

Rosemount Analytical Inc., a Division of Emerson Process Management, provides the information contained herein in good faith but makes no representation as to its comprehensiveness or accuracy. This document is intended only as a guide to the appropriate precautionary handling of the material by a properly trained person using this product. Individuals receiving the information must exercise their independent judgment in determining its appropriateness for a particular purpose. ROSEMOUNT ANALYTICAL INC. MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE INFORMATION SET FORTH HEREIN OR THE PRODUCT TO WHICH THE INFORMATION REFERS. ACCORDINGLY, ROSEMOUNT ANALYTICAL INC. WILL NOT BE RESPONSIBLE FOR DAMAGES RESULTING FROM USE OF OR RELIANCE UPON THIS INFORMATION.

.....

Prepared by: Rosemount Analytical Inc.
Phone Number: (949) 757-8500