



DEPENDING ON TURBULENCE IN TANK AND MOUNTING ANGLE THE PROBE MAY NEED TO BE ANCHORED OR SUPPORTED.

ENSURE MID PROBE HAS NO CONTACT WITH WALL.

1. P/T-RATING FOR FLANGE; SEE REF. MANUAL.

04	GASKET	I	ACC. TO BSP-G THREAD STD.	CUSTOMER
03	GASKET	I	SOFT GASKET T=MIN 1.6 (ANSI B16.5/1c, EN1514-1/1BC). SEE NOTE 1.	CUSTOMER
02	SCREW/NUT/WASHER	-	ACC. TO FLANGE STD. SEE NOTE 1.	CUSTOMER
01	FLANGE	I	DIM. ACC. TO ANSI B 16.5/EN 1092-1. OTHER ON REQUEST. P/T RATING. SEE NOTE 1.	RMT
POS	ITEM DESCRIPTION	QTY	REMARK	SUPPLIER

ISSUED BY	MEK	PRODUCT CODE	FILE	INSTALLATION DRAWING TITLE
EMe-HW-C	0909	5300	PRO/E	MECHANICAL INSTALLATION DWG
APPROVED BY	MEK	(ORIGINAL DWG. NO.)	SCALE	RIGID TWIN LEAD
EMe-HF	0909	9240030-995	-	
			T-ST ANGLE	DOC TYPE DWG NO
			2	9240030-995
			ISSUE	SHEET
			02	1/1

ROSEMOUNT

THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN

FOR MORE INFO SEE REFERENCE MANUAL