

Paine™ 211-37-520 Series Pressure Transducer

mV/V, Downhole, HP/HT, +204 °C, Ranges to 30,000 PSIA (2,068 BAR)



The Paine 11-37-520 Series is our High Pressure/High Temperature (HP/HT) combination transducer designed for 400 °F (204 °C) offshore oil, gas, and power industry requirements. The Paine 211-37-520 Series, based on its small size, all-welded construction, and ability to perform in corrosive environments, is the best solution for new downhole tool and process equipment design when temperatures are going to reach 400 °F (204 °C).

Many new exciting industries are now using the Paine 211-37-520 Series because of its rugged construction, accuracy, stability, and long term repeatability.

Solutions

- High pressure and high temperature measurement
- All-welded, sealed construction
- Harsh/extreme environment ready

Potential applications

- Wireline and rotary steering tools
- Hydraulic flow pressure and temperature monitoring
- Oil and gas exploration and production
- MWD, PWD, and LWD tools

Features

- **Full Scale (F.S.) sensitivity:** 2.6 mV/V nominal
- **Total error band (non-linearity, hysteresis, and thermal effects):** ±0.75% F.S.
- **Output:** mV/V
- **Operating temperature:** -40 to +400 °F (-40 to +204 °C)
- **Pressure range:** 0-5,000 to 0-30,000 psia (344 to 2,068 bar)
- **Operating media:** Compatible with alloy UNS NO7718 solution annealed and aged to a minimum hardness of 40HRC.
- **Pressure fitting:** Per MS33656-E3

Specifications

Calibration: Calibration certificates are supplied with each unit and available online.

Performance

Full Scale (F.S.) sensitivity: 2.6 mV/V nominal

Total error band (non-linearity, hysteresis, and thermal effects): ±0.75% F.S.

Non-linearity and hysteresis combined: ±0.150% of F.S. maximum (BSLM)

Output at zero pressure: 0 ± 2.0% F.S.

Platinum resistance temperature detector (RTD): 0 °C, 1000 Ω ± 0.06% Ω to IEC 751, Class A, Alpha = 0.00385 nominal

Sustained pressure/temperature stability: When pressurized to F.S. pressure at 350 °F, F.S. output will not shift more than 0.05% F.S. in 14 days nor more than ± 0.07% F.S. in 60 days.

Compensated: This sensor compensated for temperature effects on signal.

Environmental

Environmental: Error due to combined effect of shock, vibration and acceleration shall be less than 0.01% of F.S.O. per G.

Operating temperature range: -40 to +400 °F (-40 to +204 °C)

Compensated temperature range: +75 to +350 °F (+23 to +176 °C)

Contents

Specifications 2 Dimensional Drawings 4

Mechanical

Pressure range: Contact factory for additional pressure ranges.

Table 1. Pressure Table

| Standard part number | Pressure range PSIA (BAR) | Proof pressure PSIA (BAR) | Burst pressure PSIA (BAR) | Replaceable seal part number |
|----------------------|---------------------------|---------------------------|---------------------------|------------------------------|
| 211-37-520-01 | 0–5,000 (0–344) | 7,500 (517) | 10,000 (689) | 247-99-250-01 |
| 211-37-520-02 | 0–10,000 (0–689) | 15,000 (1,034) | 20,000 (1,378) | 247-99-250-01 |
| 211-37-520-03 | 0–15,000 (0–1034) | 18,750 (1,292) | 22,500 (1,551) | 247-99-250-01 |
| 211-37-520-04 | 0–20,000 (0–1378) | 25,000 (1,723) | 30,000 (2,068) | 247-99-250-01 |
| 211-37-520-05 | 0–22,500 (0–1551) | 28,125 (1,939) | 30,000 (2,068) | 247-99-250-01 |
| 211-37-520-06 | 0–25,000 (0–1723) | 31,250 (2,154) | 33,000 (2,275) | 247-99-250-01 |
| 211-37-520-07 | 0–30,000 (0–2068) | 37,500 (2,585) | 40,000 (2,757) | 247-99-250-02 |

External case pressure: Up to 20,000 psi (1,378 bar)

Pressure media: Any compatible with alloy UNS NO7718 solution annealed and aged to a minimum hardness of 40HRC.

Pressure fitting: Per MS33656-E3

Installation information: Mount on port using annealed alloy 600 replaceable seal. Thermal coefficient of the mounting expansion should not exceed 8.3×10^{-6} in/in °F for operation above 100 °C.

Recommended installation torque: 125–150 in-lb (14–17 Nm)

Electrical

Excitation: 1 to 20 VDC (10 VDC nominal)

Input resistance: $1500 \pm 300 \Omega$


Output resistance: $1500 \pm 150 \Omega$

Insulation resistance: All conductors together to case, 10 G Ω minimum at 50 VDC and +77 °F (+25 °C)

Electrical connections: High temperature solderable pins

Dimensional Drawings

Figure 1. Paine 211-37-520 Series



| Connections | |
|-------------|--------------|
| PIN | Function |
| A | + Excitation |
| B | + Signal |
| C | - Signal |
| D | - Excitation |
| E | R.T.D. |
| F | R.T.D. |

A-F. See connections table
 G. Fitting end per MS33656-E3
 Dimensions are shown in inches.


This page is intentionally left blank.


Rosemount Specialty Product LLC


Emerson Automation Solutions


5545 Nelpar Drive

East Wenatchee, WA 98822, USA

 +1 509 881 2100


 +1 509 881 2115


 Paine.Products@Emerson.com

 [Linkedin.com/company/Emerson-Automation-Solutions](https://www.linkedin.com/company/Emerson-Automation-Solutions)

 [Twitter.com/Rosemount_News](https://twitter.com/Rosemount_News)

 [Facebook.com/Rosemount](https://www.facebook.com/Rosemount)

 [Youtube.com/user/RosemountMeasurement](https://www.youtube.com/user/RosemountMeasurement)

 [Google.com/+RosemountMeasurement](https://www.google.com/+RosemountMeasurement)

Standard Terms and Conditions of Sale can be found on the [Terms and Conditions of Sale page](#).

The Emerson logo is a trademark and service mark of Emerson Electric Co. The Paine brand and Paine logotype are trademarks of Emerson Electric Co. All other marks are the property of their respective owners.
© 2017 Emerson. All rights reserved.