



TABLE 1

FLANGE SIZE DN / ANSI	ANTENNA PLATE (06) PIPE FLANGE (07) OD $\phi$ (mm)
80 / 3"	$\phi 130$
100 / 4"	$\phi 154$
150 / 6"	$\phi 215$
200 / 8"	$\phi 265$

① PRESSURE AND TEMP RATING: FOR PRESSURE APPLICATIONS, CALCULATION OF FLANGE THICKNESS HAS TO BE DONE WITH RESPECT TO FLANGE MATERIAL, GASKET TYPE AND BOLTING. MAX ALLOWABLE RATING FOR ANTENNA TANK SEAL ARE DEPENDING ON THE SEAL TYPE AND O-RING SELECTION.

POS	ITEM DESCRIPTION	QTY	REMARK	SUPPLIER
08	GASKET	2	SEE NOTE 1.	CUSTOMER
07	PIPE FLANGE	1	DIMENSIONS, SEE TABLE 1.	RTR
06	ANTENNA PLATE	1	DIMENSIONS, SEE TABLE 1.	RTR
05	BOLTING	1	ACC TO FLANGE STD	CUSTOMER
04	FLANGE WITH CENTRE HOLE $\phi 34 \pm 0.3$ mm.	1	FLANGE DIMENSIONS ACC TO: EN1092-1, DN80-DN200, ANSI B16.5, 3"-8" P/T RATING, SEE NOTE 1.	CUSTOMER
03	STAND PIPE FLANGE	1		
02	STAND PIPE	1		
01	STILL PIPE	1	$\phi 60.3 \times 2$ , SEE SHEET 2.	CUSTOMER

ISSUED BY GU-HF	WEEK 0307	PRODUCT CODE PRO/5600	FILE IDEAS/ACAD	INSTALLATION DRAWING TITLE	
APPROVED BY GST-TK	WEEK 0301	ORIGINAL DWG NO. 9150074-914	SCALE -	MECHANICAL INSTALLATION DWG PRO/5600, STILL PIPE	
<b>ROSEMOUNT</b>			1 ST ANGLE	DOC TYPE 2	DWG NO. 9150074-914
THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY.			CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.	ISSUE 4	SHEET 1/2