

Data sheet

Sheet No.: D105, Rev. C
 Date: February 2016

Hytork XL


Free Air Volume at Atmospheric Pressure

XL26 to XL4581 Imperial Data


Actuator Model	Double & Single Acting		
	Central Chamber Volumes (in3)		
	Open	Closed	Displaced
XL26	5.2	1.51	3.69
XL71	13.1	3.92	9.18
XL131	25.13	7.53	17.6
XL186	33.45	10.24	23.21
XL221	45.41	14.76	30.65
XL281	55.97	17.53	38.44
XL426	78.26	20.36	57.9
XL681	123.01	29.94	93.07
XL1127	205.48	50.66	154.82
XL1372	249.74	62.22	187.52
XL2586	452.16	98.19	353.97
XL4581	751.86	125.59	626.27

Actuator Model	Double Acting ONLY		
	End Cap Chamber Volumes (in3)		
	Open	Closed	Displaced
XL26	4.28	7.97	3.69
XL71	12.53	21.71	9.18
XL131	26.32	43.92	17.6
XL186	34.15	57.36	23.21
XL221	47.83	78.48	30.65
XL281	20	58.44	38.44
XL426	15.96	73.86	57.9
XL681	35.9	128.97	93.07
XL1127	49.88	204.7	154.82
XL1372	58.79	246.31	187.52
XL2586	74.69	428.66	353.97
XL4581	200.29	826.56	626.27

Spring Return and Double Acting Actuators



Double Acting Actuators



www.Hytork.com

Copyright © Emerson Process Management. The information in this document is subject to change without notice. Updated data sheets can be obtained from our website www.hytork.com or from your nearest Valve Automation Center
 USA: +1 813 630 2255 (fax 630 9449) UK: +44 191 5180020 (fax 5180032)

