


PLATE VERSION

THREADED VERSION



- ① WHEN NPT THREAD ADAPTER IS USED SUITABLE TAPER THREAD SEALING SHALL BE USED.
- ② PRESSURE AND TEMP RATING: FOR PRESSURE APPLICATIONS, CALCULATION OF FLANGE THICKNESS HAS TO BE DONE WITH RESPECT TO FLANGE MATERIAL, GASKET TYPE AND BOLTING. MAX ALLOWABLE RATING FOR ANTENNA TANK SEAL IS DEPENDING ON THE SEAL TYPE AND O-RING SELECTION.
- ③ RECOMMENDED INSTALLATION DISTANCE FROM TANK WALL TO RADAR GAUGE IS 600mm. INSTALLATION CLOSER TO THE TANK WALL MAY REDUCE PERFORMANCE.
- ④ LIQUID LEVEL ABOVE ROD END REQUIRES SPECIAL SETTINGS.
- ⑤ MAX NOZZLE HEIGHT 100 mm FOR ROD 100, MAX NOZZLE HEIGHT 250 mm FOR ROD 250.

08	THREADED ADAPTER	1	ISO 228-1, G 1.5", s60	RTR
07	GASKET	1	FOR G 1.5"	CUSTOMER
06	THREADED ADAPTER	1	1.5" NPT, s50	RTR
05	GASKET	1	SEE NOTE 2	CUSTOMER
04	ANTENNA PLATE	1	Ø99 FOR DN/JISSO AND ANSI 2" FLANGE Ø130 FOR DN/JIS80 AND ANSI 3" FLANGE Ø154 FOR DN/JIS100 AND ANSI 4" FLANGE	RTR
03	BOLTING	1	ACC. TO FLANGE STD.	CUSTOMER
02	FLANGE WITH CENTER HOLE Ø34±0,3mm, MAX THICKNESS 42mm	1	ACC. TO EN1092-1: DN50,80,100 OR ANSI B16.5: 2",3",4", P/T RATING, SEE NOTE 2.	CUSTOMER
01	TANK FLANGE	1		
POS	ITEM DESCRIPTION	QTY	REMARK	SUPPLIER
ISSUED BY	WEK	PRODUCT CODE	TITLE	
GU-TK-RS	0250	PRO/5600	ACAD	
APPROVED BY	WEK	ORIGINAL DWG NO.	SCALE	
GU-HF	0316	9150073-910		
			MECHANICAL INSTALLATION DWG	
			PRO/5600, ROD ANTENNA	
			1 ST ANGLE	
			DOC TYPE	DWG NO.
			2	9150073-910
			ISSUE	SHEET
			2	1/1

ROSEMOUNT
 THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY CONTRACTOR. WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.