

INMETRO Hazardous Area Approvals for Fisher® 4320 Wireless Position Monitor with On/Off Control Option

This supplement provides INMETRO Hazardous Area Approval information for the 4320 Wireless Position Monitor with On/Off Control Option instruction manual. Use this in conjunction with information provided in the 4320 Wireless Position Monitor with On/Off Control Option instruction manual (D103621X012).

National Institute of Metrology, Quality and Technology. INMETRO approval is accepted in Brazil.

Certain nameplates may carry more than one approval, and each approval may have unique installation/wiring requirements and/or conditions of “safe use”. These special instructions for “safe use” are in addition to, and may override, the standard installation procedures. Special instructions are listed by approval. Refer to the instruction manual for all other information regarding the 4320 wireless position monitor.

Note

This information supplements the nameplate markings affixed to the product.

Always refer to the nameplate itself to identify the appropriate certification.

⚠ WARNING

Failure to follow these conditions of “safe use” could result in personal injury or property damage from fire or explosion, and area re-classification.

Certification Number

IEEx 13.0238X

Standards Used for Certification

ABNT NBR IEC 60079-0:2013

ABNT NBR IEC 60079-11:2013

Intrinsically Safe

Battery Sourced Power Module w/out Pneumatic Output

Ex ia IIC T3/T4/T5 Ga

Battery Sourced Power Module with Pneumatic Output

Ex ia IIC T4/T5/T6 Ga



External Power Option w/out Pneumatic Output

Ex ia IIC T5 Ga

External Power Option with Pneumatic Output

Ex ia IIC T5 Ga

Enclosure:

Type 4X, IP66W, IP67W

External Power Terminal J5:U_i = 28 V, I_i = 100 mA, P_i = 1 W, C_i = 78 nF, L_i = 2.63 mH**HART Communication Terminals WP1/WP2:**U_i = 6 VDC, I_i = 5 mA, P_i = 30 mW, C_i = 2.5 nF, L_i = 0 mHU_o = 6 VDC, I_o = 14 mA, P_o = 84 mW, C_o = 39 µF, L_o = 150 mH**Temperature classification:****Battery Sourced Power Module w/out Pneumatic Output**

T5 = -40°C ≤ Tamb ≤ +40°C ; T4 = -40°C ≤ Tamb ≤ +75°C ; T3 = -40°C ≤ Tamb ≤ +85°C

Battery Sourced Power Module with Pneumatic Output

T6 = -20°C ≤ Tamb ≤ +31°C ; T5 = -20°C ≤ Tamb ≤ +46°C ; T4 = -20°C ≤ Tamb ≤ +50°C

External Power Option w/out Pneumatic Output

T5 = -40°C ≤ Tamb ≤ +80°C

External Power Option with Pneumatic Output

T5 = -20°C ≤ Tamb ≤ +50°C

Special Conditions of Use**Equipment with a Battery Sourced Power Module:**

- The HART (WP1-WP2) connections can only be connected to intrinsically safe certified equipment and in accordance with the instructions of the manufacturer. This combination must be compatible regarding intrinsic safety rules.
- The equipment should not be subjected to mechanical impacts or friction.
- Products that are operated by battery can only use power module GE57654X012 or GE57655X012.
- The piezo valve shall be used for control of non-flammable medium only.

Equipment with External Power:

- The apparatus may be powered externally via external power module GE61615X012.

Neither Emerson, Emerson Process Management, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher is a mark owned by one of the companies in the Emerson Process Management business unit of Emerson Electric Co. Emerson Process Management, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management
 Marshalltown, Iowa 50158 USA
 Sorocaba, 18087 Brazil
 Chatham, Kent ME4 4QZ UK
 Dubai, United Arab Emirates
 Singapore 128461 Singapore

www.Fisher.com