


CS200 Series

Fisher® Commercial Service Reliability



The Fisher® CS200 Series

The CS200 Series direct-operated, spring-loaded regulators have been engineered to fit a multitude of pressure-reducing applications including commercial and light industrial installations. This flexibility is provided by the numerous body sizes, outlet pressure settings, and orifice sizes. Ease of maintenance and installation is also a strength of the CS200 Series, which offers the combination of 360-degree rotatable union ring along with a rotatable upper casing that provides simplified vent positioning, especially in tight spaces or awkward installations.

To provide further flexibility, the CS200 Series offers optional overpressure protection via Internal Relief or Secondary Seat™ Protection.

By relieving gas through the diaphragm assembly to atmosphere, the Internal Relief valve minimizes downstream pressure build-up in the event of an overpressure situation.


Secondary Seat™ Protection provides shutoff in the event that the primary orifice seating surface or disk surface becomes damaged or obstructed by debris and can no longer provide shutoff. (See Figure on the following page)

Product advantages:

- Internal registration provides compact installation
- Multiple Overpressure Protection Options
 - Internal Relief
 - Secondary Seat™ Protection
 - Secondary Seat™ Protection with bleed
- Wide range of NPT body sizes
- Platform breadth and application coverage



Optional Secondary Seat™ Protection



CS200 Series Features

Operation: Direct-operated, Spring-loaded

Body Sizes:

3/4, 3/4 x 1, 3/4 x 1-1/4, 1, 1 x 1-1/4, and 1-1/4 NPT

Maximum Inlet Pressure: Up to 175 psig (12,1 bar)

Outlet Pressure Range:

3.5-inches w.c. to 2.0 psig (9 to 138 mbar)

Maximum Outlet (Casing) Pressure: 25 psig (1,7 bar)

Temperature Capabilities: -20° to 150°F (-29° to 66°C)

Spring Case Vent Connection: 1 NPT

Pressure Registration: Internal

Body Material: Gray Cast Iron

Overpressure Protection:

- Internal Relief
- Secondary Seat™ Protection

Natural Gas Technologies

Emerson Process Management Regulator Technologies, Inc.

North America

McKinney, Texas 75069-1872 USA

Tel: 1-800-558-5853

Outside U.S. 1-972-548-3574

Asia-Pacific

Singapore, Singapore 128461

Tel: +65 6777 8211

Europe

Bologna, Italy 40013

Tel: +39 051 4190611

Gallardon, France

Tel: +33 (0) 2 37 33 47 00



The distinctive swirl pattern cast into every actuator casing uniquely identifies the regulator as part of the Fisher® brand Commercial Service Regulator family and assures you of the highest-quality engineering, performance, and support traditionally associated with Fisher, Francel, and Tartarini regulators. Visit www.fishercommercialservice.com to access interactive applications.

Our Global Natural Gas Product Brands:

For further information, visit www.emersonprocess.com/regulators



D351365X012 © 2009 Emerson Process Management Regulator Technologies, Inc. All rights reserved. Printed in the U.S.A. 11/09. Fisher, Francel, Tartarini, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.

