

## Data sheet


Sheet No.: A1.101.71 Rev. C

Date: January 2012

# HIGH TEMPERATURE ACTUATOR SPECIFICATIONS

-20°C / +120°C

-4°F / +248°F



### Description

A double piston, rack and pinion pneumatic actuator incorporating a three point piston support system, anti-blowout spindle and with high duty synthetic bearings at all bearing points.

This version is a standard aluminum actuator, but incorporating parts and materials suitable for high temperature operation.

### Specification

Max. pressure : 120 psi (8 bar)  
 Torque : Standard  
 Media : Air or non corrosive gas  
 Temperature : -4°F to +248°F (-20°C to +120°C)  
 Finish : Polyester non-TGIC based powder coating (see data sheet A4.204.01)

### Spare parts

Dedicated high temperature spare parts are available for maintenance or make a standard actuator suitable for high temperature operation.

Materials				
Part	Material		Specifications	Remark
Housing	Aluminum Alloy		UNS A13600, ASTM B85	
	Aluminum Alloy		UNS 1 77075, ASTM 7075 T6	Hard anodized
Drive Shaft	Steel (180° rotation)		ETG100 or 42CrMo4V XM	Zinc Plated type > P750
	Stainless Steel		Sandvic 1802, SS2382 or X35CrM017	type > E950
	Aluminum Alloy		UNS A03560, ASTM B26	
Piston	Aluminum Alloy		UNS A03560, ASTM B26	
Sealings	Viton FPM O-rings		-/-	
Grease	Castrol LMX		-/-	
Shaft bearings	Top :	Delrin	POM	
	Bottom :	Nylatron	PA6.6 + MoS2	
Piston bearings	PTFE		25% Carbon filled	
Body bearings	PTFE	("E" series)	25% Carbon filled	
	Nylatron	("E" series)	PA6.6 + MoS2	
Shaft thrust washer	ZEDEX 100 K		-/-	
End cap bolts	Stainless Steel	("E" series)	AISI 304 A2	
	Alloy Steel	("P" series)	8.8 DIN 912	Deltatone® coating
Springs	Carbon Spring Steel		UNS G10860, ASTM A228	Deltatone® coating

**EL-O-MATIC™**

www.El-O-matic.com

Copyright © Emerson Process Management. The information in this document is subject to change without notice.

Updated data sheets can be obtained from our website [www.El-O-Matic.com](http://www.El-O-Matic.com) or from your nearest Valve Automation Center **USA:** +1 813 319 0266 **Europe:** +31 74 256 10 10 **Asia-Pacific:** +65 6501 4600



**EMERSON™**  
 Process Management