

ATEX Instruction Sheet

Part Number: ATEX145

Publish date: Feb, 2015

Wireless I/O Card (WIOC) Redundant Term Block

KL4302X1-CA2

Wireless I/O Card (WIOC) Redundant Term Block

Hazardous Atmosphere



II 3G Ex nA [ic] IIC Gc
FM13ATEX0094U
IECEX FMG 13.0036U

Power Specifications

Field circuit power rating 24 VDC +/- 10% at 30mA

Environmental Specifications

Ambient Temperature -40 to 70° C

Shock 10g ½ Sinewave for 11 msec

Vibration 1mm Peak to Peak from 2 to 13.2Hz; 0.7g from 13.2 to 150Hz

Airborne Contaminants ISA-S71.04 –1985 Airborne Contaminants Class G3

Relative Humidity 5 to 95% Non-Condensing IP 20 Rating

Terminal block key position D2

Note: Refer to the product label for serial number and location and date of manufacture.

Warning: This product has specific instructions for installation, removal and operation in hazardous areas. Refer to document 12P5403 "*DeltaV™ Electronic Marshalling Digital Automation System (CHARM I/O Subsystem) Zone 2 Installation Instructions*". Other installation instructions are available in the "*DeltaV™ S-series and CHARMs Hardware Installation*" manual.

Removal and Insertion

This unit cannot be removed or inserted with system power energized.

Maintenance and Adjustment

This unit contains no user serviceable parts and should not be disassembled for any reason. Calibration is not required.

Other Safety Approvals



CL. 1 Div. 2
GP. A,B,C,D
HAZ. LOC.
TEMP. Rating T4

