



A SOLID CONDUCTOR CAN BE PUSHED INTO THE TERMINAL BLOCK. IN CASE OF A FLEXIBLE CONDUCTOR, PUSH THE RELEASE BUTTON.



ROSEMOUNT 2410 TANK HUB.
 MAXIMUM RATINGS FOR OTHER FISCO POWER SUPPLY:
 $U_o \leq 17.5V$
 $P_o \leq 5.32W$
 (SEE NOTE 1)

ROSEMOUNT 2410 TANK HUB.
 MAXIMUM RATINGS FOR OTHER FISCO POWER SUPPLY:
 $U_o \leq 17.5V$
 $P_o \leq 5.32W$
 (SEE NOTE 1)



CABLE EXTERNAL GROUND:
 MIN 4 mm²

SEE NOTE 2 AND 3

FOR FUTURE USE

LOCKING SCREW


A BUILT-IN TERMINATOR WILL BE ENABLED BY CONNECTING A JUMPER.

TANKBUS CABLING:

CONDUCTOR INSULATION
 MAX DIAMETER 2.9 mm
 TO FIT IN TERMINAL.

8 mm STRIPPING
 LENGTH

CABLE DIAMETER FOR
 GLANDS WHEN SUPPLIED
 BY RTR: 6-12 MM.



PRESERVED
 INSULATION

CONDUCTOR:
 0.5-1.5 mm² (AWG 22-16)
 TWISTED SHIELDED PAIRS
 RECOMMENDED CABLE:
 1.0 mm² (AWG 18)

- 3 KEEP INSULATION PRESERVED IN AREA AROUND HOUSING INLETS TO AVOID CONTACT BETWEEN CABLES AND SHARP EDGES.
- 2 THE SHIELD MUST BE ISOLATED FROM THE HOUSING.
- 1 FOR MORE INFORMATION SEE SYSTEM CONTROL DWG 9240040-917.

ISSUED BY EMe-BL	WEEK 1050	PRODUCT CODE 5900	FILE ACAD	INSTALLATION DRAWING TITLE ELECTRICAL INSTALLATION DRAWING 5900 SERIES 2-in-1 DUAL BUS		
APPROVED BY EE-MK	WEEK 1052	ORIGINAL DWG NO. -	SCALE -	DOC TYPE 02	DWG NO. D9240041-969	ISSUE SHEET 02 01/01
ROSEMOUNT			1 ST ANGLE			
Tank Gauging			THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.			