

FloBoss™ 107 Enhanced Communication Module


The Enhanced Communication Module (ECM) for the FloBoss™ 107 Flow Manager (FB107) provides communications over one four-session Ethernet port and one Universal Serial Bus (USB) 2.0 port.

The Ethernet port allows up to four simultaneous independent connections into the FB107. Supported protocols include ROC, Modbus RTU Encapsulated in TCP/IP, and Modbus TCP/IP. In addition, the Ethernet port allows the FB107 to support Modbus TCP master, and up to 50 devices can be polled for data.

The USB 2.0 port allows a host to communicate with the FB107 through a standard USB connection. The USB 2.0 port supports both ROC and Modbus protocols.

Up to two ECM modules may be installed in the same FB107. The module plugs into the main board of the FB107, which provides power and control signals to activate COM2 or COM3.

You can install a communication module in slot 1 or 2 on the main FB107. When a communication module is installed in slot 2, the communication port (COM2) on the CPU is redirected to the type of module installed in slot 2. Use ROCLINK™ 800 Configuration Software to configure the modules.




D0C0835B

Enhanced Communication Module

FloBoss 107 Enhanced Communication Module

Field Wiring Terminals



DOC0835B

Terminal	Label	Definition
1	USB	USB 2.0 Port
2	ENET	Ethernet Port

Communication

Ethernet	Quantity	1
	Type	10BASE-T twisted pair. IEEE multi-segment 10 MB/second baseband Ethernet.
	Maximum Segment	100 m (330 ft)
	Protocols	ROC, Modbus master/slave (ASCII or RTU), Modbus RTU Encapsulated in TCP/IP, and Modbus TCP
	LED Indicators	Power, Link, Activity
USB	Quantity	1
	Type	USB 2.0 specification

Power

Consumption	Main power supply loading at the Battery Terminals (at 12.0 V dc):	
	Idle	450 mW
	Active	610 mW
Isolation	Per FCC Part 68.	

Physical

Dimensions	82.55 mm H by 25.4 mm W by 127 mm L (3.25 in. H by 1.0 in. W by 5.0 in. L)
Weight	68 g (2.4 oz.)

Environmental

Same as the FB107 in which it is installed.

Approvals

Same as the FB107 in which it is installed.

Headquarters:

Emerson Process Management

Remote Automation Solutions
6005 Rogerdale Road
Houston, TX 77072 U.S.A.
T +1 281 879 2699 | F +1 281 988 4445
www.EmersonProcess.com/Remote

Europe:

Emerson Process Management

Remote Automation Solutions
Unit 8, Waterfront Business Park
Dudley Road, Brierly Hill
Dudley UK DY5 1LX
T +44 1384 487200 | F +44 1384 487258
www.EmersonProcess.com/Remote

North American/Latin America:

Emerson Process Management

Remote Automation Solutions
6005 Rogerdale Road
Houston TX USA 77072
T +1 281 879 2699 | F +1 281 988 4445
www.EmersonProcess.com/Remote

Middle East/Africa:

Emerson Process Management

Remote Automation Solutions
Emerson FZE
P.O. Box 17033
Jebel Ali Free Zone – South 2
Dubai U.A.E.
T +971 4 8118100 | F +971 4 8865465
www.EmersonProcess.com/Remote

Asia-Pacific:

Emerson Process Management

Remote Automation Solutions
1 Pandan Crescent
Singapore 128461
T +65 6777 8211 | F +65 6777 0947
www.EmersonProcess.com/Remote

© 2009-2013 Remote Automation Solutions, a business unit of Emerson Process Management. All rights reserved.

Bristol, Inc., Bristol Canada, BBI SA de CV and Emerson Process Management Ltd, Remote Automation Solutions division (UK), are wholly owned subsidiaries of Emerson Electric Co. doing business as Remote Automation Solutions, a business unit of Emerson Process Management. FloBoss, ROCLINK, Bristol, Bristol Babcock, ControlWave, TeleFlow, Helicoid, OpenEnterprise, and METCO are trademarks of Remote Automation Solutions. AMS, PlantWeb and the PlantWeb logo are marks of Emerson Electric Co. The Emerson logo is a trademark and service mark of the Emerson Electric Co. All other marks are property of their respective owners.

The contents of this publication are presented for informational purposes only. While every effort has been made to ensure informational accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. Remote Automation Solutions reserves the right to modify or improve the designs or specifications of such products at any time without notice. All sales are governed by Remote Automation Solutions' terms and conditions which are available upon request. Remote Automation Solutions does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Remote Automation Solutions product remains solely with the purchaser and end-user.