


Issued by	NMi Certin B.V.
In accordance with	<ul style="list-style-type: none">- WELMEC guide 8.8 "General and Administrative Aspects of the Voluntary System of Modular Evaluation of Measuring instruments under the MID".- OIML R117-1 Edition 2007 (E) "Dynamic measuring systems for liquids other than water".
Producer	Mobrey Limited 158 Edinburgh Avenue Slough SL1 4UE United Kingdom
Measuring instrument	<p>A model of a liquid density meter (densitometer), intended to be used as a part of a measuring instrument.</p> <p>Brand : Micro Motion Type : 7835 and 7845 (Frequency and advanced electronics) Accuracy class : see description paragraph 1.2.3 Environment classes : M2 / E2 Temperature range liquid : see paragraph 1.2.3 of Description Temperature range ambient : -40 °C up to +70 °C (Density from Hart: -25 °C up to +70 °C)</p> <p>Further properties and test results are described in the annexes: - Description TC7637 revision 2 - Documentation folder TC7637-2</p>
Remarks	This revision replaces the earlier versions, except for its documentation folder.

Issuing Authority

NMi Certin B.V.
25 January 2013



C. Oosterman
Head Certification Board

NMi Certin B.V.
Hugo de Grootplein 1
3314 EG Dordrecht
The Netherlands
T +31 78 6332332
certin@nmi.nl
www.nmi.nl

This document is issued under the provision that no liability is accepted and that the applicant shall indemnify third-party liability.

Parties concerned can lodge objection against this decision, within six weeks after the date of submission, to the general manager of NMI (see www.nmi.nl).

Reproduction of the complete document only is permitted.