

ECO-SENSE Electrochemical H₂S

2-wire, Loop-powered Gas Detector

The ECO-SENSE detector is an innovative H₂S gas detection package designed for 2-wire, loop-powered installations. An economic and ecological choice, this versatile detector functions at less than 0.75 watts with 10–30 VDC and a full liquid crystal display (LCD) with light emitting diode (LED) indicators.

- Low power gas sensor functions in a 2-wire 4–20 mA sink mode
- Allows "one man" sensor calibration in hazardous areas without area declassification. No electric devices needed
- LCD readout and front panel alarm LED indicators for Alarm 1, Alarm 2, Fault, and IN CAL are standard
- Security mode allows locking of critical parameter
- CSA certifications

Features and Benefits

This advanced sensor interface includes a real time clock and calendar which is used for logging events such as sensor replacement, alarms, and calibrations.

Operator interface is through a menu driven magnetic keypad allowing full access without opening the enclosure. There are no potentiometers and all adjustments are performed through the keypad. Calibration magnet is included for non-intrusive calibration, no other special electronic devices are needed. Users can also program warm-up and calibration exit delays to avoid false alarms. Delay hold outputs at zero until sensor signals stabilize. IN/OUT alarm trip delays may also be programmed.



ECO-SENSE H₂S

- Field replaceable H₂S sensor module
- 4–20 mA signal may be transmitted thousands of feet on 2-wires

The ECO-SENSE H₂S sensor overcomes noise immunity problems associated with electrochemical sensors by enclosing all low level signals within a grounded sensor head available in aluminum and stainless steel. An integral "transient voltage suppressor" protects the device in case of lightning or other surge voltage levels. The sensor is enclosed in a rugged Class I, Division 1 enclosure suitable for hazardous environment installations and has been certified by CSA.


Specifications

Table 1 - ECO-SENSE Electrochemical H₂S

Controller Specifications	
Outputs	Low-powered, analog 2-wire 4–20 mA current sink output
Electrical	
Power Supply	10–30 VDC at less than 0.75 watts @ nominal 24 VDC 2-wire max loop R is 500 ohms 64 x 128 pixel LCD displays 30 minute trend, bar-graph and large engineering units and LED indicators
Environmental	
Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Enclosure	
Enclosure Material	316 stainless steel
Conduit Opening	¾" NPT (3X)
Mounting	Surface mount/2" Pipe mount
Certification	CSA Class I, Division 1 - Groups B, C and D; T5 Ex d IIB + H2 T5 Class I, Zone 1, AEx d IIB + H2 T5 Type 4X IP64
Warranty	2 years

ST490 Sensor Specifications	
Sensor Module	Electrochemical type sensor
Certification	CSA Class I, Division 1 - Groups B, C and D; T5 Ex d IIB + H2 T5 Class I, Zone 1, AEx d IIB + H2 T5 Type 4X IP64
Response Times	T20 < 10 s T50 < 30 s
Accuracy	±3 ppm or 10 % of reading, whichever is greater (25 °C), ±15 % of reading (at 0 and 50 °C)
Range	0–50 PPM
Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Housing	Aluminum and 316 stainless steel enclosure available
Warranty	2 years

Ordering Information
Transmitters and ST490 H2S Sensor
ECO-A-S-50 Single Channel-Analog-Stainless Steel
ECO-A-A-50 Single Channel-Analog-Aluminum



A		B		C		D		E	
in	mm	in	mm	in	mm	in	mm	in	mm
4.8	122	3.6	91	3.6	91	4.8	122	5.1	130
4.7	119	3.6	91	3.6	91	4.8	122	5.1	130

F		G		H		I		J	
in	mm	in	mm	in	mm	in	mm	in	mm
0.3	7.6	2.6	66	2.9	74	3.0	76	9.0	229
0.3	7.6	2.6	66	2.9	74	2.8	71	8.9	226

©2015 Emerson Process Management. All rights reserved.

Emerson Process Management
 Rosemount Analytical
 2721 Hopewell Place N.E.
 Calgary, AB T1Y 7J7
 CANADA
 Toll Free + 866 347 3427
 T + 403 219 0688
 F + 403 219 0694
SAFETY.CSC@Emerson.com

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

