

Rosemount 2051

Specifications

PERFORMANCE SPECIFICATIONS

For zero based spans, reference conditions, silicone oil fill, SST materials, Coplanar flange (2051C) or 1/2 in. - 14 NPT (2051T) process connections, digital trim values set to equal range points. Applicable to 4-20 mA HART output only unless otherwise noted.

Conformance To Specification ($\pm 3\sigma$ (Sigma))

Technology leadership, advanced manufacturing techniques and statistical process control ensure specification conformance to at least $\pm 3\sigma$.

Reference Accuracy⁽¹⁾

Models	Standard	Performance Option, P8
2051C		
Ranges 2-5	$\pm 0.075\%$ of span For spans less than 10:1, accuracy = $\pm \left[0.025 + 0.005 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$	Ranges 2-5 High Accuracy Option, P8 $\pm 0.065\%$ of span For spans less than 10:1, accuracy = $\pm \left[0.015 + 0.005 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$
Range 1	$\pm 0.10\%$ of span For spans less than 15:1, accuracy = $\pm \left[0.025 + 0.005 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$	
2051T		
Ranges 1-4	$\pm 0.075\%$ of span For spans less than 10:1, accuracy = $\pm \left[0.0075 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$	Ranges 1-4 High Accuracy Option, P8 $\pm 0.065\%$ of span For spans less than 10:1, accuracy = $\pm \left[0.0075 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$
Range 5	$\pm 0.075\%$ of span for spans greater than 5:1	
2051L		
Ranges 2-4	$\pm 0.075\%$ of span For spans less than 10:1, accuracy = $\pm \left[0.025 + 0.005 \left(\frac{URL}{Span} \right) \right] \% \text{ of Span}$	

(1) For FOUNDATION fieldbus transmitters, use calibrated range in place of span.


Long Term Stability

Models	Standard	Performance Option, P8
2051CD, CG	Range 1 (CD) $\pm 0.2\%$ of URL for 1 year, Reference Stability	
	Ranges 2-5 $\pm 0.1\%$ of URL for 2 years, Operating Stability	$\pm 0.125\%$ of URL for 5 years, Operating Stability
2051T	Ranges 1-5 $\pm 0.1\%$ of URL for 2 years, Operating Stability	$\pm 0.125\%$ of URL for 5 years, Operating Stability
2051L	Ranges 2-4 Not Specified	

Dynamic Performance

	4-20 mA HART ⁽¹⁾	1-5 Vdc HART Low Power	Fieldbus ⁽³⁾	Typical HART Transmitter Response Time
Total Response Time ($T_d + T_c$)⁽²⁾:				
2051C, Range 3-5:	115 milliseconds		152 milliseconds	
Range 1:	270 milliseconds		307 milliseconds	
Range 2:	130 milliseconds		152 milliseconds	
2051T:	100 milliseconds		152 milliseconds	
2051L:	See <i>Instrument Toolkit</i> [®]		See <i>Instrument Toolkit</i>	
Dead Time (T_d)	60 milliseconds (nominal)		97 milliseconds	
Update Rate	22 times per second		22 times per second	

(1) Dead time and update rate apply to all models and ranges; analog output only
 (2) Nominal total response time at 75 °F (24 °C) reference conditions.
 (3) Transmitter fieldbus output only, segment macro-cycle not included.



Line Pressure Effect per 1000 psi (6,9 MPa)

For line pressures above 2000 psi (13,7 MPa) and Ranges 4-5, see user manual (Rosemount publication number 00809-0100-4101).

Models	Line Pressure Effect
2051CD	Zero Error ⁽¹⁾
	Ranges 2-3 $\pm 0.1\%$ of URL/1000 psi (68,9 bar) for line pressures from 0 to 2000 psi (0 to 13,7 MPa)
	Range 1 $\pm 0.5\%$ of URL/1000 psi (68,9 bar)
	Span Error
	Ranges 2-3 $\pm 0.1\%$ of reading/1000 psi (68,9 bar)
	Range 1 $\pm 0.4\%$ of reading/1000 psi (68,9 bar)

(1) Can be calibrated out at line pressure.

Rosemount 2051

Ambient Temperature Effect per 50°F (28°C)

Models	Ambient Temperature Effect
2051C	Ranges 2-5 $\pm(0.025\% \text{ URL} + 0.125\% \text{ span})$ from 1:1 to 5:1 $\pm(0.05\% \text{ URL} + 0.25\% \text{ span})$ from 5:1 to 100:1 Range 1 $\pm(0.2\% \text{ URL} + 0.5\% \text{ span})$ from 1:1 to 50:1
2051T	Range 2-4 $\pm(0.05\% \text{ URL} + 0.25\% \text{ span})$ from 1:1 to 30:1 $\pm(0.07\% \text{ URL} + 0.25\% \text{ span})$ from 30:1 to 100:1 Range 1 $\pm(0.05\% \text{ URL} + 0.25\% \text{ span})$ from 1:1 to 10:1 $\pm(0.10\% \text{ URL} + 0.25\% \text{ span})$ from 10:1 to 100:1 Range 5 $\pm(0.2\% \text{ URL} + 0.3\% \text{ span})$
2051L	See <i>Instrument Toolkit</i>

Mounting Position Effects

Models	Mounting Position Effects
2051C	Zero shifts up to ± 1.25 inH ₂ O (3,1 mbar), which can be calibrated out. No span effect.
2051T	Zero shifts up to ± 2.5 inH ₂ O (6,2 mbar), which can be calibrated out. No span effect.
2051L	With liquid level diaphragm in vertical plane, zero shift of up to 1 inH ₂ O (2,49 mbar). With diaphragm in horizontal plane, zero shift of up to 5 inH ₂ O (12,43 mbar) plus extension length on extended units. Zero shifts can be calibrated out. No span effect.

Vibration Effect

Less than $\pm 0.1\%$ of URL when tested per the requirements of IEC60770-1 field or pipeline with high vibration level (10-60 Hz 0.21mm displacement peak amplitude / 60-2000 Hz 3g).

Power Supply Effect

Less than $\pm 0.005\%$ of calibrated span per volt.

Electromagnetic Compatibility (EMC)

Meets all relevant requirements of EN 61326 and NAMUR NE-21.

Transient Protection (Option Code T1)

Meets IEEE C62.41, Category Location B

- 6 kV crest (0.5 μ s - 100 kHz)
- 3 kV crest (8 x 20 microseconds)
- 6 kV crest (1.2 x 50 microseconds)

FUNCTIONAL SPECIFICATIONS

Range and Sensor Limits

Range	2051CD, 2051CG, 2051L					
	Minimum Span	Range and Sensor Limits				
		Upper (URL)	Lower (LRL)			
			2051C Differential	2051C Gage ⁽¹⁾	2051L Differential	2051L Gage ⁽¹⁾
1	0.5 inH ₂ O (1,2 mbar)	25 inH ₂ O (62,3 mbar)	-25 inH ₂ O (-62,1 mbar)	-25 inH ₂ O (-62,1 mbar)	N/A	N/A
2	2.5 inH ₂ O (6,2 mbar)	250 inH ₂ O (0,62 bar)	-250 inH ₂ O (-0,62 bar)	-250 inH ₂ O (-0,62 bar)	-250 inH ₂ O (-0,62 bar)	-250 inH ₂ O (-0,62 bar)
3	10 inH ₂ O (24,9 mbar)	1000 inH ₂ O (2,49 bar)	-1000 inH ₂ O (-2,49 bar)	-393 inH ₂ O (-979 mbar)	-1000 inH ₂ O (-2,49 bar)	-393 inH ₂ O (-979 mbar)
4	3 psi (0,207 bar)	300 psi (20,6 bar)	-300 psi (-20,6 bar)	-14.2 psig (-979 mbar)	-300 psi (-20,7 bar)	-14.2 psig (-979 mbar)
5	20 psi (1,38 bar)	2000 psi (137,9 bar)	-2000 psi (-137,9 bar)	-14.2 psig (-979 mbar)	N/A	N/A

(1) Assumes atmospheric pressure of 14.7 psig.

Range	2051T			
	Minimum Span	Range and Sensor Limits		
		Upper (URL)	Lower (LRL) (Abs)	Lower ⁽¹⁾ (LRL) (Gage)
1	0.3 psi (20,6 mbar)	30 psi (2,06 bar)	0 psia (0 bar)	-14.7 psig (-1,01 bar)
2	1.5 psi (0,103 bar)	150 psi (10,3 bar)	0 psia (0 bar)	-14.7 psig (-1,01 bar)
3	8 psi (0,55 bar)	800 psi (55,2 bar)	0 psia (0 bar)	-14.7 psig (-1,01 bar)
4	40 psi (2,76 bar)	4000 psi (275,8 bar)	0 psia (0 bar)	-14.7 psig (-1,01 bar)
5	2000 psi (137,9 bar)	10000 psi (689,4 bar)	0 psia (0 bar)	-14.7 psig (-1,01 bar)

(1) Assumes atmospheric pressure of 14.7 psig.

Service

Liquid, gas, and vapor applications

Protocols

4–20 mA HART (Output Code A)

Output

Two-wire 4–20 mA, user-selectable for linear or square root output. Digital process variable superimposed on 4–20 mA signal, available to any host that conforms to the *HART* protocol.

Power Supply

External power supply required. Standard transmitter operates on 10.5 to 42.4 V dc with no load.


Turn-On Time

Performance within specifications less than 2.0 seconds after power is applied to the transmitter.

Load Limitations

Maximum loop resistance is determined by the voltage level of the external power supply, as described by:

$$\text{Maximum Loop Resistance} = 43.5 * (\text{Power Supply Voltage} - 10.5)$$



The *HART* communicator requires a minimum loop resistance of 250Ω for communication.

FOUNDATION fieldbus (Output Code F)

Power Supply

External power supply required; transmitters operate on 9.0 to 32.0 V dc transmitter terminal voltage.

Current Draw

17.5 mA for all configurations (including LCD display option)

Turn-On Time

Performance within specifications less than 20.0 seconds after power is applied to the transmitter.

FOUNDATION fieldbus Function Block Execution Times

Block	Execution Time
Resource	-
Transducer	-
LCD Block	-
Analog Input 1, 2	30 milliseconds
PID	45 milliseconds

FOUNDATION fieldbus Parameters

Schedule Entries	7 (max.)
Links	20 (max.)
Virtual Communications Relationships (VCR)	12 (max.)

Standard Function Blocks

Resource Block

- Contains hardware, electronics, and diagnostic information.

Transducer Block

- Contains actual sensor measurement data including the sensor diagnostics and the ability to trim the pressure sensor or recall factory defaults.

LCD Block

- Configures the local display.

2 Analog Input Blocks

- Processes the measurements for input into other function blocks. The output value is in engineering units or custom and contains a status indicating measurement quality.

PID Block

- Contains all logic to perform PID control in the field including cascade and feedforward.

Backup Link Active Scheduler (LAS)

The transmitter can function as a Link Active Scheduler if the current link master device fails or is removed from the segment.

1-5 Vdc HART Low Power (Output Code M)

Output

Three wire 1–5 Vdc output, user-selectable for linear or square root output. Digital process variable superimposed on voltage signal, available to any host conforming to the *HART* protocol.

Power Supply

External power supply required. Standard transmitter operates on 9 to 28 Vdc with no load.

Power Consumption

3.0 mA, 27–84 mW

Output Load

100 kΩ or greater

Turn-On Time

Performance within specifications less than 2.0 seconds after power is applied to the transmitter.

Overpressure Limits

Transmitters withstand the following limits without damage:

2051C

- Ranges 2–5: 3626 psig (250 bar)
4500 psig (310,3 bar) for option code P9
- Range 1: 2000 psig (137,9 bar)

2051T

- Range 1: 750 psi (51,7 bar)
- Range 2: 1500 psi (103,4 bar)
- Range 3: 1600 psi (110,3 bar)
- Range 4: 6000 psi (413,7 bar)
- Range 5: 15000 psi (1034,2 bar)

2051L

Limit is flange rating or sensor rating, whichever is lower (see Table 1).

TABLE 1. 2051L Flange Rating

Standard	Type	CS Rating	SST Rating
ANSI/ASME	Class 150	285 psig	275 psig
ANSI/ASME	Class 300	740 psig	720 psig
<i>At 100 °F (38 °C), the rating decreases with increasing temperature.</i>			
DIN	PN 10–40	40 bar	40 bar
DIN	PN 10/16	16 bar	16 bar
<i>At 248 °F (120 °C), the rating decreases with increasing temperature.</i>			

Static Pressure Limit

2051CD

- Operates within specifications between static line pressures of -14.2 psig (0.034 bar) and 3626 psig (250 bar)
- For Option Code P9, 4500 psig (310,3 bar)
- Range 1: 0.5 psia to 2000 psig (34 mbar and 137,9 bar)

Burst Pressure Limits

2051C Coplanar or traditional process flange

- 10000 psig (689,5 bar)

2051T

- Ranges 1–4: 11000 psi (758,4 bar)
- Range 5: 26000 psi (1792,64 bar)

Temperature Limits

Ambient⁽¹⁾

–40 to 185 °F (–40 to 85 °C)

With LCD display⁽²⁾: –40 to 175 °F (–40 to 80 °C)

Storage⁽¹⁾

–50 to 230 °F (–46 to 110 °C)

With LCD display: –40 to 185 °F (–40 to 85 °C)

(1) Limits for silicone fill fluid only.

(2) LCD display may not be readable and LCD updates will be slower at temperatures below -4 °F (-20 °C).

Process Temperature Limits

At atmospheric pressures and above.

TABLE 2. 2051 Process Temperature Limits

2051C	
Silicone Fill Sensor ⁽¹⁾	
with Coplanar Flange	–40 to 250 °F (–40 to 121 °C) ⁽²⁾
with Traditional Flange	–40 to 300 °F (–40 to 149 °C) ⁽²⁾
with Level Flange	–40 to 300 °F (–40 to 149 °C) ⁽²⁾
with 305 Integral Manifold	–40 to 300 °F (–40 to 149 °C) ⁽²⁾
Inert Fill Sensor ⁽¹⁾	0 to 185 °F (–18 to 85 °C) ⁽³⁾
2051T (Process Fill Fluid)	
Silicone Fill Sensor ⁽¹⁾	–40 to 250 °F (–40 to 121 °C) ⁽²⁾
Inert Fill Sensor ⁽¹⁾	–22 to 250 °F (–30 to 121 °C) ⁽²⁾
2051L Low-Side Temperature Limits	
Silicone Fill Sensor ⁽¹⁾	–40 to 250 °F (–40 to 121 °C) ⁽²⁾
Inert Fill Sensor ⁽¹⁾	0 to 185 °F (–18 to 85 °C) ⁽²⁾
2051L High-Side Temperature Limits (Process Fill Fluid)	
Syltherm [®] XLT	–100 to 300 °F (–73 to 149 °C)
D.C. Silicone 704 [®]	32 to 400 °F (0 to 205 °C)
D.C. Silicone 200	–40 to 400 °F (–40 to 205 °C)
Inert	–50 to 350 °F (–45 to 177 °C)
Glycerin and Water	0 to 200 °F (–18 to 93 °C)
Neobee M-20	0 to 400 °F (–18 to 205 °C)
Propylene Glycol and Water	0 to 200 °F (–18 to 93 °C)

(1) Process temperatures above 185 °F (85 °C) require derating the ambient limits by a 1.5:1 ratio.

(2) 220 °F (104 °C) limit in vacuum service; 130 °F (54 °C) for pressures below 0.5 psia.

(3) 160 °F (71 °C) limit in vacuum service.

Humidity Limits

0–100% relative humidity

Volumetric Displacement

Less than 0.005 in³ (0,08 cm³)

Damping

Analog output response to a step input change is user-selectable from 0 to 25.6 seconds for one time constant. This software damping is in addition to sensor module response time.

Rosemount 2051

Failure Mode Alarm

If self-diagnostics detect a sensor or microprocessor failure, the analog signal is driven either high or low to alert the user. High or low failure mode is user-selectable with a jumper on the transmitter. The values to which the transmitter drives its output in failure mode depend on whether it is factory-configured to *standard* or *NAMUR-compliant* operation. The values for each are as follows:

Standard Operation			
Output Code	Linear Output	Fail High	Fail Low
A	$3.9 \leq I \leq 20.8$	$I \geq 21.75 \text{ mA}$	$I \leq 3.75 \text{ mA}$
M	$0.97 \leq V \leq 5.2$	$V \geq 5.4 \text{ V}$	$V \leq 0.95 \text{ V}$

NAMUR-Compliant Operation			
Output Code	Linear Output	Fail High	Fail Low
A	$3.8 \leq I \leq 20.5$	$I \geq 22.5 \text{ mA}$	$I \leq 3.6 \text{ mA}$

Output Code F

If self-diagnostics detect a gross transmitter failure, that information gets passed as a status along with the process variable.

PHYSICAL SPECIFICATIONS

Electrical Connections

$1/2$ -14 NPT, $G^{1/2}$, and $M20 \times 1.5$ (CM20) conduit.

Process Connections

2051C

- $1/4$ -18 NPT on $2^{1/8}$ -in. centers
- $1/2$ -14 NPT and RC $1/2$ on 2-in. (50.8mm), $2^{1/8}$ -in. (54.0 mm), or $2^{1/4}$ -in. (57.2mm) centers (process adapters)

2051T

- $1/2$ -14 NPT female
- $G^{1/2}$ A DIN 16288 Male (available in SST for Range 1-4 transmitters only)
- Autoclave type F-250-C (Pressure relieved $9/16$ -18 gland thread; $1/4$ OD high pressure tube 60° cone; available in SST for Range 5 transmitters only)

2051L

- High pressure side: 2-in. (50.8mm), 3-in. (72 mm), or 4-in. (102mm), ASME B 16.5 (ANSI) Class 150 or 300 flange; 50, 80 or 100 mm, DIN 2501 PN 40 or 10/16 flange
- Low pressure side: $1/4$ -18 NPT on flange, $1/2$ -14 NPT on process adapter

2051C Process Wetted Parts

Drain/Vent Valves

316 SST or Alloy C-276

Process Flanges and Adapters

Plated carbon steel, SST CF-8M (cast version of 316 SST, material per ASTM-A743), or CW12MW (cast version of Alloy C-276)

Wetted O-rings

Glass-filled PTFE or Graphite-filled PTFE

Process Isolating Diaphragms

316L SST or Alloy C-276

2051T Process Wetted Parts

Process Connections

- 316L SST or Alloy C-276

Process Isolating Diaphragms

- 316L SST or Alloy C-276

2051L Process Wetted Parts

Flanged Process Connection (Transmitter High Side)

Process Diaphragms, Including Process Gasket Surface

- 316L SST or Alloy C-276

Extension

- CF-3M (Cast version of 316L SST, material per ASTM-A743), or Cast C-276. Fits schedule 40 and 80 pipe.

Mounting Flange

- Zinc-cobalt plated CS or SST

Reference Process Connection (Transmitter Low Side)

Isolating Diaphragms

- 316L SST or Alloy C-276

Reference Flange and Adapter

- CF-8M (Cast version of 316 SST, material per ASTM-A743)

Product Data Sheet

00813-0100-4101, Rev BA
February 2009

Rosemount 2051

Non-Wetted Parts for 2051C/T/L

Electronics Housing

Low-copper aluminum or CF-8M (Cast version of 316 SST).
Enclosure Type 4X, IP 65, IP 66, IP68

Coplanar Sensor Module Housing

CF-3M (Cast version of 316L SST)

Bolts

ASTM A449, Type 1 (zinc-cobalt plated carbon steel)
ASTM F593G, Condition CW1 (Austenitic 316 SST)
ASTM A193, Grade B7M (zinc plated alloy steel)

Sensor Module Fill Fluid

Silicone oil (D.C. 200) or Fluorocarbon oil (Halocarbon or Fluorinert® FC-43 for 2051T)

Process Fill Fluid (2051L only)

Syltherm XLT, D.C. Silicone 704,
D.C. Silicone 200, inert, glycerin and water, Neobee M-20 or propylene glycol and water

Paint

Polyurethane

Cover O-rings

Buna-N

Shipping Weights

TABLE 3. Transmitter Weights without Options

Transmitter	lb. (kg)
2051C	4.9 (2,2)
2051L	Table 4 below
2051T	3.1 (1,4)

TABLE 4. 2051L Weights without Options

Flange	Flush lb. (kg)	2-in. Ext. lb (kg)	4-in. Ext. lb (kg)	6-in. Ext. lb (kg)
2-in., 150	12.5 (5,7)	—	—	—
3-in., 150	17.5 (7,9)	19.5 (8,8)	20.5 (9,3)	21.5 (9,7)
4-in., 150	23.5 (10,7)	26.5 (12,0)	28.5 (12,9)	30.5 (13,8)
2-in., 300	17.5 (7,9)	—	—	—
3-in., 300	22.5 (10,2)	24.5 (11,1)	25.5 (11,6)	26.5 (12,0)
4-in., 300	32.5 (14,7)	35.5 (16,1)	37.5 (17,0)	39.5 (17,9)
DN 50/PN 40	13.8 (6,2)	—	—	—
DN 80/PN 40	19.5 (8,8)	21.5 (9,7)	22.5 (10,2)	23.5 (10,6)
DN 100/ PN 10/16	17.8 (8,1)	19.8 (9,0)	20.8 (9,5)	21.8 (9,9)
DN 100/ PN 40	23.2 (10,5)	25.2 (11,5)	26.2 (11,9)	27.2 (12,3)

TABLE 5. Transmitter Options Weights

Code	Option	Add lb (kg)
J, K, L, M	Stainless Steel Housing	3.9 (1,8)
M5	LCD display for Aluminum Housing	0.5 (0,2)
B4	SST Mounting Bracket for Coplanar Flange	1.0 (0,5)
B1 B2 B3	Mounting Bracket for Traditional Flange	2.3 (1,0)
B7 B8 B9	Mounting Bracket for Traditional Flange	2.3 (1,0)
BA, BC	SST Bracket for Traditional Flange	2.3 (1,0)
H2	Traditional Flange	2.6 (1,2)
H3	Traditional Flange	3.0 (1,4)
H4	Traditional Flange	3.0 (1,4)
H7	Traditional Flange	2.7 (1,2)
FC	Level Flange—3 in., 150	12.7 (5,8)
FD	Level Flange—3 in., 300	15.9 (7,2)
FA	Level Flange—2 in., 150	8.0 (3,6)
FB	Level Flange—2 in., 300	8.4 (3,3)
FP	DIN Level Flange, SST, DN 50, PN 40	7.8 (3,5)
FQ	DIN Level Flange, SST, DN 80, PN 40	12.7 (5,8)