


Using Virtual Technology



Your Requirements:

- Platform familiarity for your staff
- Small footprint to fit into a limited space
- Portable between different plant locations

The Best Solution:

Ovation™ Simulation using innovative virtual technology replicates traditional control system controllers using a few desktop workstations.

Actual DCS controllers are replaced with controller software embedded in Microsoft® Windows®-based workstations. Implementing an Ovation simulation solution with virtual technology executes the control logic, algorithms and control timing directly in the Windows operating system environment, leaving the controller code undisturbed. Virtual controllers incorporate all of the functionality of the actual control system controller package.

Ovation virtual architectures are available as single workstations containing multiple virtual controllers and a combination of operator, engineering and database functions or in a networked configuration with functions spread across several workstations. Up to 20¹ controllers can be virtually duplicated in a single workstation, making Ovation Simulation a powerful and portable training tool for use throughout your facility.

Benefits

- Minimizes hardware costs
- Executes control logic, algorithms and control timing in the workstation, keeping the original controller code intact
- Provides a smaller system footprint to fit into training areas with limited space
- Offers a portable configuration that can easily be moved to anywhere in the plant
- Uses well-known desktop systems that are similar to your control room workstations

¹The maximum number of virtual controllers per host is 20, but the recommended limit for maximum performance is 10.

© 2016 Emerson Process Management. All rights reserved. For Emerson Process Management trademarks and service marks, go to: <http://www.emersonprocess.com/home/news/resources/marks.pdf>. All other marks are property of their respective owners. The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the design or specification of such products at any time without notice.

Emerson Process Management
Power & Water Solutions, Inc.
200 Beta Drive
Pittsburgh, PA 15238
USA
Phone: 1-412-963-4000
Fax: 1-412-963-4447
www.EmersonProcess-PowerWater.com