



Triaxial Accelerometer with Integral Magnet

Reduce route collection time up to 50% by simultaneously collecting three axis measurements (horizontal, vertical, axial) — plus PeakVue™ measurements — using one button push on the AMS 2140 four-channel analyzer.

To aid in data-collection efficiency, the sensor has a patented integral magnet for use on any curved or flat surfaces without needing special mounting hardware to attach to the machine. And to make handling the sensor simpler, the sensor uses a single cable attachment to the AMS 2140.




Directions in which each AMS 2140 channel collects data on the sensor.



Dynamic Performance	
Sensitivity ($\pm 10\%$)	100 mV/g (10.2 mV/m/s ²); All 3 Axis
Measurement Range	± 50 g (± 490 m/s ²)
Frequency Range: ± 3 dB (CH/A axis)	0.5 to 10,000 Hz (30 to 600,000 cpm)
± 3 dB (CH/B & CH/C axis)	2.0 to 3,500 Hz (120 to 210,000 cpm)
Mounted Resonant Frequency	23 kHz Nominal
Amplitude Linearity	$\pm 1\%$ (0 Based, Least Squares, Straight Line)
Transverse Sensitivity	$\leq 7\%$
Environmental	
Shock Limit	5,000g pk (49,010 m/s ²)
Temperature Range	-54 to 121°C (-65 to 250°F)
Temperature Response	See Graph
Sealing / Rating	Welded Hermetic / IP68
Electrical	
Settling Time	≤ 2.0 sec (Within 1% of Bias)
Discharge Time Constant (Z axis)	≥ 0.3 sec
Discharge Time Constant (X & Y axis)	≥ 0.06 sec
Excitation Voltage / Current	18 to 28 VDC / 2.0 to 20 mA
Output Bias	8 to 12 VDC
Output Impedance	<150 ohms
Broadband Resolution (1 to 10 KHz)	500 μ g (4,905 μ m/s ²) Electrical Noise
Case Isolation	$>10^8$ ohms



The combination of the four-channel AMS 2140 and the safety-rated integral magnet triaxial accelerometer allows the user to collect data going from bearing to bearing rather than point to point resulting in significantly reduced route data collection times.



Mechanical			
Weight	175 grams (6.18 oz) Sensor & Magnet		
Mounting / Magnet Pull Strength	2 Pole Magnet / 200 N (45 lb) min		
Sensor Element / Geometry	Ceramic / Shear		
Case Material	Stainless Steel		
Connector Type (Top)	5 Pin		
Safety Ratings			
<p>ATEX - This sensor has been approved for Hazardous Locations Directive 94/9/EC Ex ic IIC T4, Ex nA IIC T4. For safe use all applicable local electrical laws must be followed.</p> <p>The supply electrical parameters must not exceed any of the following values:</p> <ul style="list-style-type: none"> ▪ X and Y axis $U_i \leq 28V$, $I_i \leq 180mA$, $P_i \leq 1.26W$, $C_i \leq 21nF$, $L_i \leq 0$ ▪ Z axis $U_i \leq 28V$, $I_i \leq 180mA$, $P_i \leq 1.26W$, $C_i \leq 63 nF$, $L_i \leq 0$ 			
Ambient Operating Temperature Range	$-54^{\circ}C \leq T_a \leq +121^{\circ}C$		
CSA(US)	AEx ic IIC T4 AEx nA IIC T4 CI I, DIV 2, GR A,B,C,D		
IECEX	Ex ic IIC T4 Gc Ex nA IIC T4 Gc IECEs LCIE 14.0051X		
Accessories			
Three Point Calibration Supplied	Optional accessories include cable (D25493) and mounting pad (D24826)		
Sensor Channels Accessories			
A0643TX -EX Triax Accelerometer Axis as marked on sensor	A	B	C
AMS 2140 Input Channel	A	B	C
AMS Machinery Manager Software Channel	1	2	3
Horizontally mounted orientation of the A0643TX-EX with "C" label pointing up	Horizontal	Axial	Vertical

©2017, Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

Emerson
Reliability Solutions
 835 Innovation Drive
 Knoxville, TN 37932
 ☎ +1 865 675 2400
 🌐 www.emerson.com/ams