ASCO[™] Gas Shutoff Valves

Direct Acting | 1/8" NPT

Features

- 2-way normally closed operation
- For control of commercial and industrial gas pilot controls
- Brass body construction
- Mountable in any position
- Direct lift with resilient soft sealing for tight shutoff

Fluid

Fuel Gas

Construction

Valve Parts in Contact with Fluids						
Body	Brass					
Core Tube/ Bonnet	Stainless Steel / Plated Steel					
Core and Plugnut	Stainless Steel					
Springs	Stainless Steel					
Seals and Disc	NBR / FKM					
Shading Coil	Copper					

Electrical

				ating and onsumptio					
	Standard			AC					
	Coil and Class of	DC		VA	VA	Ambient	Spare Coil Famil		
Prefix	Insulation	Watts	Watts	Holding	Inrush	Temp.0F	AC	DC	
U	F	6.9	6.3	8.8	12.1	-22 to 140	400117	400117	
SC	F	6.9	6.3	8.8	12.1	-22 to 140	400127	400127	
Standard voltages: 24,120, 240 volts AC, 50-60 Hz. 12, 24, 120 volts DC Must be specified when ordering.									

Solenoid Enclosures

Standard: Open frame (Prefix U) 18" leads

Optional: DIN (size 11mm, form B) (Prefix SC). Watertight/IP-65 when used with DIN connector kit for SC coils (see kits below).

Valve Response Time

Opening Time: Less than 1 second Closing Time: Less than 1 second

Kits

1/2" NPT conduit hub kit for leaded coils 224735-001-*
(Kit contains 10 pcs. of each: threaded hub, gasket and attaching screw.)
DIN connector kit for SC coils 226061-001-*
(Kit contains 10 pcs of each: connector, gasket, and attaching screw.)

Approvals

UL recognized component to standard 429 "Electrically Operated Valves," Guide YIOZ2, File MH45368 Safety Shutoff Valves. CSA Certified to:

- 1) Standard C22.2 No. 139 "Electrically Operated Valves," File 234503.
- 2) Automatic Gas Safety Shutoff Valves ANSI Z21.21 CSA 6.5 C/I, File 234503.






Specifications English units (Metric)

				Operati	ng Pressure Differe					Wattage			
Pipe	Orifice	Flow	Gas Capacity ①	1	Max. AC	Max. DC	Min.	Max. Fluid Temp. °F (°C)					Approx. Shipping
Size (in)	Size in (mm)	Factor Cv (Kv)	Btu/hr.	Min.	Fuel Gas	Fuel Gas	Fluid Temp.0F	AC	DC	Brass	AC	DC	Weight Ibs (kgs)
Fuel Gas Shutoff - Normally Closed													
1/8	7/64 (2.8)	0.16 (0.14)	9000	0	200 (14)	65 (4)	-22 (-30)	180 (82)	180 (82)	U8256A091V (2)	6.3	6.9	0.5 (0.22)
① 1" W.C	① 1" W.C. Drop @ 2" W.C. Inlet Pressure, 1,000 Btu/cu.ft. or more, 0.64 Specific Gravity Gas. ② For DIN option, replace U prefix with SC prefix.												

Gas Flow Chart



Dimensions: inches (mm)

EMERSON

308

