

RIDGID

WD1956 16 Gallon Stainless Steel Wet/Dry Vac

RIDGID
FULL LIFETIME WARRANTY
Against Material Defects
& Workmanship

This RIDGID® 16 Gallon Stainless Steel Wet/Dry Vac is designed to deliver the powerful suction, large capacity, rugged construction, unique features and excellent mobility that Pros demand for job site or shop. The powerful 6.5 peak horsepower motor easily handles the toughest job site clean-up tasks. A 3-layer fine dust filter captures dry wall dust. Moving up & down steps or across rough terrain is a snap with the large fixed rear wheels. Add a top handle with a cord wrap, stainless steel drum construction, an accessory storage bag attached to a quick release handle plus patented Scroll Noise Reduction® for quiet operation and you've got a wet/dry vacuum that meets the demands of Pros on the job site.

FEATURES	BENEFITS
• 6.5 Peak HP Motor	Provides industry leading power and performance.
• Sound Reduction Technology	Scroll Noise Reduction® is a patented feature that provides quiet operation by precisely controlling the flow of air through the vac.
• Sturdy Cart, Push Handle, Large Rear Wheels	These features act together to allow vac to travel easily up/down stairs and over rough terrain.
• Quick Release Push Handle	Depress two spring loaded ball bearings to quickly remove handle & accessory storage bag as a unit. Makes emptying debris from drum quick, easy, and much more convenient.
• Stainless Steel Drum	Provides rugged, attractive, & clean exterior to meet the higher demands found on the job site.
• 3-Layer Fine Dust Filter	Captures fine dust particles such as dry wall dust.
• Dual-Flex® Locking Hose	Resists collapsing and adds 180° flexibility at both hose ends. Hose locks onto vac.
• Large Carry Handle	Allows easy lifting of vac into service vehicle.
• Long Cord Plus Cord Storage	Extra long 20' power cord wraps neatly around carry handle.
• Powerful Blowing Performance	Move hose to exhaust port to blow debris from garages, decks, sidewalks, etc.
• Included Accessories	2-1/2" x 7' Dual-Flex® Locking Hose, 2 Extension Wands, Utility Nozzle, Car Nozzle, Wet Nozzle, Crevice Tool



SPECIFICATIONS

Drum Size	16 gal.
Motor	
- Peak Horsepower	6.5
- Air Watts	294
- Voltage	120
- Amps	12.0
Cord Length	20'
Construction	Stainless Steel
U.L. Listed	Yes
Included Filter	Fine Dust
Replacement Filters	VF5000 VF6000
Optional Wet Filter	VF7000
Optional Filter Bag	VF3502
Accessory Size	2-1/2"
Shipping Weight	38.5 lbs.
Net Weight	27.8 lbs.



Accessory Storage Bag



Wet Pick-up - Basements, etc.



Vac with Accessories & Filter



Dry Pick-up - Workshop, Garage etc.