

# RIDGID

## WD1450 14 Gallon High Performance Wet/Dry Vac



This RIDGID® 14 Gallon High Performance Wet/Dry Vac is designed to deliver the powerful suction, large capacity, and rugged construction in a more compact design than is offered in our largest cart type vacs. The vacuum's 14 gallon drum size achieve a more compact overall design but it still provides a big capacity capable of handling large job-site chores. The 6.0 peak horsepower motor delivers the high performance necessary to handle these chores. Other key features include; a 3-layer fine dust filter captures dry wall dust, accessories are stored on-board, casters provide 360° mobility. Add a top handle with a cord wrap, heavy duty 2-piece drum construction, a large drain and you've got a wet/dry vac that achieves the demands of Pro's on the job site or in the shop.

FEATURES	BENEFITS
• 6.0 Peak HP Motor	Market proven quality, performance, and durability.
• Sound Reduction Technology	Scroll Noise Reduction® is a patented feature that provides quiet operation by precisely controlling the flow of air through the vac.
• 4 Swivel Casters	Provide easy 360° mobility.
• Innovative Accessory Storage	Unique built-in accessory caddy - Conveniently stores accessories and hose quick at hand. No more searching or fumbling to find the accessories you need.
• 2-Piece Drum Construction	Provides improved, more rugged construction to meet the higher demands found on the job site.
• 3-Layer Fine Dust Filter	Captures fine dust particles such as dry wall dust.
• Dual-Flex® Locking Hose	Resists collapsing and adds 180° flexibility at both hose ends. Hose locks onto vac.
• Large Carry Handle	Allows easy lifting of vac into service vehicle.
• Long Cord Plus Cord Storage	Extra long 20' power cord wraps neatly around carry handle.
• Powerful Blowing Performance	Move hose to exhaust port to blow debris from garages, decks, sidewalks, etc.
• Included Accessories	2-1/2" x 7' Dual-Flex® Locking Hose, 2 Extension Wands, Utility Nozzle, Car Nozzle, Wet Nozzle, & a 3-Layer Fine Dust Filter



### SPECIFICATIONS

Drum Size	14 gal.
Motor	
- Peak Horsepower	6.0
- Air Watts	256
- Voltage	120
- Amps	11.0
Cord Length	20'
Construction	High Impact Polypropylene
U.L. Listed	Yes
Included Filter	Fine Dust
Replacement Filters	VF5000 VF6000
Optional Wet Filter	VF7000
Optional Filter Bag	VF3502
Accessory Size	2-1/2"
Shipping Weight	26 lbs.
Net Weight	22 lbs.



Dual-Flex® Locking Hose



On-Board Accessory Storage



Vac with Accessories & Filter



Dry Pick-up - Workshop, Garage etc.