ASCO™ Gas Shutoff Valves

Pilot Operated | 3/8" - 3/4" NPT

Features

- 2-way normally closed operation
- For control of commercial and industrial gas burners
- Ideal for high pressure applications
- Brass body construction
- Mountable in any position

Fluid

Fuel Gas

Construction

Valve Parts in Contact with Fluids									
Body	Brass								
Seals and Disc	NBR								
Core Tube	305 Stainless Steel								
Core and Plugnut	430F Stainless Steel								
Springs	302 Stainless Steel								
Shading Coil	Copper								

Electrical

	l .		ating and onsumpti			Spare Coil Family					
Standard Coil and			AC			General	Purpose	Explosionproof			
Class of Insulation	DC Watts	Watts	VA Holding	VA Inrush	Ambient Temp.°F	AC	DC	AC	DC		
F	-	10.1	25	70	-20 to 125	238610	-	238614	-		
Н	-	10.1	25	70	-20 to 140	238810	-	238914	-		
F	11.6	-	-	-	-20 to 104	-	238710	-	238714		

Standard Voltages: 24, 120, 240 volts AC, 60 Hz (or 110, 220 volts AC, 50 Hz). 6, 12, 24, 120, 240 volts DC. Must be specified when ordering.

Solenoid Enclosures

Standard: Watertight, Types 1, 2, 3, 3S, 4, and 4X with 1/2" conduit hub. **Optional:** RedHat II - Explosionproof and Watertight. To order, add Prefix "EF" to catalog numbers. (e.g. EF8210G075).

Valve Response Time
Opening Time: Less than 1 second
Closing Time: Less than 1 second









Approvals

UL listed to standard 429 "Electrically Operated Valves," Guide YIOZ, File MP618, Safety Valves.

FM Approved to Class 7400 "Liquid and Gas Safety Shutoff Valves."

CSA Certified to:

- Standard C22.2 No. 139 "Electrically Operated Valves," File 010381
- 2) Automatic Gas Valves Z21.21(6.5) C/I, File 112872.

Specifications English units (Metric)

Pipe			Operating Pressure Differential psi (bar)		Max. Fluid Temp. °F (°C)			_	Agency			Wattage		Approx. Shipping		
Size (in)	Size (in)	Factor Cv (Kv)	Btu/hr.	Min.	Max. AC	Max. DC	AC	DC	Catalog Number	Const. Ref.	UL	FM	CSA	AC	DC	Weight lbs (kgs)
COMBUSTION (Fuel Gas) - NORMALLY CLOSED																
3/8	5/8	2.8 (2.4)	150,000	0	50 (3.4)	25 (1.7)	125 (52)	104 (40)	8210G074	1	0	0	0	10.1	11.6	3.2 (1.5)
1/2	5/8	3.6 (3.1)	193,000	0	50 (3.4)	25 (1.7)	125 (52)	104 (40)	8210G075	1	0	0	0	10.1	11.6	3.2 (1.5)
3/4	3/4	5.0 (4.3)	295,000	0	50 (3.4)	25 (1.7)	125 (52)	104 (40)	8210G076	2	0	0	0	10.1	11.6	3.2 (1.5)
) = Safe	○ = Safety Shutoff Valve. ① 1" W.C. Drop @ 2" W.C. Inlet Pressure, 1,000 Btu/cu.ft. or more, 0.64 Specific Gravity Gas.															


Capabilities Chart

	Sole	enoid Options	Base Catalog Number	Resilient Materials	Standard Rebuild Kit		
Type 3-9	High Temp.	Junction Box ②	Wiring Box Screw Terminal	Brass	NBR	AC	DC
EF	HT	JB	JKF	8210G074	•	304076	306359
EF	HT	JB	JKF	8210G075	•	304076	306359
EF	HT	JB	JKF	8210G076	•	304076	306359

 ⁼ Standard. Other options may be available. All option combinations may not be available.
 UL and CSA only.

Gas Flow Chart

8210 N.C Watertight



Note: Flow curves are based on the following standard conditions: 5 psi (0.3 bar) inlet pressure and 68°F (20°C) fluid temperature.

EMERSON


COMBUSTION


Pilot Operated | 3/8" - 3/4" NPT

Dimensions inches (mm)

Con Re			Α	В	Н	J	K	L	N	Р	Т	w
1		in	1.66	3.03	3.95	2.04	2.42	2.75	3.42	3.39	1.95	2.28
	Ī	mm	42	77	100	52	61	70	87	86	50	58
2	2	in	1.66	3.03	4.20	2.04	2.58	2.81	3.45	3.55	1.95	2.28
		mm	42	77	107	52	66	71	88	90	50	58

Const. Ref. 1, 2





Mountable in any position.