



## 48" Industrial Fan - HF948


- HF948BS** - Brushed Steel Housing, Brushed Steel Blades
- HF948W** - Appliance White Housing, Appliance White Blades

- 48" span contoured metal blades
- Supplied with "J" hook for easy installation and smooth performance
- Blades must be mounted at least 10 feet above the floor
- Single speed fan using 120 volts
- Fan hung at 20 feet covers 1,500 sq. ft.
- Fan hung at 30 feet covers 1,200 sq. ft.
- Fan hung at 40 feet covers 700 sq. ft.
- Not reversible
- 8" and 22" downrod included
- Three Contoured Metal Blades
- Ships to Canada
- SW 81 or SW82 Control Sold Separately
- Not for residential applications



### 48" Industrial Fan Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
6879	72	95



A: 19.5"/33.5 B: 16.0"/30.0" C: 7.5" D:4.8"

go **ABOVE**™