ASCO[™] Tamper-Proof High-Shock Manual Reset Valves

Stainless Steel Bodies | 1/4" and 1/2" NPT

SERIES EV8308 Manual Reset

Features

- Designed to keep the valve in the shut-off position when the solenoid is de-energized, even if the handle is lifted. The valve will not be in the open position until the solenoid is energized and auxiliary air is present.
- Once the solenoid is de-energized, it requires power to be restored to the solenoid then the valve to be manually reset. Ideal for controlling critical processes
- Designed to meet vibration and/or shock per ISA specification S71.03C2
- Handles aggressive atmosphere per salt resistance testing (ASTM B117)
- Most hardware is stainless steel, and all aluminum components are hard anodized and Nituff[®] coated
- SIL 3 capable per IEC 61508, certified by Exida

Nituff is a registered trademark of Nimet Industries, Inc.

Construction

Valve Parts in Contact with Fluids									
Main Valve									
Body	316 Stainless Steel								
Springs	302 Stainless Steel								
Seals	NBR / FKM								
Air Operator Diaphragm	FMQ								
Pilot Valve	AC 10.1 W	DC 1.4 W							
Body	303 Stainless Steel	303 Stainless Steel							
Shading Coil	Silver	NA							
Seals	NBR	NBR / PTFE							
Core Tube	305 Stainless Steel	305 Stainless Steel							
Core and Plugnut	430F Stainless Steel	430F Stainless Steel							
Core Guide	CA	CA							
Core Springs	302 Stainless Steel	302 Stainless Steel							

Electrical

Standard	Wa	-	g and Pow mption	<i>i</i> er	Spare Coil Part Number				
Coil and			AC		General	Purpose	Explosionproof		
Class of	DC		VA	VA					
Insulation	Watts	Watts	Holding	Inrush	AC	DC	AC	DC	
F	11.6	10.1	25	76	238610	238710	238614	238714	
F	1.4	-	-	-	-	-	274714-902-D*		
		·			°				

Standard Voltages: 24, 120, 240, 480 volts AC, 60 Hz. 12, 24 volts DC. Must be specified when ordering.

* 24 VDC. For other voltages contact factory.



Solenoid Enclosures

Standard: Explosionproof and Watertight, Types 3, 3S, 4, 4X, 6, 6D, 7, and 9.

Approvals

CSA certified and UL listed General Purpose Valve (solenoid only) ATEX/IECEx certified with prefix "EV" as listed. SIL 3 capable per IEC 61508. Third party certification provided by EXIDA. Refer to Optional Features Electrical Section for details.

Options

Position indicator switch - GO[™] Switch (suffix SP) Contact factory for ordering information.

Operation Alternatives

No Voltage Release – With the pilot valve solenoid energized, the handle is raised manually and latches the operator in the "up" (latched) position. Upon loss of voltage, the latch is tripped returning the operator to the "down" (unlatched) position. If auxiliary air supply to the pilot valve is lost, the main valve will shift position.

Moving the handle while the valve is in the tripped state will not cause the actuator/process valve to shift.



ASCO[™] Tamper-Proof High-Shock Manual Reset Valves

Stainless Steel Bodies | 1/4" and 1/2" NPT

Specifications English units (Metric)

Pipe Size	Orifice Size	Flow Factor	Operating Pressure Differential psi (bar)		Fluid Temp. °F (°C)		Max. Ambient	Catalog	Const.			of Coil In per So		
(in)	(in)	Cv (Kv)	Pilot Min.	Pilot Max.	Main Max.	Min.	Max.	Temp. °F (°C)	Number	Ref.	Body Material	Pilot Construction	AC	DC
3/2 Tamp	3/2 Tamperproof High-Shock Manual Reset Valves - SiL 3 capable, certified by Exida													
1/4	5/16	1.5 (1.3)	25 (1.7)	125 (9)	150 (10)	-4 (-20)	180 (82)	125 (52)	EV8308G060 ①	1	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/4	5/16	1.5 (1.3)	25 (1.7)	125 (9)	150 (10)	-4 (-20)	140 (60)	140 (60)	EV8308G360 ①	1	Stainless Steel	No Voltage Release (NVR)	-	1.4/F
1/2	5/8	4 (3.4)	25 (1.7)	125 (9)	150 (10)	-4 (-20)	180 (82)	125 (52)	EV8308G061 ①	2	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/2	5/8	4 (3.4)	25 (1.7)	125 (9)	150 (10)	-4 (-20)	140 (60)	140 (60)	EV8308G361 ①	2	Stainless Steel	No Voltage Release (NVR)	-	1.4/F

① ATEX/IECEx certified with prefix "EV".

Dimensions Inches (mm)



