# RedHa

# **Tamperproof High-Shock Manual Reset Valves**

Stainless Steel Bodies 1/4" and 1/2" NPT

#### **Features**

- Designed to keep the valve in the shut-off position when the solenoid is de-energized, even if the handle is lifted. The valve will not be in the open position until the solenoid is energized and auxiliary air is present.
- Once the solenoid is de-energized, it requires power to be restored to the solenoid then the valve to be manually reset. Ideal for controlling critical processes
- Designed to meet vibration and/or shock per ISA specification S71.03C2
- Handles aggressive atmosphere per salt resistance testing (ASTM B117)
- Most hardware is stainless steel, and all aluminum components are hard anodized and Nituff® coated Nituff is a registered trademark of Nimet Industries, Inc.

#### Construction

Valve Parts in Contact with Fluids											
Main Valve											
ody 316 Stainless Steel											
Springs 302 Stainless Steel											
Seals NBR / FKM											
Air Operator Diaphragm FMQ											
Pilot Valve	AC 10.1 W	DC 1.4 W									
Body	303 Stainless Steel	303 Stainless Steel									
Shading Coil	Silver	NA									
Seals	NBR	NBR / PTFE									
Core Tube	305 Stainless Steel	305 Stainless Steel									
Core and Plugnut	430F Stainless Steel	430F Stainless Steel									
Core Guide	CA	CA									
Core Springs	302 Stainless Steel	302 Stainless Steel									

#### **Electrical**

Standard	Wa		g and Po umption	wer	Spare Coil Part Number					
Coil and			AC		General	Purpose	Explosionproof			
Class of	DC		VA	VA						
Insulation	Watts	Watts	Holding	Inrush	AC	DC	AC	DC		
F	11.6	10.1	25	76	238610	238710	238614	238714		
F	1.4	27471					274714-	902-D*		

Standard Voltages: 24, 120, 240, 480 volts AC, 60 Hz. 12, 24 volts DC. Must be specified when ordering.

\* 24 VDC. For other voltages contact factory.


#### Solenoid Enclosures

**Standard:** Explosionproof and Watertight, Types 3, 3S, 4, 4X, 6, 6D, 7, and 9.

#### **Approvals**

CSA certified and UL listed General Purpose Valve (solenoid only). ATEX/IECEx certified with prefix "EV" as listed. Refer to Optional Features Electrical Section for details.





#### **Options**

Position indicator switch (suffix SP); Redundant pilot valves. Contact factory for ordering information.

#### **Operation Alternatives**

No Voltage Release – With the pilot valve solenoid energized, the handle is raised manually and latches the operator in the "up" (latched) position. Upon loss of voltage, the latch is tripped returning the operator to the "down" (unlatched) position. If auxiliary air supply to the pilot valve is lost, the main valve will shift position.

Moving the handle while the valve is in the tripped state will not cause the actuator/process valve to shift.



## **Specifications** (English units)

Pipe Size	Orifice Size	Cv Flow	Operating Pressure Differential (psi)			uid p. °F	Max. Ambient	Catalog	Const.			Watt Rati of Coil Ir per So		
(in)	(in)	Factor	Pilot Min.	Pilot Max.	Main Max.	Min.	Max.	Temp. °F	Number	Ref.	Body Material	Pilot Construction	AC	DC
3/2 Tar	3/2 Tamperproof High-Shock Manual Reset Valves													
1/4	5/16	1.5	25	125	150	-4	180	125	EV8308G060 ①	1	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/4	5/16	1.5	25	125	150	-4	140	140	EV8308G360 ①	1	Stainless Steel	No Voltage Release (NVR)	-	1.4/F
1/2	5/8	4	25	125	150	-4	180	125	EV8308G061 ①	2	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/2	5/8	4	25	125	150	-4	140	140	EV8308G361 ①	2	Stainless Steel	No Voltage Release (NVR)	-	1.4/F

① ATEX/IECEx certified with prefix "EV".

### **Specifications (Metric units)**

Pipe Size	Orifice Size	Kv Flow Factor	Operating Pressure Differential (bar)		I	uid p. °C	Max. Ambient	Catalog	Const.				ng/ Class sulation lenoid	
(in)	(in)	(m³/h)	Pilot Min.	Pilot Max.	Main Max.	Min.	Max.	Temp. °C		Ref.	Body Material	Pilot Construction	AC	DC
3/2 Tamperproof High-Shock Manual Reset Valves														
1/4	5/16	1.3	1.7	9	10	-20	82	52	EV8308G060 ①	1	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/4	5/16	1.3	1.7	9	10	-20	60	60	EV8308G360 ①	1	Stainless Steel	No Voltage Release (NVR)	-	1.4/F
1/2	5/8	3.4	1.7	9	10	-20	82	52	EV8308G061 ①	2	Stainless Steel	No Voltage Release (NVR)	10.1/F	-
1/2	5/8	3.4	1.7	9	10	-20	60	60	EV8308G361 ①	2	Stainless Steel	No Voltage Release (NVR)	-	1.4/F

① ATEX/IECEx certified with prefix "EV".

### **Dimensions Inches (mm)**

