November 2022

# Type ACE95jr Tank Blanketing Valve




Figure 1. Type ACE95jr Tank Blanketing Valve

# Introduction

Tank blanketing is the process of using a gas, usually an inert gas such as nitrogen, to maintain a slightly positive pressure in an enclosed storage tank. Tank blanketing prevents a stored product from vaporizing into the atmosphere, reduces product combustibility and prevents oxidation or contamination of the product by reducing its exposure to air. Tank blanketing is utilized with various products, including: adhesives, pharmaceuticals, pesticides, fertilizers, fuels, inks, photographic chemicals and food additives. The Type ACE95jr valves are self-contained, fully balanced and used for accurate pressure control on tank blanketing systems. These valves help control emissions and provide protection against atmospheric contamination. Type ACE95jr valves maintain a positive tank pressure which reduces the possibility of tank wall collapse during pump out operations and prevents a stored product from vaporizing to atmosphere.



### **Specifications**

This section lists the specifications and ratings for the Type ACE95jr Tank Blanketing Valve. Factory specifications are stamped on the nameplate fastened to the actuator of the valve.

| Sizes and End Connection Styles<br>1/2 NPT<br>1 x 1/2 NPT<br>1 NPT<br>NPS 1/2 / DN 15, CL150 RF<br>NPS 1 / DN 25, CL150 RF<br>NPS 1 x 1/2 / DN 25 x 15, CL150 RF<br>NPS 1 / DN 25, Sanitary Flange | Temperature Capabilities <sup>(1)</sup> Nitrile (NBR):         -20 to 180°F / -29 to 82°C         Fluorocarbon (FKM):         0 to 212°F / -18 to 100°C         Ethylenepropylene (EPDM - FDA) <sup>(2)</sup> :         -20 to 212°F / -29 to 100°C         Perfluoroelastomer (FFKM):         -20 to 212°F / -29 to 100°C |  |  |  |  |
|--|--|--|--|--|--|
| Maximum Operating Inlet Pressure <sup>(1)</sup>  | Flow Coefficients for Relief Valve Sizing  |  |  |  |  |
| 200 psig / 13.8 bar  | (110% of rated C_)   |  |  |  |  |
| Maximum Emergency Outlet (Casing) Pressure <sup>(1)</sup>  | $C_v 0.2$ use $C_v 0.22$   |  |  |  |  |
| 20 psig / 1.4 bar  | $C_v 0.4$ use $C_v 0.44$   |  |  |  |  |
| Maximum Operating Control Pressure <sup>(1)</sup>  | IEC Sizing Coefficients  |  |  |  |  |
| 1.5 psig / 0.10 bar  | X <sub>r</sub> : 0.655; F <sub>n</sub> : 0.86; F <sub>i</sub> : 0.89   |  |  |  |  |
| Control Pressure Ranges <sup>(1)</sup>   | Construction Materials   |  |  |  |  |
| See Table 1  | Body: 316 Stainless steel  |  |  |  |  |
| Maximum Differential Pressure<br>Up to 200 psig / 13.8 bar   | <b>Trim:</b> 304 Stainless steel and 316 Stainless steel <b>Elastomers:</b> Nitrile (NBR), Fluorocarbon (FKM),   |  |  |  |  |
| Main Valve Flow Characteristic   | FDA-Ethylenepropylene (EPDM), or   |  |  |  |  |
| Linear   | Perfluoroelastomer (FFKM)  |  |  |  |  |
| Pressure Registration  | <b>Diaphragm:</b> Polytetrafluoroethylene (PTFE)   |  |  |  |  |
| External   | <b>Actuator:</b> 316 Stainless steel or Carbon steel   |  |  |  |  |
| Capacities   | Approximate Weight (with all accessories)  |  |  |  |  |
| See Table 4  | 30 lbs / 14 kg   |  |  |  |  |
| <ol> <li>The pressure/temperature limits in this Bulletin and any applicable standard or code limitatic</li> <li>FDA/USP Class VI approved/ADI-free elastomers (wetted parts only).</li> </ol>     | n should not be exceeded.  |  |  |  |  |

| OUTLET<br>(CONTROL PRESSURE RANGE) |                       | SPRING PART NUMBER         | SPRING MATERIAL                    | SPRING<br>FREE LENGTH |                             | SPRING WIRE<br>DIAMETER |                            |
|------------------------------------|-----------------------|----------------------------|------------------------------------|-----------------------|-----------------------------|-------------------------|----------------------------|
| in. w.c.                           | mbar                  |                            | -                                  | in.                   | mm                          | in.                     | mm                         |
| -5 to -0.5                         | -12 to -1             | GC220701X22                | Stainless steel                    | 2.75<br>0.88          | 69.8<br>22.4 <sup>(1)</sup> | 0.080<br>0.085          | 2.03<br>2.16 <sup>(1</sup> |
| -1 to 1                            | -2 to 2               | GC220701X22                | Stainless steel                    | 2.75<br>1.60          | 69.8<br>40.6 <sup>(1)</sup> | 0.080<br>0.065          | 2.03<br>1.65 <sup>(</sup>  |
| 0.5 to 5<br>4 to 10                | 1 to 12<br>10 to 25   | GC220701X22<br>GC220702X22 | Stainless steel<br>Stainless steel | 2.75<br>2.00          | 69.8<br>50.8                | 0.080<br>0.112          | 2.03<br>2.84               |
| 8 to 15<br>0.5 to 1.5 psig         | 20 to 37<br>34 to 103 | GC220703X22<br>GC220708X22 | Stainless steel<br>Stainless steel | 2.00<br>2.75          | 50.8<br>69.8                | 0.125<br>0.225          | 3.17<br>5.71               |

# Features and Benefits

**Large PTFE Diaphragm**—Resistant to corrosion and highly sensitive to changes in tank pressure.

**Fully Balanced**—Eliminates setpoint changes caused by variations in inlet pressure.

**Large Actuator**—Large actuator diaphragm increases sensitivity to tank pressure changes.

**Rolling Diaphragm**—The rolling diaphragm balances the pilot valve and eliminates friction, resulting in extremely accurate control.

**Special Service Capabilities**—Optional materials are available for applications handling sour gases.




Figure 2. Operational Schematic

# **Options and Accessories**

**Inlet Pressure Gauge**—Displays pressure of blanketing gas supply to the tank blanketing valve.

**Control Pressure Gauge**—Low-pressure gauge to measure control pressure (tank pressure).

**Purge Meter (Rotameter)**—Maintains a small amount of flow through the sensing or main line. Prevents corrosive tank vapors from damaging upstream equipment.

**Pressure Switch**—Allows installation of an alarm system to indicate low or high-pressure on the tank.

**Outlet Check Valve**—Prevents corrosive gases and vapors from flowing back into the blanketing system through the delivery line.

**Single Array Manifold (SAM)**<sup>(1)</sup>—Provides sense line connection and main valve connection through a single tank nozzle.

**Inlet Filter**—Screens out any foreign material upstream that may cause blockage in the gas flow.

**FDA/USP Class VI/ADI-free**—Sanitary constructions available with FDA/USP Class VI approved/ADI-free elastomers (wetted parts only).

# **Principle of Operation**

The Type ACE95jr Tank Blanketing Valve controls the vapor space pressure over a stored liquid. When liquid is pumped out of the tank or vapors in the tank condense, the pressure in the tank decreases. Tank pressure is sensed by the large actuator diaphragm. When tank pressure is less than the valve set pressure, spring force moves the actuator diaphragm downward.

When the actuator moves downward, it pushes open the valve plug which allows flow in to the tank. See Figure 2. When pressure in the tank increases above setpoint, the large actuator diaphragm is pushed upward, allowing the valve plug to close.

The valve plug is balanced (inlet pressure creates equal upward and downward force on these components); therefore, the outlet (control) pressure of the unit is not affected by fluctuating inlet pressure.

1. Installation of single array manifold requires the blanketing gas supply pipe to extend into the vapor space a minimum of 6 in. / 152 mm beyond the tank roof.




Figure 3. Type ACE95jr Tank Blanketing Valve Installation

# Installation

The Type ACE95jr Tank Blanketing Valve was assembled and preset to the customer specified pressure and setpoint at the factory. The outlet (control) pressure range of the valve is stamped on the nameplate fastened to the upper actuator case. The gas blanketing setpoint is the only adjustable feature on this unit.

When installing Type ACE95jr, the sensing line and gas-to-tank line must always be above the tank liquid level and should slope down towards the tank without any traps to avoid catching of liquid. Inlet supply line may be installed with a filter and the outlet piping should be full-sized and self draining to the tank and also valves and vents must be full line size and should be mounted above the tank.

# **NACE** Compliance

Optional materials are available for applications handling sour gases. These constructions comply with the recommendations of NACE International sour service standards.

The manufacturing processes and materials used by Emerson assure that all products specified for sour gas service comply with the chemical, physical and metallurgical requirements of NACE MR0175 ISO-2002, NACE MR0103 and/or NACE MR0175/ISO 15156. Customers have the responsibility to specify correct materials. Environmental limitations may apply and shall be determined by the user.

#### Table 2. Flow Rate Conversion(1)

| MULTIPLY MAXIMUM PUMP RATE OUT                              | ВҮ     |       |
|---|--------|-------|
| U.S. GPM  | 8.021  | SCFH  |
| U.S. GPH  | 0.1337 | SCFH  |
| m³/h  | 1.01   | Nm³/h |
| Barrels/h   | 5.615  | SCFH  |
| Barrels/day   | 0.2340 | SCFH  |
| 1. Gas flow of blanketing gas to replace liquid pumped out. |        |       |

Table 3. Correction Factors (for converting nitrogen flow rates to other gas flow rates)

| BLANKET GAS         | SPECIFIC GRAVITY                              | CORRECTION FACTOR |
|---------------------|---|-------------------|
| Natural Gas         | 0.60  | 1.270             |
| Air                 | 1.00  | 0.985             |
| Dry CO <sub>2</sub> | 1.52  | 0.797             |
|                     | Correction Factor = $\frac{0.985}{\sqrt{SG}}$ |                   |

# **Sizing Methods**

### **Direct Displacement**

Use the direct displacement method with extreme caution. The direct displacement method determines the amount of blanketing gas required to replace liquid pumped out of the tank. Direct displacement does not account for fluctuating temperature or other factors that may affect pressure in the vapor space. This method is typically applied to tanks operating at constant temperatures and containing non-flammable, non-volatile products.

$$Q_{total} = Q_{pum}$$

where,

Q<sub>total</sub> = Required Flow Rate

 Required Flow Rate to replace pumped out liquid from Table 2

### API 2000

 $\mathsf{Q}_{_{pump}}$ 

The American Petroleum Institute Standard 2000 (API 2000) sizing criteria accounts for liquid pump out as well as contraction of tank vapors due to cooling. When using API methods:

where,

$$Q_{total} = Q_{pump} + Q_{thermal}$$

Q<sub>total</sub> = Required Flow Rate

Q<sub>pump</sub> = Required Flow Rate to replace pumped out liquid from Table 2

Q<sub>thermal</sub> = Required Flow Rate due to thermal cooling. See Thermal Equations 1 through 4.

### Thermal Equations

For tanks up to 840,000 gal / 3180 m<sup>3</sup> capacity:

### **Equation 1:**

$$Q_{thermal}$$
 [SCFH air] =  $V_{tank} \times 0.0238$ 

**Equation 2:** 

Q<sub>thermal</sub> [SCFH nitrogen] = V<sub>tank</sub> x 0.0238 x 1.015

**Equation 3:** 

$$Q_{thermal}$$
 [Nm<sup>3</sup>/h air] =  $V_{tank} \times 0.169$ 

### **Equation 4:**

 $Q_{\text{thermal}}$  [Nm<sup>3</sup>/h nitrogen] =  $V_{\text{tank}} \times 0.169 \times 1.015$ 


where,

For Equations 1 and 2:  $V_{tank}$  = tank volume, gallons For Equations 3 and 4:  $V_{tank}$  = tank volume, m<sup>3</sup>

Depending on the method, there can be a significant difference in the calculated required capacity. No matter which method is used, the tank must be equipped with supplemental venting to protect the tank, product, and personnel in cases of equipment failure, fire exposure, or other conditions that could cause the tank pressure or vacuum to exceed operating limits.

# **Capacity Information**

Capacity tables are based on 0.97 specific gravity nitrogen. Nitrogen is the most common blanketing gas. Should you use a different gas, convert the tabular values as follows. For blanketing (pad) gases other than nitrogen, multiply the given nitrogen flow rate by the correction factors in Table 3. For gases of other specific gravities, multiply the given nitrogen flow rate by 0.985, and divide by the square root of the appropriate specific gravity.



IN. /

mm

### Figure 4. Type ACE95jr Dimensions

Table 4. Capacities in 0.97 Specific Gravity Nitrogen

|                  | INLET PR                   | ESSURE                   |      | Cv   | = 0.2 | C <sub>v</sub> = 0.4 |       |
|------------------|----------------------------|--------------------------|------|------|-------|----------------------|-------|
| psig             | bar                        | kg/cm                    | kPa  | SCFH | Nm³/h | SCFH                 | Nm³/h |
| 1 <sup>(1)</sup> | 0.07                       | 0.07                     | 6.90 | 42   | 1.1   | 84                   | 2.2   |
| 2(1)             | 0.14                       | 0.14                     | 13.8 | 61   | 1.6   | 120                  | 3.2   |
| 5 <sup>(1)</sup> | 0.34                       | 0.35                     | 34.5 | 98   | 2.6   | 210                  | 5.6   |
| 10               | 0.69                       | 0.70                     | 69.0 | 130  | 4.6   | 310                  | 8.3   |
| 15               | 1.0                        | 1.06                     | 103  | 160  | 4.3   | 400                  | 10.7  |
| 20               | 1.4                        | 1.41                     | 138  | 210  | 5.6   | 480                  | 12.9  |
| 25               | 1.7                        | 1.76                     | 172  | 250  | 6.7   | 550                  | 14.7  |
| 30               | 2.1                        | 2.11                     | 207  | 290  | 7.7   | 630                  | 16.9  |
| 40               | 2.8                        | 2.81                     | 276  | 370  | 9.9   | 780                  | 20.9  |
| 50               | 3.4                        | 3.52                     | 345  | 450  | 12.1  | 930                  | 24.9  |
| 60               | 4.1                        | 4.22                     | 414  | 530  | 14.2  | 1070                 | 28.7  |
| 70               | 4.8                        | 4.92                     | 483  | 610  | 16.3  | 1230                 | 33.0  |
| 80               | 5.5                        | 5.63                     | 552  | 690  | 18.5  | 1390                 | 37.3  |
| 90               | 6.2                        | 6.33                     | 621  | 780  | 20.9  | 1560                 | 41.8  |
| 100              | 6.9                        | 7.03                     | 690  | 860  | 23.0  | 1720                 | 46.1  |
| 120              | 8.3                        | 8.44                     | 827  | 1020 | 27.3  | 2040                 | 54.7  |
| 140              | 9.6                        | 9.85                     | 965  | 1180 | 31.6  | 2360                 | 63.2  |
| 160              | 11.0                       | 11.3                     | 1103 | 1340 | 35.9  | 2680                 | 71.8  |
| 180              | 12.4                       | 12.7                     | 1241 | 1500 | 40.2  | 3000                 | 80.4  |
| 200              | 13.8                       | 14.1                     | 1379 | 1660 | 44.5  | 3330                 | 89.2  |
| umes an outlet   | (control) pressure of 5 in | . w.c. / 12 mbar or less |      |      |       |                      |       |

#### Table 5. Type ACE95jr Dimensions

| DOD       | (0)75  |                     | DIMENSIONS     |     | ISIONS          | DNS |          |     |     |
|-----------|--------|---------------------|----------------|-----|-----------------|-----|----------|-----|-----|
| BODY SIZE |        | STRUCTURE           | NPT            |     | CL150 RF Flange |     | Sanitary |     |     |
|           |        |                     |                | Α   |                 |     |          |     |     |
| NPS       | DN     |                     | in.            | mm  | in.             | mm  | in.      | mm  |     |
| 1/2       | 15     | without Filter      | 3.7            | 94  | 9.7             | 246 |          |     |     |
| 1/2       | 15     | with Filter         | 8.1            | 206 | 10.1            | 256 |          |     |     |
| 1         | 0.5    | 4 05                | without Filter | 7.5 | 190             | 9.8 | 249      | 9.4 | 238 |
| 1         | 25     | with Filter         | 11.8           | 300 | 10.2            | 259 | 10.0     | 254 |     |
|           |        |                     |                | В   |                 |     |          |     |     |
| 4/0       | 45     | without Check Valve | 1.0            | 25  | 2.9             | 74  |          |     |     |
| 1/2       | 1/2 15 | with Check Valve    | 3.8            | 96  | 5.7             | 145 |          |     |     |
| 4         | 05     | without Check Valve | 4.7            | 119 | 3.0             | 76  | 2.8      | 71  |     |
| Т         | 25     | with Check Valve    | 7.5            | 190 | 5.8             | 147 | 5.6      | 142 |     |

# **Ordering Information**

Refer to the Specifications section on page 2. Carefully review each specification and construction feature, then complete the Ordering Guide.

Also, please complete the Specifications Worksheet at the bottom of the Ordering Guide on page 8.

# **Ordering Guide**

Body Size and Connection Styles (Select One)

- □ 1/2 NPT
- □ 1 x 1/2 NPT
- □ 1 NPT
- □ NPS 1/2 / DN 15, CL150 RF
- □ NPS 1 / DN 25, CL150 RF
- □ NPS 1 x 1/2 / DN 25 x 15, CL150 RF
- □ NPS 1 / DN 25, Sanitary Flange

### Actuator/Diaphragm (Select One)

- □ Carbon steel with PTFE Diaphragm
- □ Stainless steel with PTFE Diaphragm

### Elastomers (Select One)

- □ Nitrile (NBR)
- □ Fluorocarbon (FKM)
- □ Ethylenepropylene (EPDM FDA)
- □ Perfluoroelastomer (FFKM)

#### Main Valve Coefficient (Select One)

- □ C<sub>v</sub> 0.2
- □ C<sub>v</sub> 0.4

### Control Pressure Range (Select One)

- □ -5 to -0.5 in. w.c. / -12 to -1 mbar
- □ -1 to 1 in. w.c. / -2 to 2 mbar
- □ 0.5 to 5 in. w.c. / 1 to 12 mbar
- □ 4 to 10 in. w.c. / 10 to 25 mbar
- □ 8 to 15 in. w.c. / 20 to 37 mbar
- □ 0.5 to 1.5 psig / 34 to 103 mbar

### Accessories (Optional)

- □ Inlet Pressure Gauge
- □ Control Pressure Gauge
- □ Purge Meter (Rotameter)
- □ Pressure Switch
- □ Outlet Check Valve
- □ Inlet Filter

#### Single Array Manifold (Optional)

 Yes, please add a SAM unit to my order.
 Applicable only for 1/2 NPT body size and end connection.

#### Parts Kit (Optional)

□ Yes, please send one parts kit to match this order.

#### NACE

- □ MR0175-2002
- □ MR0103
- □ MR0175/ISO 15156

# **Ordering Guide (continued)**

| Specification Worksheet   |
|---|
| Application Specifications:         Product in Tank         Tank Size         Pump In Rate         Pump Out Rate  |
| Blanketing Gas (Type and Specific Gravity)  |
| Conservation Vent Setpoints:PressureVacuum  |
| Pressure Requirements (Please Designate Units):         Maximum Inlet Pressure $(P_{1max})$ Minimum Inlet Pressure $(P_{1min})$ Control Pressure Setting $(P_2)$ Maximum Flow $(Q_{max})$ |
| Other Specifications:<br>Is a vapor recovery regulator required?  |
| Other Requirements:   |

|  | Regulators Quick Order Guide  |  |  |  |  |
|--|---|--|--|--|--|
| * * *  | Readily Available for Shipment  |  |  |  |  |
| * *  | Allow Additional Time for Shipment  |  |  |  |  |
| *  | Special Order, Constructed from Non-Stocked Parts.<br>Consult Your local Sales Office for Availability. |  |  |  |  |
| Availability of the product being ordered is determined by the component with the<br>longest shipping time for the requested construction. |   |  |  |  |  |

Sisher.com

#### Webadmin.Regulators@emerson.com

- LinkedIn.com/company/emerson-automation-solutions
- Twitter.com/emr\_automation

#### **Emerson Automation Solutions**

#### Americas

McKinney, Texas 75070 USA T +1 800 558 5853 +1 972 548 3574

Europe Bologna 40013, Italy T +39 051 419 0611

Asia Pacific Singapore 128461, Singapore

T +65 6777 8211

Middle East and Africa Dubai, United Arab Emirates T +971 4 811 8100

D101964X012 © 1994, 2022 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 11/22. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher™ is a mark owned by Fisher Controls International LLC, a business of Emerson Automation Solutions.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management Regulator Technologies, Inc. does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selesssction, use and maintenance of any Emerson Process Management Regulator Technologies, Inc. product remains solely with the purchaser.

