November 2015

H722, H733, H284 and H5114 Series Relief Valves

Introduction

The H722, H733, H284 and H5114 Series relief valves are installed in tanks, both stationary and mobile, as a means of preventing excessive overpressure.

Features

- Stainless Steel—Total stainless steel construction (H284 Series has brass body) provides maximum resistance to corrosion and rust. This also allows for easier removal from the tank for periodic testing.
- H722 and H733 Series True Internal Design For Mobile Applications—The complete valve is secure inside the tank with only the nameplate extending above the coupling. The rugged hex body allows for easier insertion and removal.
- H284 and H5114 Series For Stationary Bulk Storage—Internal spring relief valves have only the poppet and part of the body outside the tank. The



Figure 1. H5114, H284, H733 and H722 Series

adjusting screw and all other parts are inside the tank, safe from tampering.

- **Standard Spring Settings**—The valves are available in industry standard start-to-discharge settings for ordering ease.
- Nitrile (NBR) Seat—The valve seat is made of nitrile for superior performance in LP-gas and NH₃ service.


| CONTAINER CONNECTION | START-TO-DISCHARGE SETTING | | | FLOW CAPACITY, SCFM AIR | | ACCESSORIES | |
|----------------------------|-------------------------------|-------------------|---------------|-------------------------|--------|------------------------------|---------------------|
| | psig | bar | - TYPE NUMBER | UL® | ASME | Protective Cap (Included) | Installation Wrench |
| 2 in. MNPT Mobile | 250 | 17.2 | H722-250 | 3635 | 3203 | P297 | P304 |
| | 265 | 18.3 | H722-265 | 3556 | 3386 | | |
| | 275 | 19.0 | H722-275 | 3714 | 3508 | | |
| 2 in. MNPT Bulk Storage | 225 | 15.5 | H284-225 | 9835 | 8797 | | ÷ |
| | 250 | 17.2 | H284-250 | 10,530 | 9724 | | |
| | 250 | 17.2 | H5114-250 | 10,530 | 9724 | | |
| | 265 | 18.3 | H5114-265 | 11,300 | 10,280 | | |
| 3 in. MNPT Mobile | 250 | 17.2 | H733-250 | 10,150 | 9369 | - P298 | P305 |
| | 265 | 18.3 | H733-265 | 10,940 | 9904 | | |
| All valves are 100% sta | ainless steel excep | t Type H284 has a | brass body. | | | | · |

Table 1. Ordering Information

UL® is a mark owned by Underwriters Laboratories



Bulletin LP-7: H722, H733, H284 and H5114



H284/H5114 SERIES

Figure 2. H722, H733, H284 and H5114 Series Dimension Drawings

LPG Equipment

Emerson Process Management Regulator Technologies, Inc.

USA - Headquarters McKinney, Texas 75070 USA Tel: +1 800 558 5853 Outside U.S. +1 972 548 3574

For further information visit www.fisherregulators.com

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher is a mark owned by Fisher Controls International LLC, a business of Emerson Process Management.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management Regulator Technologies, Inc. does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Process Management Regulator Technologies, Inc. product remains solely with the purchaser.



IN / mm