

Fisher™ Baumann™ 24003

3-Way Bronze or Stainless Steel Control Valve



General Application

The Fisher Baumann 24003 3-way control valve is ideally suited for control of flow and temperature where mixing or diverting service is required. This 3-way valve uses a rugged cast bronze or CF8M stainless steel body with S31600 austenitic stainless steel trim for extended service life.

Features

- Compact and light weight design reduces installed piping costs.
- Optional Fisher enhanced ENVIRO-SEAL™ packing system to meet critical emission control requirements; suitable for use in light duty chemical service (not for use in corrosive service). This option is available in the stainless steel version only.
- High quality S31600 austenitic stainless steel trim materials.
- Dual plug and stem guiding provides increased stability during plug travel.
- Multiple trim capacity reductions available to meet changing process requirements.
- Fisher™ FIELDVUE™ digital valve controllers available for remote calibration and diagnostics.




STAINLESS STEEL 3-WAY VALVE
WITH 32 ACTUATOR

Table 1. Flow Direction⁽¹⁾

Service	Inlet	Outlet
Diverting	C	U and L
Mixing	U and L	C

1. C = Common port, U = Upper port, L = Lower port


Figure 1. 24003 Valve Body with Standard Bonnet and NPS 1 Integral Seat




E1281

Table 2. Materials of Construction


KEY NO.	DESCRIPTION		MATERIAL	
			Bronze	Stainless Steel
1	Valve body		Bronze ASTM B62	ASTM A351 CF8M
2	Seat rings		ASTM A276 S31600 Condition A	ASTM A276 S31600 Condition A
2B	O-ring		N/A	TFE/P (Tetrafluoroethylene Propylene)
3	Bonnet		Bronze ASTM B62	ASTM A351 CF8M
4	Plug and stem assembly		ASTM A276 S31600 Condition A	ASTM A276 S31600 Condition A
5	Bottom port		Bronze ASTM B62	ASTM A351 CF8M
6	Packing	Standard	PTFE (Polytetrafluoroethylene) / PTFE, 25% Carbon-filled	
		Optional	Molded Graphite Ribbon (Flexible Graphite)	
			Fisher enhanced ENVIRO-SEAL (Stainless steel ONLY)	
7	Packing follower		ASTM A276 S31600 Condition A Stainless steel	
8	Drive nut (Yoke)		ASTM A194 S30400 Gr. 8	
27	Locknuts		Stainless steel (18-8 SST)	
58	Travel indicator		ASTM A240 S30400	

Figure 2. Standard Spring-Loaded PTFE V-Ring Packing Kit**Table 3. Standard Spring-Loaded PTFE V-Ring Packing Kit**

Key Number	Description	Material
6	Spring	ASTM A313 S30200
14	Packing set	PTFE (Polytetrafluoroethylene) / PTFE, 25% Carbon-filled
16	Washer	ASTM A240 S31600
20	Spacer	J-2000 (filled-Polytetrafluoroethylene)

Figure 3. Molded Graphite (Flexible Graphite) Packing Kit (Optional)**Table 4. Molded Graphite (Flexible Graphite) Packing Kit (Optional)**

Key Number	Description	Material
13	Bushings	Carbon-Graphite
14A	Packing rings	Graphite
14B	Packing ring	Graphite

Figure 4. Fisher enhanced ENVIRO-SEAL Packing Kit (Optional for Stainless Steel Only)**Table 5. Fisher enhanced ENVIRO-SEAL Packing Kit (Optional for Stainless Steel Only)**

Key Number	Description	Material
13	Bushing	Carbon-Graphite
14	Packing set	PTFE (Polytetrafluoroethylene) / PTFE, 25% Carbon-filled
17	Belleville spring	N06600 Nickel Alloy (ASTM B637 N07718, 40 HRC max)
18	Bushing	PEEK (Polyetheretherketone)
19	Washer	Modified PTFE

Special Fisher enhanced ENVIRO-SEAL Packing Note

The Fisher enhanced ENVIRO-SEAL PTFE packing system is suitable for 100 ppm environmental applications on services up to 51.7 barg / 750 psig and process temperatures ranging from -28 to +204°C / -20 to +400°F.

For non-environmental applications, this packing system offers excellent performance at the same temperature range up to the maximum valve working pressure.


Temperature limits apply to packing arrangements only. Complete valve assembly temperature limits may differ, refer to appropriate pressure/temperature ratings.

(Reference Fisher Packing Selection Guidelines for Sliding-Stem Valves, Bulletin 59.1:062, [D101986X012](#)).

Table 6. Technical Specifications

NOMINAL PIPE SIZE	NPS 1/2, 1, 1-1/2 and 2	
END CONNECTIONS	Screwed NPT	
SEAT PLUG SEALING	Metal-to-metal	
CHARACTERISTIC	Linear	
SEAT LEAKAGE	Class III	
VALVE BODY MATERIAL	Bronze	Stainless Steel
PRESSURE RATING	400 psi at 150°F / 250 psi at 400°F	720 psi at 150°F / 515 psi at 400°F
TEMPERATURE LIMITS	-20 to +400°F	-20 to +400°F

Figure 5. Valve Body and Temperature Limits




E1282

Table 7. Max C_v Values at 100% Plug Opening⁽¹⁾ ($K_v = 0.86 \times C_v$)

VALVE SIZE	ORIFICE DIAMETER	PLUG TRAVEL	RATED VALUES
NPS	in.	in.	C_v
1/2	0.626	0.56	1, 2
	0.876	0.56	4
1	0.876	0.56	4
	1.126	0.56	10
1-1/2	1.676	0.75	20
2	2.126	0.75	40


1. See [Fisher Catalog 12](#) for a full range of flow and sizing information.

Figure 6. Mixing Service Flow Characteristics



E1283

Figure 7. Diverting Service Flow Characteristics




E1284

Table 8. Valve Body Dimensions and Weights: NPT Valve Bodies Only

VALVE SIZE	VALVE BODY MATERIAL						TRAVEL	WEIGHT
	Bronze, NPT			Stainless Steel, NPT (A)				
NPS	A	B	C1	A	B	C1	in.	lbs
1/2	4.88	2.75	2.75	5.0	2.75	2.75	0.56	8
1	4.88	2.75	2.75	5.0	2.75	2.75	0.56	8
1-1/2	5.75	3.81	3.31	6.1	3.38	3.31	0.75	15
2	6.50	4.0	3.6	6.50	3.75	3.6	0.75	20

Figure 8. Dimensional Drawing



E1285

MM / IN.


**24000 3-WAY ATC/FAIL OPEN ACTUATOR
WITH HANDWHEEL**

NOTE: ACTUATOR REMOVAL REQUIRES 115 MM / 4.5 IN. VERTICAL CLEARANCE.

Table 9. Application Port⁽¹⁾

Service	Inlet	Outlet
Diverting	C	U and L
Mixing	U and L	C

1. C = Common port, U = Upper port, L = Lower port

Figure 9. Mixing and Diverting Applications

E1286

Table 10. Model Numbering System

24	SERVICE		PORT "L" FAILS		3	MATERIAL	
Valve Body Series					3-Way Valve Body		
24	D	Diverting	1	Closed	3	---	Bronze
	M	Mixing	2	Open		S	Stainless steel

 [LinkedIn.com/groups/3941826](https://www.linkedin.com/groups/3941826)
 [Fisher.com](https://www.fisher.com)

 [Facebook.com/FisherValves](https://www.facebook.com/FisherValves)
 [X.com/FisherValves](https://www.x.com/FisherValves)

D103329X012 © 2009, 2026 Emerson. All rights reserved. The Emerson logo is a trademark and service mark of Emerson Electric Co. Baumann, ENVIRO-SEAL, Fisher, and FIELDVUE are marks of an entity in the Emerson family of businesses. All other marks are the property of their respective owners.

Neither Emerson nor any of its affiliated entities assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson
Marshalltown, Iowa 50158 USA
Sorocaba, 18087 Brazil
Cernay 68700 France
Dubai, United Arab Emirates
Singapore 128461 Singapore

www.fisher.com

FISHER™


EMERSON™