

2-Way/2 Position Valves

Two-way solenoid valves have one inlet and one outlet, and are used to permit and shut off fluid flow.

Two Types of Operations Apply

Normally Closed (NC)

Fluid is shut off when the coil is de-energized, flows through the valve when the coil is energized.

Normally Open (NO)

Fluid flows through the valve when the coil is de-energized, shuts off when the coil is energized.

Two Types of Constructions Apply

Direct Acting

When the solenoid is energized, the core directly opens the orifice of a Normally Closed valve or closes the orifice in a Normally Open valve. The valve will operate at pressures from 0 psi to its rated maximum. The force needed to open the valve is proportional to the orifice size and fluid pressure. As orifice size increases, so does the required force. To open larger orifices without increasing solenoid size, internal pilots are used.

Internally Piloted

These valves use line pressure to assist operation.


When the coil is de-energized (on a Normally Closed valve), the pilot orifice is closed and line pressure is applied to the top of the piston or diaphragm through the bleed orifice, closing the valve. When the coil is energized, the core opens the pilot orifice, relieving pressure from the diaphragm or piston. Line pressure, alone, opens the valve by lifting the diaphragm or piston off the main orifice.

See Engineering Section for further details.


Standard and Optional Features

Solenoid valves are supplied, as listed, with either RedHat II molded epoxy solenoids or RedHat solenoids with metal enclosures. RedHat II valves are identified by the letter "G" or "H" in their catalog numbers; e.g., 8030G016. Many optional features may be added to your valves; e.g., high-temperature Class H molded coils, manual operators, and metering devices. See the Optional Features Section for details.


2-Way/2 Position Valves Flow Diagrams




Normally Closed Valve De-Energized



Normally Closed Valve Energized



Normally Open Valve De-Energized



Normally Open Valve Energized

Index

Series	General Description	Pipe Size (NPT)	Page
8030	Low Pressure	3/8" - 3/4"	3
8040/8215	Aluminum Body	1/8" - 3"	7
8210	General Service	3/8" - 2 1/2"	11
212	Composite Body	1/2" & 3/4"	17
8221	Slow Closing	3/8" - 2 1/2"	23
8223	High Pressure	1/4" - 3/4"	27
8256	Subminiature	1/8"	29
8260	Plastic Body	1/4" - 3/8"	33
8262/8263 NC	General Service	1/8" - 3/8"	37
8262 NO	General Service	1/8" - 1/4"	41





Because Time Matters

ASCO Today delivers the great products you need, when you need them. Just place your order by 3:00 P.M. EST and ASCO ships TODAY.

Guaranteed same day shipment or ASCO pays the freight. Over 2000 of ASCO's most popular products qualify for ASCO Today's guarantee. ASCO Today includes our most popular valves, valve rebuild kits, and accessories. As part of our continued drive for customer service, we expanded the ASCO Today program with over 50,000 products that can be shipped within five business days.

2, 3, & 4-Way Solenoid Valves | Air Operated Valves | Combustion Products | Miniature Valves

Products may vary in Canada, please call 1-519-758-2700 to check availability of specific catalog numbers.



ASCO Today is registered in the United States.