March 2009

Types J31 and J32 Rotary Gauge



Figure 1. J31 Series Rotary Gauge




Figure 2. Types J31 and J32 Rotary Gauge Installation Schematic

WARNING

Install, use, and maintain per Fisher® instructions and all applicable federal state, local laws and codes, and NFPA Pamphlet 58 or ANSI K61. 1. Periodic inspection and maintenance is essential.

The Types J31 and J32 rotary gauges can be used on both stationary and mobile installations. One mobile installations hangers should be used with these units to support the horizontal length of the dip tube.


CAUTION

Do not make the "A" dimension, see Figure 2 on reverse side, of the gauge any longer than is needed for the dip tube to reach the bottom of the container. Excessively long horizontal lengths produce stress on the gauge near the face of the coupling.

If the gauge is ordered with a straight dip tube, care must be taken when bending the tube to the particular container in installation. Do not place the encircled area of the gauge, see Figure 2, in a vise because this can weaken the gauge internally. Instead grip the dip tube portion of the gauge when bending the dip tube.







T20179

Figure 3. Types J31 and J32 Assembly

Parts List

Key	Description	Part Number	Key	Description	Part Number
1	Body Extension Tube		12	Set Screw, Alloy steel-plate	T1096424152
	Type J31, Zinc-plated steel	T10885T0012	13*	Key, Carbon steel-plate	T1096528982
	Type J32, 304 Stainless steel	T10885T0022	15	Dip Tube Assembly, Steel plate	
2	Stem Tube Collar Assembly			(For Type J31 Only)	
	Type J31	T10979000A2		69 to 92-inches (1753 to 2337 mm)	T11047000A2
	Type J32	T10979000B2		92 to 108-inches (2337 to 2743 mm)	T11047000C2
3*	O-ring, Nitrile (NBR)	T1095106562	17	Insert	
4	Packing Sleeve, Nylon (PA)	T1095606162		Type J31, Zinc-plate steel	T1095224102
5	Indicator, Ductile iron	T1088719232		Type J32, 303 Stainless steel	T1106635032
6*	Cap-Seat Assembly, Stainless steel		18*	Needle Bearing	
	Type J31	T10971000A2		Type J31, Carbon steel	T1095328992
	Type J32	T10971000B2		Type J32, Polytetrafluoroethylene (PTFE)	T1106538992
7	Friction Ring, Nylon (PA)	T1095706162	19	Washer, Nylon (PA)	T1095406162
9	Lock Nut, Zinc-plated steel	T1096124102	20	Dial, Aluminum	
10	Lock Nut, Zinc-plated steel	T1096224102		Type P322	T20207T0012
11	Seal Nut, 410/416 Stainless steel	T1096335132		Type P323	T20206T0012
	,			Type P324	T20237T0012

^{*}Recommended spare part

LP-Gas Equipment

Emerson Process Management Regulator Technologies, Inc.

USA - Headquarters McKinney, Texas 75070 USA Tel: 1-800-558-5853 Outside U.S. 1-972-548-3574

For further information visit www.emersonprocess.com/regulators/lp

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher is a mark owned by Fisher Controls, Inc., a business of Emerson Process Management.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Process Management product remains solely with the purchaser.

