March 2015

# Fisher™ MR95 and MR98 Series Regulators Transition Management Guide




Figure 1. Typical MR95/MR98 Series Regulator

# **Background**

The Fisher 95 Series pressure reducing regulators and Fisher 98 Series backpressure regulators, relief and differential relief valves have proven to be reliable, effective solutions in a wide variety of applications. Like the 95/98 Series, the MR95/MR98 Series operates with steam, air, liquids and process gases within a large range of temperatures and pressures. The introduction of the Fisher MR95 and MR98 Series builds on this history of success with improvements in performance and range of application. The MR95 Series features higher inlet pressures, while both the MR95 and MR98 Series offer increased flow capacity, more material options and extra features. These and other enhancements result in a product that is a marked improvement over its predecessors.

Table 1. New and Legacy Products Description

NEW PRODUCT	DESCRIPTION	LEGACY PRODUCT			
MR95 Series	MR95 Series Pressure Reducing / Differential Pressure Regulators				
MR98 Series	Backpressure Regulators / Relief and Differential Relief Valves	98 Series			

## **Purpose**

The purpose of this document is to ease the transition for the user from the 95/98 Series to the new MR95/MR98 Series. This transition can be most easily understood through the following categories:

- 1. **Fit** Is the installation of this product different?
- 2. Form Are there any physical changes?
- 3. **Function** How is the product different in its operation and performance?



Table 2. New and Legacy Products Configuration Description

NEW PRODUCT TYPE	DESCRIPTION	LEGACY PRODUCT TYPE					
	MR95 Series: Pressure Reducing Regulator						
MR95L	Direct-operated low pressure regulator for 2 to 30 psig / 0.14 to 2.1 bar outlet pressures	95L					
MR95H	Direct-operated high pressure regulator for 5 to 150 psig / 0.34 to 10.3 bar outlet pressures	95H					
MR95LD	Pressure-loaded low pressure differential regulator for 2 to 30 psi / 0.14 to 2.1 bar differential pressures	95LD					
MR95HD	Pressure-loaded high pressure differential regulator for 5 to 150 psi / 0.34 to 10.3 bar differential pressures	95HD					
MR95HP	Direct-operated high pressure regulator for 15 to 400 psig / 1.0 to 27.6 bar outlet pressures (soft-seated)	95HP					
MR95HT	Pressure-operated high pressure/high temperature regulator for 15 to 300 psig / 1.0 to 20.7 bar outlet pressures (metal seat) and up to 650°F / 343°C	95HT					
	MR98 Series: Backpressure Regulator/Relief Valve						
MR98L	Direct-operated low pressure backpressure regulator/relief valve with 2 to 38 psig / 0.14 to 2.6 bar set pressure range	98L					
MR98H	Direct-operated high pressure backpressure regulator/relief valve with 5 to 200 psig / 0.34 to 13.8 bar set pressure range	98H					
MR98LD	Pressure-loaded low pressure differential pressure relief valve with 2 to 38 psi / 0.14 to 2.6 bar set pressure range	98LD					
MR98HD	Pressure-loaded high pressure differential pressure relief valve with 5 to 200 psi / 0.34 to 13.8 bar set pressure range	98HD					
MR98HH	Direct-operated high pressure backpressure regulator/relief valve with 150 to 375 psig / 10.3 to 25.9 bar set pressure range	98HH					
MR98HHD	Pressure-operated high pressure backpressure regulator/relief valve with 150 to 375 psi / 10.3 to 25.9 bar differential set pressure range	98HHD					

Table 3. Physical Design Comparison

CATEGORY	MR95 SERIES	95 SERIES
Body Size	1/4, 1/2, 3/4, 1, 1-1/2 and 2 in. / DN 15, 20, 25, 40 and 50	1/4, 1/2, 3/4, 1, 1-1/2 ,and 2 in. / DN 15, 20, 25, 40 and 50
End Connection	NPT, SWE, CL150 RF, CL300 RF, CL600 RF* and PN 16/25/40 RF	NPT, SWE, CL150 RF, CL300 RF and PN 16/25/40 RF
Face-to-Face Dimension (Flanged Bodies)	14 in. / 356 mm	14 in. / 356 mm
Pressure Registration	Internal or External*	Internal
Vent Connection	1/4 NPT or Drilled Untapped Hole	1/4 NPT or Drilled Untapped Hole
CATEGORY	MR98 SERIES	98 SERIES
Body Size	1/4, 1/2, 3/4, 1, 1-1/2 and 2 in. / DN 15, 20, 25, 40 and 50	1/4, 1/2, 3/4, 1, 1-1/2 and 2 in. / DN 15, 20, 25, 40 and 50
End Connection	NPT, SWE, CL150 RF, CL300 RF and PN 16/25/40 RF	NPT, SWE, CL150 RF, CL300 RF and PN 16/25/40 RF
Face-to-Face Dimension (Flanged Bodies)	14 in. / 356 mm	14 in. / 356 mm
Pressure Registration	Internal or External*	Internal
Vent Connection	1/4 NPT or Drilled Untapped Hole	1/4 NPT or Drilled Untapped Hole
*New product offer		

The following is a discussion covering each of these three elements.

#### Fit

See Table 3. The new and legacy products have the same body sizes and end connections, with the addition of the CL600 RF end connection option for the MR95 Series. Face-to-face dimensions of flanged connections are the same. As a new feature, external pressure sensing is introduced for the MR95/MR98 Series products with the addition of a control line connection tap.

#### **Form**

See Tables 4 and 5. The new MR95/MR98 Series offers the same configuration options as the legacy series. New body and trim materials are available, including more standard diaphragm material options. A redesigned spring barrel introduces the unique diamond shape, distinguishing the Fisher™ brand. While the diaphragms and some springs remain common between the new and legacy series, other

parts are not interchangeable. See Table 9 for the list of interchangeable parts. The MR95/MR98 Series offers optional gauges on the inlet and outlet lines to allow for easy monitoring of regulator function.

#### **Function**

See Tables 4, 5 and 8. The MR95/MR98 Series features improvements that allow them to function effectively in a larger range of applications. These improvements include an option for steam applications, which includes 302 Stainless steel diaphragms and graphite gaskets, a redesigned bottom plug to reduce the chance of leakage and a more robust diaphragm clamping design. Options for inlet and outlet gauges and external pressure registration are available. These optional features combine with increased flow capacities to deliver greater utility. The orifice sizes of the new product are slightly larger than the legacy product resulting in an increase in flow capacity. The new external pressure registration option for the MR95/MR98 Series allows for more stable regulation.




Figure 2. Typical MR95/MR98 and 95/98 Series Operational Schematics

# MR95/MR98 Series

Table 4. Detailed Comparison of MR95 Series (New Product) and 95 Series (Legacy Product) Pressure Reducing Regulators


CATEGORY		MR95 S	ERIES (NEW PRODUC	CT)	95 SERIES (LEGACY PRODUCT)			
End Connection Style			NPT SWE CL150 RF CL300 RF PN 16/25/40 RF		NPT SWE CL150 RF CL300 RF PN 16/25/40 RF			
			CL600 RF					
Body Material			WCC Steel, CF8M Stain nel® and Hastelloy® C	lless steel,	Gray cast iron, WCC/WCB Steel, CF8M Stainless steel, Monel® and Hastelloy® C			
		Aluminum-Bronze,	LCC Steel and CF3M S	stainless steel				
		Body Size	Orific	e Size	Orifice	e Size		
		1/4 in.	0.284 in.	7.2 mm	0.25 in.	6.4 mm		
Body and Orifice Size		1/2 in.	0.416 in.	11 mm	0.375 in.	9.5 mm		
Office Size		3/4 and 1 in.	0.631 in.	16 mm	0.5625 in.	14 mm		
		1-1/2 and 2 in.	1.142 in.	29 mm	1.0625 in.	27 mm		
Control Pressure Range		5 to 5 to 5 to 5 to 13 to 15 to 15 to 15 to 15 to 25 to 60 to 60 to 60 to 70 to 80 to 80 to 100 t	6 psig / 0.14 to 0.41 bar 15 psig / 0.34 to 1.0 bar 80 psig / 0.34 to 5.5 bar 30 psig / 0.90 to 2.1 bar 5 30 psig / 1.0 to 2.1 bar 5 100 psig / 1.0 to 6.9 bar 5 120 psig / 1.7 to 5.2 bar 5 120 psig / 4.1 to 8.3 bar 5 260 psig / 4.1 to 20.7 bar 5 150 psig / 4.8 to 10.3 bar 5 400 psig / 5.5 to 20.7 bar 5 400 psig / 5.5 to 27.6 bar 6 140 psig / 6.9 to 9.7 bar 6 150 psig / 6.9 to 9.7 bar 6 150 psig / 8.3 to 10.3 bar 6 150 psig / 8.3 to 10.3 bar	r r r r r r r r r r r ar ar ar	5 to 15 psig / 0.34 to 1.0 bar 5 to 80 psig / 0.34 to 5.5 bar 13 to 30 psig / 0.90 to 2.1 bar 15 to 30 psig / 1.0 to 2.1 bar 15 to 100 psig / 1.0 to 2.1 bar 15 to 100 psig / 1.0 to 6.9 bar 25 to 75 psig / 1.7 to 5.2 bar 60 to 120 psig / 4.1 to 8.3 bar 60 to 260 psig / 4.1 to 17.9 bar 60 to 300 psig / 4.1 to 20.7 bar 70 to 150 psig / 4.8 to 10.3 bar 80 to 300 psig / 5.5 to 27.6 bar 100 to 140 psig / 5.5 to 27.6 bar 100 to 140 psig / 6.9 to 9.7 bar 120 to 150 psig / 8.3 to 10.3 bar			
Temperature Range			to 650°F / -40 to 343°C		-40 to 650°F / -40 to 343°C			
Diaphragm Material		Ethy Mo	2 Stainless steel, Fluoro lenepropylene (EPDM), nel® and Hastelloy® C	. ,	Neoprene (CR), 302 Stainless steel, Fluorocarbon (FKM), Ethylenepropylene (EPDM), Monel® and Hastelloy® C			
		Polytetrafluoroethyler	ne (PTFE) diaphragm pro	otector available	••	••		
Disk/Seat Material		Metal Seat: 416	e (NBR), Fluorocarbon ( Stainless steel, 316 Stai nel <sup>®</sup> and Hastelloy <sup>®</sup> C		Elastomer Seat: Nitrile (NBR), Fluorocarbon (FKM) and PTFE Metal Seat: 416 Stainless steel, 316 Stainless steel, Monel® and Hastelloy® C			
		Perf	t: Ethylenepropylene (E luoroelastomer (FFKM) Metal Seat: Alloy 6	PDM) and	Elastomer Seat  			
NACE Construction		Available (NA	CE MR0175-2002 and N	MR0103)	Available (NACE MR01	175-2002 and MR0103)		
			MR95L Series		95L S			
		1/4 in.	7 lbs	3.2 kg	6 lbs	2.7 kg		
	ige Ze	1/2 in. 3/4 and 1 in.	15 lbs 35 lbs	6.8 kg 16 kg	12 lbs 32 lbs	5.4 kg 15 kg		
Approximate Weight	y Size	3/4 and 1 iii.	MR95H Series	10 kg		Series		
	Body	1/4 in.	5 lbs	2.3 kg	4 lbs	1.8 kg		
		1/2 in.	10 lbs	4.5 kg	8 lbs	3.6 kg		
		3/4 and 1 in.	22 lbs	10 kg	20 lbs	9.1 kg		
Maximum Published Flow Capacity		1-1/2 and 2 in. 510,0	55 lbs 00 SCFH / 13,668 Nm³/h	25 kg	73 lbs 280,000 SCFH	33 kg H / 7504 Nm³/h		
Dimension		See Fi	gures 3 and 4 and Table	6	See Figures 3 a	nd 4 and Table 6		
Adjusting Screw	Squ	See Figures 3 and 4 and Table 6  Square Head Adjustment, Stainless steel Square Head Adjustment, Sealed Square Head Adjustment, Handwheel Adjustment and Tee-handle  Standard Adjusting Screw, Handwheel and Tee-handle						

Monel® is a registered trademark of Special Metals Corporation. Hastelloy® C is a registered trademark of Haynes International, Inc.

**Table 5.** Detailed Comparison of MR98 Series (New Product) and 98 Series (Legacy Product) Backpressure Regulators, Relief and Differential Relief Valves

CATEGORY		MR98 S	ERIES (NEW PRODUC	T)	98 SERIES (L	EGACY PRODUCT)	
End Connection Style			NPT SWE CL150 RF CL300 RF PN 16/25/40 RF		CI	NPT SWE _150 RF _300 RF 6/25/40 RF	
Body Material			WCC Steel, CF8M Stain nel® and Hastelloy® C	less steel,	Gray cast iron, WCC Steel, CF8M Stainless steel, Monel® and Hastelloy® C		
•		LCC Steel, CF3M	Stainless steel and Alum				
		Body Size	Orifice	e Size	Or	ifice Size	
		1/4 in.	0.284 in.	7.2 mm	0.25 in.	6.4 mm	
Body and Orifice Size		1/2 in.	0.416 in.	11 mm	0.375 in.	9.5 mm	
		3/4 and 1 in.	0.631 in.	16 mm	0.5625 in.	14 mm	
		1-1/2 and 2 in.	1.142 in.	29 mm	1.0625 in.	27 mm	
	İ	2 to 7	7 psig / 0.14 to 0.48 bar		2 to 7 psig	/ 0.14 to 0.48 bar	
		5 to 3	35 psig / 0.34 to 2.4 bar		5 to 35 psi	g / 0.34 to 2.4 bar	
	İ	6 to 1	4 psig / 0.41 to 0.97 bar		6 to 14 psig	/ 0.41 to 0.97 bar	
	İ	12 to	25 psig / 0.83 to 1.7 bar		12 to 25 psi	g / 0.83 to 1.7 bar	
	İ	15 to	35 psig / 1.0 to 2.4 bar	15 to 35 ps	ig / 1.0 to 2.4 bar		
	İ	20 to	38 psig / 1.4 to 2.6 bar	20 to 38 ps	ig / 1.4 to 2.6 bar		
Control Pressure Range	İ	20 to	65 psig / 1.4 to 4.5 bar		20 to 65 ps	ig / 1.4 to 4.5 bar	
•	İ	25 to	75 psig / 1.7 to 5.2 bar		25 to 75 psig / 1.7 to 5.2 bar		
	İ	50 to	100 psig / 3.4 to 6.9 bar	50 to 100 psig / 3.4 to 6.9 bar			
	İ	70 to	140 psig / 4.8 to 9.7 bar	70 to 140 psig / 4.8 to 9.7 bar			
		130 to	200 psig / 9.0 to 13.8 ba	r	130 to 200 psig / 9.0 to 13.8 bar		
		150 to 3	375 psig / 10.3 to 25.9 ba	ar	150 to 375 psig / 10.3 to 25.9 bar		
		75 to	170 psig / 5.2 to 11.7 bar		80 to 170 psig / 5.5 to 11.7 bar		
Temperature Range		-40 t	to 450°F / -40 to 232°C		-40 to 450°F / -40 to 232°C		
Diaphragm Material			2 Stainless steel, Fluoroo e (EPDM), Monel® and F		Neoprene (CR), 302 Stainless steel, Fluorocarbon (FKM), Ethyleneproplylene (EPDM), Monel® and Hastelloy® C		
Diapinagin material		PTFE dia	aphragm protector availa	ble			
Disk/Seat Material		Metal Seat: 416	Nitrile (NBR) and Fluoroc Stainless steel, 316 Stai nel® and Hastelloy® C		Metal Seat: 416 Stainle	NBR) and Fluorocarbon (FKM) ess steel, 316 Stainless steel, nd Hastelloy® C	
Disklocat material		Perl	t: Ethylenepropylene (Effluroelastomer (FFKM) Metal Seat: Alloy 6	PDM) and			
NACE Construction		Available (NA	CE MR0175-2002 and M	IR0103)	Available (NACE Mi	R0175-2002 and MR0103)	
			MR98L Series		98	L Series	
		1/4 in.	7 lbs	3.2 kg	6 lbs	2.7 kg	
	Se Ze	1/2 in.	15 lbs	6.8 kg	12 lbs	5.4 kg	
Approximate Weight	l iΩ ⊢	3/4 and 1 in.	35 lbs MR98H Series	16 kg	32 lbs	H Series	
Approximate Weight	Body	1/4 in.	5 lbs	2.3 kg	4 lbs	1.8 kg	
	"	1/2 in.	10 lbs	4.5 kg	8 lbs	3.6 kg	
		3/4 and 1 in.	22 lbs	10 kg	20 lbs	9.1 kg	
	$\perp$	1-1/2 and 2 in.	55 lbs	25 kg	73 lbs	33 kg	
Maximum Published Flow Capacity		206,0	000 SCFH / 5521 Nm <sup>3</sup> /h		157,000 SC	CFH / 4208 Nm³/h	
Dimension		See Fig	gures 3 and 5 and Table	7	See Figures	3 and 5 and Table 7	
Adjusting Screw	S	Sealed	t, Stainless steel Square Square Head Adjustmen el Adjustment and Tee-ha	Standard Adjusting	g Screw and Handwheel		

 $\label{eq:money} \mbox{Monel}{}^{\text{\tiny{lo}}} \mbox{is a registered trademark of Special Metals Corporation.} \\ \mbox{Hastelloy}{}^{\text{\tiny{lo}}} \mbox{C is a registered trademark of Haynes International, Inc.} \\$ 



TYPE MR95H/MR98H (DIMENSIONS ALSO APPLY TO TYPES MR95L/MR98L, MR95HT, MR95HP AND MR98HH) TYPE MR95L/MR98L FLANGED BODIES

AVAILABLE IN 1/2 TO 2 IN. / DN 15 TO 50 SIZES

(DIMENSIONS ALSO APPLY TO

TYPES MR95L/MR98L, MR95HT AND MR95HP)

TYPE MR95HD/MR98HD (DIMENSIONS ALSO APPLY TO TYPES MR95LD/MR98LD AND MR98HHD)

IN. / mm

Figure 3. Typical MR95 and MR98 Series Dimensions




Figure 4. Typical 95 and 98 Series Dimensions

Table 6. Typical MR95 and 95 Series Dimensions (see Figures 3 and 4)

						DIMI	ENSION, IN.	/ mm				
		,	A		(	3		D (	Max)			
	BODY SIZE.							T	/PE			
SERIES	IN. / DN	Gray Cast Iron	Steel and Stainless Steel	В		MR95L	MR95LD	MR95H, MR95HT and MR95HP	MR95HD	E	J	
	1/4 NPT	2.8 / 70	2.8 / 70	2.0 / 52	5.1 / 129	3.2 / 81	6.2 / 157	10.5 / 266	6.4 / 162	10.4 / 264	1/4 NPT	4.0 / 102
	1/2 / 15	3.9 / 99	4.0 / 102	1.9 / 47	7.0 / 178	4.3 / 108	7.8 / 199	11.6 / 295	8.3 / 211	11.5 / 293	1/4 NPT	4.0 / 102; 3.5 / 88.9 <sup>(1)</sup>
MR95	3/4 / 20	4.9 / 124	5.0 / 127	2.3 / 58	10.2 / 259	6.1 / 154	9.9 / 250	13.9 / 353	10.2 / 259	13.8 / 349	1/4 NPT	4.0 / 102
	1 / 25	4.9 / 124	5.0 / 127	2.3 / 58	10.2 / 259	6.1 / 154	9.9 / 250	13.9 / 353	10.2 / 259	13.8 / 349	1/4 NPT	4.0 / 102
	1-1/2 / 40	7.3 / 184	7.4 / 187	3.1 / 78		8.2 / 208			14.8 / 375	18.6 / 473	1/4 NPT	8.0 / 203
	2 / 50	7.3 / 184	7.4 / 187	3.1 / 78		8.2 / 208			14.8 / 375	18.6 / 473	1/4 NPT	8.0 / 203
						DIMI	ENSION, IN.	/ mm				
	BODY SIZE.		A		(	3		D (	Max)			
SERIES	IN. / DN	Gray Cast	Steel and	В			TYPE				E	J
		Iron	Stainless Steel		95L SERIES	95H SERIES	95L	95LD	95H, 95HT and 95HP	95HD		-
	1/4 NPT	2.3 / 57	2.8 / 70	1.8 / 46	5.1 / 129	3.2 / 81	4.6 / 117	7.9 / 202	4.5 / 114	7.9 / 200	1/8 NPT	2.8 / 70
	1/2 / 15	3.9 / 99	4.0 / 102	1.8 / 46	7.0 / 178	4.3 / 108	6.1 / 155	10.1 / 257	6.0 / 152	10.0 / 254	1/4 NPT	4.0 / 102
95	3/4 / 20	4.9 / 124	5.0 / 127	2.3 / 57	10.2 / 259	6.1 / 154	9.1 / 232	15.3 / 389	9.1 / 232	15.1 / 384	1/4 NPT	4.0 / 102
33	1 / 25	4.9 / 124	5.0 / 127	2.3 / 57	10.2 / 259	6.1 / 154	9.1 / 232	15.3 / 389	9.1 / 232	15.1 / 384	1/4 NPT	4.0 / 102
	1-1/2 / 40	7.3 / 184	7.4 / 187	2.8 / 71		8.2 / 208			14.7 / 373	18.3 / 465	1/4 NPT	6.8 / 171
	2 / 50	7.3 / 184	7.4 / 187	2.8 / 71		8.2 / 208			14.7 / 373	18.3 / 465	1/4 NPT	6.8 / 171
1. 1/2 in. /	DN 15 Flanged	Body.										

Note: Shaded cells indicate differences between the new and legacy product.

Table 7. Typical MR98 and 98 Series Dimensions (see Figures 3 and 4)

							DII	MENSION, I	N. / mm					
	BODY SIZE.		A		C	;		D (Max)						
SERIES	IN. / DN	Gray Cast	Steel and	В	B MR98L MR98H		TYPE							J
		Iron	Stainless Steel		SERIES SERIES	MR98L	MR98LD	MR98H	MR98HH	MR98HD	MR98HHD	_ E		
	1/4 NPT	2.8 / 70	2.8 / 70	2.0 / 52	5.1 / 129	3.2 / 81	6.2 / 157	10.5 / 66	6.4 / 162	8.6 / 219	10.4 / 64	13.7 / 349	1/4 NPT	4.0 / 102
	1/2 / 15	3.9 / 99	4.0 / 102	1.9 / 47	7.0 / 178	4.3 / 108	7.8 / 199	11.6 / 295	8.3 / 211	10.8 / 275	11.5 / 293	15.1 / 383	1/4 NPT	4.0 / 102; 3.5 / 88.9 <sup>(1)</sup>
	3/4 / 20	4.9 / 124	5.0 / 127	2.3 / 58	10.2 / 259	6.1 / 154	9.9 / 250	13.9 / 353	10.2 / 259	12.1 / 307	13.8 / 349	17.4 / 441	1/4 NPT	4.0 / 102
MR98	1 / 25	4.9 / 124	5.0 / 127	2.3 / 58	10.2 / 259	6.1 / 154	9.9 / 250	13.9 / 353	10.2 / 259	12.1 / 307	13.8 / 349	17.4 / 441	1/4 NPT	4.0 / 102
	1-1/2 / 40	7.3 / 184	7.4 / 187	3.1 / 78		8.2 / 208			14.8 / 375		18.6 / 473		1/4 NPT	8.0 / 203 <sup>(2)</sup> ; 8.76 / 223 <sup>(3)</sup>
	2 / 50	7.3 / 184	7.4 / 187	3.1 / 78		8.2 / 208			14.8 / 375		18.6 / 473		1/4 NPT	8.0 / 203 <sup>(2)</sup> ; 8.76 / 223 <sup>(3)</sup>
							DI	MENSION, I	N. / mm					
SERIES	BODY SIZE,				C	;	D (Max)							
OLIVILO	IN. / DN		Α	В	98L	98H			Т	YPE			E	J
					SERIES	SERIES	98L	98LD	98H	98HH	98	HD		
	1/4 NPT	3.2	/ 81	1.0 / 25	5.1 / 128	3.2 / 81	5.5 / 140	8.4 / 213	5.5 / 140	7.8 / 197	8.3	/ 211	1/8 NPT	2.8 / 70
	1/2 / 15	4.3	/ 108	0.9 / 22	7.0 / 178	4.3 / 108	7.3 / 184	10.6 / 270	7.2 / 183	10.0 / 254	10.5	7 267	1/4 NPT	4.0 / 102
98	3/4 / 20	5.0	/ 127	1.3 / 32	10.2 / 259	6.1 / 154	9.8 / 249	12.5 / 317	9.7 / 246	12.4 / 314	12.3	1/313	1/4 NPT	4.0 / 102
	1 / 25	5.0	/ 127	1.3 / 32	10.2 / 259	6.1 / 154	9.8 / 249	12.5 / 317	9.7 / 246	12.4 / 314	12.3	1/313	1/4 NPT	4.0 / 102
	1-1/2 / 40	6.6	/ 168	1.9 / 48		8.2 / 208			14.1 / 359		18.1	/ 459	1/4 NPT	6.8 / 171
	2 / 50	6.6	/ 168	1.9 / 48		8.2 / 208			14.1 / 359		18.1	/ 459	1/4 NPT	6.8 / 171

1. 1/2 in. / DN 15 Flanged Body.
 2. Type MR98HD
 3. Type MR98HHD
 Note: Shaded cells indicate differences between the new and legacy product.

Table 8. Pressure and Temperature Specifications

CATEGORY	MR95 SERIES	95 SERIES
Maximum Inlet Pressure	1000 psig / 68.9 bar*	600 psig / 41.4 bar
Maximum Outlet Pressure	600 psig / 41.4 bar	600 psig / 41.4 bar
Control Pressure Range	2 to 400 psig / 0.14 to 27.6 bar	2 to 400 psig / 0.14 to 27.6 bar
Temperature Range	-40 to 650°F / -40 to 343°C	-40 to 650°F / -40 to 343°C
Sample Flow Capacity Comparison <sup>(1)</sup>	26,000 SCFH / 687 Nm³/h	24,000 SCFH / 643 Nm³/h
Shutoff Classification per ANSI/FCI 70-3-2004:	Metal Seats: Class IV PTFE: Class IV Elastomer Seats: Class VI or better	Metal Seats: Class IV PTFE: Class IV Elastomer Seats: Class VI or better

Improved feature

<sup>1.</sup> Air at 30 psig / 2.1 bar outlet pressure, 100 psig / 6.9 bar inlet pressure, 10% droop. Higher capacities are available; see separate Bulletin for complete capacity information

CATEGORY	MR98 SERIES	98 SERIES		
Maximum Inlet Pressure	400 psig / 27.6 bar	400 psig / 27.6 bar		
Control Pressure Range	2 to 375 psig / 0.14 to 25.9 bar	2 to 375 psig / 0.14 to 25.9 bar		
Temperature Range	-40 to 450°F / -40 to 232°C	-40 to 450°F / -40 to 232°C		
Sample Flow Capacity Comparison <sup>(1)</sup>	35,000 SCFH / 950 Nm³/h	17,000 SCFH / 456 Nm³/h		
Shutoff Classification per ANSI/FCI 70-3-2004:	Metal Seats: Class IV PTFE: Class IV Elastomer Seats: Class VI or better	Metal Seats: Class IV PTFE: Class IV Elastomer Seats: Class VI		

<sup>1.</sup> Air at 35 psig / 2.4 bar relief setting, 10 psig / 0.69 bar pressure buildup over relief setting. Higher capacities are available; see separate Bulletin for complete capacity information.

Table 9. Interchangeable Parts

COMMON BETWEEN MR95/MR98 VS.95/98 SERIES?			
No			
No			
No			
Yes <sup>(1)</sup>			
Yes			
Yes <sup>(1)</sup>			
Yes <sup>(1)</sup>			
Yes			
Yes <sup>(1)</sup>			
Yes <sup>(1)(2)</sup>			
No			
Yes <sup>(3)</sup>			
Yes			

<sup>1.</sup> Applicable only to certain body sizes/spring ranges. See separate Instruction Manual for complete list.

### Conclusion

The introduction of the MR95/MR98 Series marks the improvement of pressure reducing, backpressure regulator and relief valve technology established by the 95/98 Series, while maintaining their standard of quality and durability. The increased flow and pressure capabilities, combined with new material options, make the MR95/MR98 Series more versatile than their predecessors, while still allowing easy in-line maintenance. Please refer to the respective product bulletins and instruction manuals for complete features.

Webadmin.Regulators@emerson.com





Facebook.com/EmersonAutomationSolutions



in LinkedIn.com/company/emerson-automation-solutions



Twitter.com/emr\_automation

#### **Emerson Automation Solutions**

#### **Americas**

McKinney, Texas 75070 USA T +1 800 558 5853 +1 972 548 3574

Bologna 40013, Italy T +39 051 419 0611

#### Asia Pacific

Singapore 128461, Singapore T +65 6777 8211

#### Middle East and Africa

Dubai, United Arab Emirates T +971 4 811 8100

D103745X012 © 2013, 2015 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 07/20.
The Emerson logo is a trademark and service mark of Emerson Electric

Co. All other marks are the property of their prospective owners Fisher™ is a mark owned by Fisher Controls International LLC, a business of Emerson Automation Solutions.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management Regulator Technologies, Inc. does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Process Management Regulator Technologies, Inc. product remains solely with the purchaser.



The distinctive diamond shape cast into every spring case uniquely identifies the regulator as part of the Fisher™ brand and assures you of the highest-quality engineering, durability, performance, and support.



<sup>2.</sup> Applicable for MR98/98 Series only. 3. Applicable for MR95/95 Series only.