

Eliminate the need to install, order or stock separate conduit body gaskets and covers with Appleton's Form-IN-Place covers.

Form-IN-Place covers feature an integral gasket that takes the place of traditional removable gaskets. The cover with integral gasket reduces parts to stock and simplifies cover installations by putting an end to time-consuming aligning, assembling and installing gaskets. Every Form-IN-Place cover comes ready to install right from the factory, with no additional assembly required.



For product information: www.appletonelec.com | 1.800.621.1506



Appleton Grp LLC d/b/a Appleton Group. The Appleton and Emerson logos are registered in the U.S. Patent and Trademark Office. © 2016, Appleton Grp LLC. All rights reserve.

## INTEGRAL GASKETS INCREASE INSTALLATION SPEED AND EFFICIENCIES.

Appleton's line of Form-IN-Place conduit body covers allows for new or existing facilities to benefit from superior sealing, reduced inventory parts and faster installation times. Form-IN-Place covers maintain maximum possible corrosion protection and now, with an integral gasket, provide a powerful, reusable seal against moisture and solvents. With captive pan-head screws, Form-IN-Place covers can be easily removed and re-installed while retaining these sealing properties for years of reuse.

- Broadest line of integral gasket covers available
- Captive pan-head screws
- Wedge-Lok<sup>™</sup> clips (FM7 only) provide superior screwdriver torque and cover seating
- High-strength, corrosion and weather resistant
- FM7, FM8 and FM9 are approved for wet locations
- Fits all body configurations and sizes from ½" to 4"

## **Standard Materials**

- Class I, Stamped Aluminum FM7, FM9
- Stamped Steel FM7, FM8
- Cast Aluminum FM7
- Cast Grayloy-Iron FM7, FM8

## **NEC/CEC Third Party Certifications:**

- UL Listed E2527
- CSA Certified 65183, Class 4413-02















| HUB<br>SIZE<br>(in.) | FM7              |                     |                      |                  | FM8              |                      | FM9                 |
|----------------------|------------------|---------------------|----------------------|------------------|------------------|----------------------|---------------------|
|                      | Stamped<br>Steel | Stamped<br>Aluminum | Cast<br>Grayloy-Iron | Cast<br>Aluminum | Stamped<br>Steel | Cast<br>Grayloy-Iron | Stamped<br>Aluminum |
| 1/2                  | APP170IG         | APP170IGSA          | APP170FIG            | APP170FIGSA      | 180IG            | 180FIG               | 190IG               |
| 3/4                  | APP270IG         | APP270IGSA          | APP270FIG            | APP270FIGSA      | 280IG            | 280FIG               | 290IG               |
| 1                    | APP370IG         | APP370IGSA          | APP370FIG            | APP370FIGSA      | 380IG            | 380FIG               | 390IG               |
| 11⁄4                 | APP470IG         | APP470IGSA          | APP470FIG            | APP470FIGSA      | 480IG            | 480FIG               | 490IG               |
| 1½                   | APP570IG         | APP570IGSA          | APP570FIG            | APP570FIGSA      | 580IG            | 580FIG               | 590IG               |
| 2                    | APP670IG         | APP670IGSA          | APP670FIG            | APP670FIGSA      | 680IG            | 680FIG               | 690IG               |
| 21/2 & 3             | APP870IG         | APP870IGSA          | APP870FIG            | APP870FIGSA      | 880IG            | 880FIG               | 889IG               |
| 31/2 & 4             | APP970IG         | APP970IGSA          | APP970FIG            | APP970FIGSA      | 980IG            | 980FIG               | 989IG               |



