ASCO™ Direct Mount RedHat II Spool Valves

High Flow, Pilot Operated | Direct NAMUR Mount | 1/4" - 1/2" NPT

Features

- Compact spool valve convertible from 3/2 to 5/2 with a single flow plate design (551 Series only)
- Mount directly to actuators with NAMUR interface per VDI/VDE 3845
- Single and dual solenoid constructions available
- Integral breather block vents to spring side of actuator to exhaust, preventing corrosion of the actuator
- Unique design combines hard T-seals and flexible o-rings, provides bubble-tight shutoff, resistance to dirt and multimillion cycle life controlling air or inert gas
- Low Power and Intrinsically Safe construction available See Special Service Pilot Valve Section for details

Construction

Valve Parts in Contact with Fluids								
Body	Aluminum, Black Anodized	Brass	316L Stainless Steel					
End Cover (Spring end)	Glass-filled Polyamide Brass 316L Stainless							
Spool Valve Internals	Zamak, Stainless Steel, Acetal (POM), Aluminum	Brass, Acetal (POM), Delrin						
Pilot End Covers	Aluminum, Black Anodized	Brass 316L Stainless Steel						
Core Tube	Stainless Steel							
Core and Plugnut	Stainless Steel							
Springs	Stainless Steel							
Seals and Discs	NBR							
Top Disc	Nylon (PA)							
Core Guide	Acetal							
Seat and Seat Insert	Brass, Acetal							
Shading Coil	Copper							
Rider Ring (low power)	PTFE							

Electrical

		Watt Rating and Spare Coil Power Consumption Part Number								
Standard Coil and			AC		General	Purpose	Explosi	onproof		
Class of Insulation	DC Watts	Watts	VA Holding	VA Inrush	AC	DC	AC	DC		
F	11.6	10.1	25	50	238610	238710	238614	238714		

Standard Voltages: 24, 120, 240, 480 volts AC, 60 Hz (110, 220 volts AC, 50 Hz). 6, 12, 24, 120, 240 volts DC. Must be specified when ordering. Other voltages are available when required.

Solenoid Enclosures

Standard: Watertight, Types 1, 2, 3, 3S, 4, and 4X.

 $\begin{tabular}{ll} \textbf{Optional:} Explosion proof and Watertight, Types 3, 3S, 4, 4X, 6, 6P, 7, and 9. \\ (To order, add prefix "EF" or ("EV" for stainless steel) to catalog number.) \\ \end{tabular}$


See Optional Features Section for other available options.











Nominal Ambient Temp. Ranges

Body Material	Description
Aluminum	AC: 5°F to 125°F (-15°C to 52°C) DC: 5°F to 104°F (-15°C to 40°C)
Brass	AC: -40°F to 125°F (-40°C to 52°C)
Stainless Steel	DC: -40°F to 104°F (-40°C to 40°C)

Approvals

UL/CSA approvals for aluminum constructions pending. EF and EV are UL listed solenoids.

CSA certified.

Meet applicable CE directives.

SIL 3 capable per IEC 61508 on normally closed single solenoid. Third party certification provided by EXIDA. *Refer to Engineering Section for details.*

ATEX/IECEx certified with prefix "EV" as listed.

Refer to Optional Features Electrical Section for details.



Specifications English units (Metric)

					Sin	gle So	lenoid	– PFD	$O_{AVG} = 3.3 \times 10^{-3}$						Du	al Solenoid			
	Pipe	Orifice	Flow Factor	Di	ting Pr ifferent psi (ba '-Inert (ial r)	Fli Ter	ax. uid np. (°C)			. Di	ting Pr fferent psi (ba -Inert (r)	Fl. Tei	ax. uid np. (°C)			Class	Rating/ of Coil lation
Body Material	Size (in)	Size	Cv (Kv=m ³ /h)		Max.	Max. DC	AC	DC	Catalog Number	Const. Ref.	Min.	Max.	Max. DC	AC	DC	Catalog Number	Const. Ref.	AC	DC
Aluminum 3/2, 5/2									8551G401	1						8551G402	1		
Aluminum 5/3 Center Closed									-	2						8551G465	2		
Aluminum 5/3 Center Open	1/4 ①	1/4 (6.4)	.86 (.7)	30	150	120	140	120	-	2	30	150	120	140	120	8551G466	2	10.1/5	11.6/F
Brass 3/2, 5/2				(2)	(10)	(8.2)	(60)	(48)	EF8551G403 ②	1	(2)	(10)	(8.2)	(60)	(48)	EF8551G404 ②	1	10.1/F	11.0/F
316L Stainless Steel 3/2, 5/2									EV8551G409 34	2						EV8551G410 34	2		
Aluminum 3/2, 5/2	1/2	1/2 (13)	3.7 (3.2)						8553G401	2						8553G402	2		

① 1/8 inch NPT exhaust for aluminum and brass. ② Brass construction supplied standard with EF solenoid. ③ Stainless steel construction supplied standard with EV solenoid. ④ ATEX/IECEx certified with prefix "EV".


Dimensions inches (mm)

Optional Manual Operators								
Add Suffix		Description						
МО		Push and turn to lock with flat head screwdriver slot						
MI	1 2	Momentary push in with flat head screwdriver slot						
МН	1 2	Momentary push in by hand						
мѕ	1 2	Push and turn to lock by hand						

Series	551
NPT	1/4
L1 ①	4.96 (126)
L2 ①	6.50 (165)
H2	4.38 (111)
H1	1.57 (40)
W	1.77 (45)

① Manual override option MH adds .250" (6.4), MS option adds .468" (11.9) to each solenoid endcap.

Const. Ref. 1



ASCO™ Direct Mount RedHat II Spool Valves

High Flow, Pilot Operated | Direct NAMUR Mount | 1/4" - 1/2" NPT


Dimensions inches (mm)

Optional Manual Operators								
Add Suffix		Description						
МО		Push and turn to lock with flat head screwdriver slot						
MI	1 2	Momentary push in with flat head screwdriver slot						
МН		Momentary push in by hand						
MS		Push and turn to lock by hand						

Series	551 (5/3)	553
NPT	1/4	1/2
L1 ①	-	7.09 (180)
L2 ①	7.44 (189)	8.85 (225)
H2	4.38 (111)	4.77 (121)
H1	1.57 (40)	2.08 (53)
W	1.77 (45)	2.87 (73)

Manual override option MH adds .250" (6.4),
 MS option adds .468" (11.9) to each solenoid endcap.

Const. Ref. 2



553 NAMUR Footprint

1.57 (40)

551 NAMUR Footprint

