



VACUUM REGULATORS

MAINTAIN DESIRED VACUUM



CPV (Bronze)

- **Body Size:** 1/4 in. / 8 mm
- **Outlet Pressure Range:** 1 to 30 in. Hg



D51/52 (Bronze)

- **Body Size:** NPS 1/2, 3/4, 1, 1 1/4, 1 1/2, 2 / DN 15, 18, 25, 32, 38, 50
- **Outlet Pressure Range:** 0 to 30 in. Hg
- **Maximum Inlet Pressure:** 250 psig / 17.2 barg
- **Maximum Capacity:** 200 SCFM
- **Temperature:** 180°F / 82°C