Rosemount[™] 385+

General Purpose pH/ORP Sensors



High performance for your process pH/ORP needs

The Rosemount 385+ pH/ORP combination sensors are used for reliable pH or oxidation/reduction potential measurements of aqueous solutions in pipelines, open tanks, or ponds. Rosemount 385+ sensors feature a triple junction reference that extends sensor life in processes containing poisoning ions.



Overview



A Robust Sensor Design

- Extended sensor life and protection against poisoning ions using a triple junction reference.
- Enhanced performance and increased life with cracking resistant glass.
- High pH glass option for greater performance and linearity at high process pH levels.
- Operates in pressures up to 100 psig at 100 °C.

Versatile Installation Options

- The sensor features both a submersion/insertion and a retractable version.
- Safely remove and replace retractable sensors under pressure without the need to shutdown your process.
- Compatible for use with a 1-1/2 in. ball valve assembly.

SMART Preamplifier

- Automatic recognition of pH sensors by Rosemount transmitters: 1066, 1057, 1056, and 56
- pH calibration data is stored which allows sensors to be calibrated in advance for "Plug and Play" installations in the field.

Contents

Overview	Dimensional Drawings
	· ·
Ordering Information	Accessories
Considerations	
Specifications	

Ordering Information



The Rosemount 385+ pH/ORP sensor features a Tefzel sensor body with a triple junction gel filled reference electrode and automatic temperature compensator housed in a titanium tube. The retractable version of this sensor comes with an integral sensor head junction box, a process connector, and integral preamplifier. Interconnecting cable from sensor junction box to transmitter is sold separately (PN 23646-01 or 9200273; see Accessories).

Table 1. Rosemount 385+ General Purpose pH/ORP Sensor ordering information

Model	Sensor type	
385+	pH/ORP sensor	
Body Configuration		
02	Retractable with Integral Preamplifier (1)	
03	Insertion/Submersion with Integral Preamplifier and 25 ft. Integral Cable (1)	
04	Insertion/Submersion without Integral Preamplifier and 15 ft. Integral Cable	
Measuring Electrode		
10	pH - General Purpose Low Resistivity (GPLR) pH glass	
11	High pH Glass	
12	Platinum ORP	
Typical Model Number: 385+-02-10		

^{1.} Preamplifier is SMART with -10 and -11 options and a standard preamplifier if with -12 option.

Specifications

Table 2. Rosemount 385+ General Purpose pH/ORP Sensor specifications

Measured Range		
pH range	0 to 14 pH	
ORP range	-1500 mV to 1500 mV	
Maximum Pressure at Retraction or Insertion (ball valve version)		
542 KPa abs (64 psig)		
Maximum Process Pressure and Temperature		
790 KPa abs (100 psig) at 100 °C (212 °F)		
Temperature Compensation		
(pH only) 0 to 100°C (32 to 212°F)		
Wetted Materials		
Tefzel, titanium, EPDM, 316 SS and Teflon (Code 02), Viton, glass, ceramic and (ORP only) platinum.		


Table 2. Rosemount 385+ General Purpose pH/ORP Sensor specifications

M . 1 (161 M . 1 .		
Weight/Shipping Weight		
Submersion/insertion	1.6 lb/2.8 lb (0.7 kg/1.25 kg)	
Retraction	6 lb/11 lb (2.7 kg/5.0 kg)	
Ball Valve	5 lb/10 lb (2.25 kg/4.5 kg)	
Process Connections		
With ball valve	1-1/2 in.	
Without ball valve	1 in.	
Cable Length		
Code 02	Requires interconnecting cable P/N 9200273 (Unprepped) or P/N 23646-01 (Prepped)	
Code 03	25 ft. Integral Cable	
Code 04	15 ft. Integral Cable	

Table 3. Percent Linearity Over pH Range

pH Range	Option 10	Option 11
0-2 pH	94%	94%
2-12 pH	99%	97%
12-13 pH	97%	98%
13-14 pH	92%	98%

Figure 1. Typical mounting configurations for the Rosemount 385+ Sensor



Dimensional Drawings

MILLIMETER INCH SCREW CAP -J-BOX TO TRANSMITTER 3/4" 8 FPT RECOMMENDED **FLEX CONDUIT** X 1/2" NPT MALE CONNECTOR **HEX NUTS** 1" X 1" NPT MALE CONNECTOR 1-1/2" FPT CAUTION REDUCING COUPLING Residual pressure and process may remain 1-1/2" FPT CLOSED NIPPLE trapped between ball valve and male connec Pressure/Temperature 1-1/2" FPT Rating: 100 PSIG at 100° C maximum pres-BALL

sure at retraction: 64

psig.

25.4 O.D. HOUSING

pH/ORP ELECTRODE

O.D. RETRACTION STOP COLLAR

Figure 2. Rosemount 385+-02 sensor dimensions (shown with and without ball valve kit PN 23240-00)

(Ball valve kit includes 1-1/2 in. coupling, 1-1/2 in. nipple, and 1-1/2 in. ball valve)

VALVE

 $\frac{152.4}{6.0}$ APPROX

TC

<u>553.7</u> 21.84

409.7 16.13

LOCKING PIN W/BEAD CHAIN CUSTOMER SENSOR CABLE HANDRAIL 2 PLCS MOUNTING CHANNEL **ALUMINUM** 2 PLCS. 10FT. STANDARD 6.096M 20FT. 1-1/2" PIPE **OPTIONAL** CLAMP SCHED 80 1-1/2" PIPE CLAMP 3 PLCS. 1-1/2" PIPE CLAMP 2
PLCS 45° SWEEP ELL **EXTENSION PIPE** UNISTRUT 1-5/8" X 1-5/8" **ALUMINUM** MILLIMETER INCH 385+PH/ORP

Figure 3. Rosemount 385+-03/-04 sensor dimensions (shown in handrail mounting assembly PN 11275-01)




Figure 4. Dimensional drawing for submersion/inversion version (code -03, -04)

SUBMERSION/INSERTION VERSIONS

Accessories

Table 4. Rosemount 385+ Sensor accessories information

Part number	Description
23166-00	1 in. x 1 in. NPT 316 SS process connector
23166-01	1 in. x 1 in. NPT titanium process connector
23594-01	EPDM O-ring for process connector (23166-01/-01), Qty 4
9510066	1 in. x 1 in. NPT nylon process connector
915240-03	2 in. PVC flow through Tee, 3/4 in. NPT process connection
915240-04	2 in. PVC flow through Tee, 1 in. NPT process connection
915240-05	2 in. PVC flow through Tee, 1-1/2 in. NPT process connection
11275-01	Handrail mounting assembly
23555-00	Remote junction box with preamplifier
23550-00	Remote junction box without preamplifier
23646-01	Extension cable for junction box, 11 conductor, shielded, prepped
9200273	Extension cable for junction box, 11 conductor, shielded, unprepped
23240-00	1-1/2 in. ball valve assembly, 316 SS (Process connector required)
9210012	4.01 pH buffer solution, 16 oz
9210013	6.86 pH buffer solution, 16 oz
9210014	9.18 pH buffer solution, 16 oz

LIQ-PDS-385+ June 2017

Global Headquarters

Emerson Automation Solutions

8200 Market Blvd Chanhassen, MN 55317

+1 800 999 9307 or +1 952 906 8888

+1 952 949 7001

Liquid.CSC@Emerson.com

North America Regional Office

Emerson Automation Solutions

8200 Market Blvd.

Chanhassen, MN 55317, USA

+1 800 999 9307 or +1 952 906 8888

+1 952 949 7001

RMT-NA.RCCRFQ@Emerson.com

Latin America Regional Office

Emerson Automation Solutions

1300 Concord Terrace, Suite 400 Sunrise. FL 33323. USA

+1 954 846 5030

+1 954 846 5121

RFQ.RMD-RCC@Emerson.com

Europe Regional Office

Emerson Automation Solutions GmbH

Neuhofstrasse 19a P.O. Box 1046 CH 6340 Baar Switzerland

+41 (0) 41 768 6111

+41 (0) 41 768 6300

RFQ.RMD-RCC@Emerson.com

Asia Pacific Regional Office

Emerson Automation Solutions Asia Pacific Pte Ltd

1 Pandan Crescent Singapore 128461

+65 6777 8211

+65 6777 0947

Enquiries@AP.Emerson.com

Middle East and Africa Regional Office

Emerson Automation Solutions

Emerson FZE P.O. Box 17033, Jebel Ali Free Zone - South 2 Dubai, United Arab Emirates

+971 4 8118100

+971 4 8865465

RFQ.RMTMEA@Emerson.com

Analyticexpert.com

in Linkedin.com/company/Emerson-Automation-Solutions

Twitter.com/Rosemount_News

Facebook.com/Rosemount

Youtube.com/user/RosemountMeasurement

S+ Google.com/+RosemountMeasurement

The Emerson logo is a trademark and service mark of Emerson Electric Co.

Rosemount and Rosemount logotype are trademarks of Emerson. All other marks are the property of their respective owners.

© 2017 Emerson. All rights reserved.

