

# Magnetic Latching Valves

Stainless Steel Bodies 1/4" NPT 3/2 SERIES Maglatch

#### **Features**

- Ideal for remote applications where continuously powered devices are not preferred, such as gas well equipment.
- Pressures up to 125 psi
- Stainless steel constructions

#### **Operation**

- 3 wire magnetic latching configuration
- In the latched position, when supply voltage is momentarily applied to coil 1, pressure port is connected to the cylinder port and the exhaust port is closed.
- In the unlatched position, when supply voltage is momentarily applied to coil 2, cylinder port is connected to the exhaust port and the pressure port is closed.

#### Fluid

Fuel Gas

#### Construction

Valve Parts in Contact with Fluids					
Body	303 Stainless Steel				
Seals and Discs	Acetal, NBR				
Core Tube	305 Stainless Steel				
Core and Plugnut	430F Stainless Steel				
Springs	Stainless Steel				
Shading Coil	Silver				


#### **Electrical**

Standard Coil and Class	Watt Rating and Power Consumption	Spare Coil Part Number	Spare Coil Part Number			
of Insulation	Watts	24/DC	12/DC			
F	14.2	278543-004-K*	278543-002-K*			
Standard Voltages: 12 & 24 VDC. Must be specified when ordering.						

#### **Solenoid Enclosures**

**Standard:** Explosion proof and Watertight, Types 3, 3S, 4, 4X, 6, 6P, 7, and 9.





# Nominal Ambient Temp. Ranges

-25°F to 110°F (-31°C to 43°C)

### **Approvals**

**Solenoid Only:** 

UL listed.

Meets applicable CE directives.



# **Specifications** (English units)

Pipe Size	Orifice Size	Cv Flow		Pressure tial (psi)	Max.Fluid		Const.	Watt Rating/ Class
(ins.)	(ins.)	Factor	Min.	Max	Temp. °F	Catalog Number	Ref.	of Coil Insulation
1/4	0.08	0.20	0	125	120	HV428342001 12/DC	1	14.2/F
1/4	0.08	0.20	0	125	120	HV428342002 24/DC	1	14.2/F

## **Specifications (Metric units)**

Pipe Size			Operating Pressure Differential (bar)		Max.Fluid		Const.	Watt Rating/ Class
(ins.)	(mm)	(m <sup>3</sup> /h)	Min.	Max	Temp. °C	Catalog Number	Ref.	of Coil Insulation
1/4	2.0	0.17	0	8.6	48	HV428342001 12/DC	1	14.2/F
1/4	2.0	0.17	0	8.6	48	HV428342002 24/DC	1	14.2/F

## **Dimensions: inches (mm)**

