ASCO™ Series 212 Composite Valves

Composite, Engineered Plastic Valves

Applications

Water purification, conditioning and distribution in commercial/industrial markets with membrane based reverse osmosis systems. Reverse osmosis systems are found in several drinking water applications including restaurants, food and beverage equipment, and grocery store vegetable misting.



Features & Benefits

Tested and certified by NSF international:

- NSF 61-G: Drinking Water System Components (includes Lead Free requirements)
- NSF 169: Special Purpose Food Equipment and Devices
- NSF 42: Drinking Water Treatment Units Material and Structural Integrity Requirements
- NSF 372: Drinking Water System Components Lead Content Certification

Modular design with FasN™ technology, the world's first universal connection system

- The new ASCO FasN technology enables a quick and reliable connection system
- Available in Turn & Lock, and NPT Thread

Up to 150 psi and 150°F

• ASCO provides the most reliable valve on the market, with the highest performance

Increased reliability

ASCO's innovative design is tested for up to 1 million cycles

Manual operator option

• Allows for manual operation of the valve for system filling and troubleshooting

Low power coils

• 6.3 W in AC and 6.9 W in DC normally closed versions

Wide Range: From 1/2" to 1"

FasN[™] connection system

Reliable and secure connections

- Easy to install
- Save time when replacing a valve
- Ability to mix the types of connections on a single valve
- Fit with Copper (CTS) or PEX pipe



Specifications

•						
Pipe/Tubing Type	FasN End Connection	Port Size	MOPD (Water)	Fluid Temperature	Operation	Wattage
NPT Thread	NPT Threaded Pipe	1/2" 3/4" 1" ②	150 psi (10.3 bar)	150°F (66°C)	Normally Closed	AC = 6.3W DC = 6.9W
Copper (CTS), PEX Tubing	Turn & Lock					
					Normally Open ①	AC = 11W
						DC = 10W

① For NO version with DC coils, MOPD on water is 90 psi, with AC Coil is 120 psi

® For 1* NSF 61-G valves with PVC tubing, maximum fluid temperature is 73 *F/23 *C; for all other 1* valves, maximum fluid temperature is 122 *F/50 *C



For more information:

